



# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

**MAX4533**

## General Description


The MAX4533 quad, single-pole/double-throw (SPDT), fault-protected analog switch is pin-compatible with the industry-standard MAX333 and MAX333A. The MAX4533 features fault-protected inputs and Rail-to-Rail® signal handling. The normally open (NO<sub>-</sub>) and normally closed (NC<sub>-</sub>) terminals are protected from overvoltage faults up to  $\pm 25\text{V}$  with power on and up to  $\pm 40\text{V}$  with power off. During a fault condition, NO<sub>-</sub> and NC<sub>-</sub> become high impedance with only nanoamperes of leakage current flowing to the source. In addition, the output (COM<sub>-</sub>) clamps to the appropriate polarity supply rail and provides up to  $\pm 10\text{mA}$  of load current. This ensures unambiguous rail-to-rail outputs when a fault occurs.

The MAX4533 operates from dual  $\pm 4.5\text{V}$  to  $\pm 18\text{V}$  power supplies or a single  $+9\text{V}$  to  $+36\text{V}$  supply. All digital inputs have  $+0.8\text{V}$  and  $+2.4\text{V}$  logic thresholds, ensuring both TTL and CMOS logic compatibility when using  $\pm 15\text{V}$  supplies or a  $+12\text{V}$  supply. On-resistance is  $175\Omega$  max and is matched between switches to  $10\Omega$  max. The off-leakage current is only  $0.5\text{nA}$  at  $T_A = +25^\circ\text{C}$  and  $10\text{nA}$  at  $T_A = +85^\circ\text{C}$ .

## Applications

|                                |                          |
|--------------------------------|--------------------------|
| Redundant/Backup Systems       | Portable Instruments     |
| Test Equipment                 | Data-Acquisition Systems |
| Communications Systems         | Avionics Systems         |
| Industrial and Process Control |                          |

## Typical Operating Circuit



Rail-to-Rail is a registered trademark of Nippon Motorola, Ltd.

## Features


- ◆ Rail-to-Rail Signal Handling
- ◆  $\pm 40\text{V}$  Fault Protection with Power Off
- ◆  $\pm 25\text{V}$  Fault Protection with  $\pm 15\text{V}$  Supplies
- ◆ All Switches Off with Power Off
- ◆ No Power-Supply Sequencing Required During Power-Up or Power-Down
- ◆ Output Clamped to Appropriate Supply Voltage During Fault Condition—No Transition Glitch
- ◆  $1\text{k}\Omega$  (typ) Output Clamp Resistance During Overvoltage
- ◆  $175\Omega$  (max) Signal Paths with  $\pm 15\text{V}$  Supplies
- ◆  $20\text{ns}$  (typ) Fault Response Time
- ◆  $\pm 4.5\text{V}$  to  $\pm 18\text{V}$  Dual Supplies
- ◆  $+9\text{V}$  to  $+36\text{V}$  Single Supply
- ◆ Pin-Compatible with Industry-Standard MAX333/MAX333A
- ◆ TTL/CMOS-Compatible Logic Inputs with  $\pm 15\text{V}$  or Single  $+9\text{V}$  to  $+15\text{V}$  Supplies

## Ordering Information

| PART       | TEMP. RANGE                              | PIN-PACKAGE |
|------------|------------------------------------------|-------------|
| MAX4533CAP | $0^\circ\text{C}$ to $+70^\circ\text{C}$ | 20 SSOP     |
| MAX4533CWP | $0^\circ\text{C}$ to $+70^\circ\text{C}$ | 20 Wide SO  |

Ordering Information continued at end of data sheet.

## Pin Configuration/Functional Diagram



Maxim Integrated Products 1

**For pricing, delivery, and ordering information, please contact Maxim/Dallas Direct! at 1-888-629-4642, or visit Maxim's website at [www.maxim-ic.com](http://www.maxim-ic.com).**

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

## ABSOLUTE MAXIMUM RATINGS

Voltages Referenced to GND

|                                                                                          |                                  |
|------------------------------------------------------------------------------------------|----------------------------------|
| V+                                                                                       | .....-0.3V to +44.0V             |
| V-                                                                                       | .....-44.0V to +0.3V             |
| V+ to V-                                                                                 | .....-0.3V to +44.0V             |
| COM <sub>-</sub> , IN <sub>-</sub> (Note 1)                                              | ..... (V- - 0.3V) to (V+ + 0.3V) |
| NC <sub>-</sub> , NO <sub>-</sub> (Note 2)                                               | .....(V+ - 40V) to (V- + 40V)    |
| NC <sub>-</sub> , NO <sub>-</sub> to COM <sub>-</sub>                                    | .....-40V to +40V                |
| NC <sub>-</sub> , NO <sub>-</sub> Overvoltage with Switch Power On<br>(supplies at ±15V) | .....-30V to +30V                |
| NC <sub>-</sub> , NO <sub>-</sub> Overvoltage with Switch Power Off                      | .....-40V to +40V                |
| Continuous Current into Any Terminal                                                     | .....±30mA                       |
| Peak Current into Any Terminal<br>(pulsed at 1ms, 10% duty cycle)                        | .....±50mA                       |

Continuous Power Dissipation (T<sub>A</sub> = +70°C)

|                                                    |                      |
|----------------------------------------------------|----------------------|
| 20-Pin SSOP (derate 10.53mW/°C above +70°C)        | .....842mW           |
| 20-Pin Wide SO (derate 10.00mW/°C above +70°C)     | .. 800mW             |
| 20-Pin Plastic DIP (derate 11.11mW/°C above +70°C) | 889mW                |
| 20-Pin CERDIP (derate 11.11mW/°C above +70°C)      | .....889mW           |
| Operating Temperature Ranges                       |                      |
| MAX4533C                                           | .....0°C to +70°C    |
| MAX4533E                                           | .....-40°C to +85°C  |
| MAX4533M                                           | .....-55°C to +125°C |
| Storage Temperature Range                          | .....-65°C to +150°C |
| Lead Temperature (soldering, 10s)                  | .....+300°C          |

**Note 1:** COM<sub>-</sub> and IN<sub>-</sub> pins are not fault protected. Signals on COM<sub>-</sub> or IN<sub>-</sub> exceeding V+ or V- are clamped by internal diodes. Limit forward diode current to maximum current rating.

**Note 2:** NC<sub>-</sub> and NO<sub>-</sub> pins are fault protected. Signals on NC<sub>-</sub> or NO<sub>-</sub> exceeding -25V to +25V may damage the device. These limits apply with power applied to V+ or V-. The limit is ±40V with V+ = V- = 0.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

## ELECTRICAL CHARACTERISTICS—Dual Supplies

(V+ = +15V, V- = -15V, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted. Typical values are at T<sub>A</sub> = +25°C.) (Note 3)

| PARAMETER                                                                | SYMBOL                                        | CONDITIONS                                                                        | T <sub>A</sub> | MIN  | TYP  | MAX | UNITS |
|--------------------------------------------------------------------------|-----------------------------------------------|-----------------------------------------------------------------------------------|----------------|------|------|-----|-------|
| ANALOG SWITCH                                                            |                                               |                                                                                   |                |      |      |     |       |
| Fault-Free Analog Signal Range (Note 2)                                  | V <sub>NO_</sub> , V <sub>NC_</sub>           | V+ = +15V, V- = -15V, V <sub>NO_</sub> or V <sub>NC_</sub> = ±15V                 | C, E, M        | V-   |      | V+  | V     |
| COM_ to NO_ or COM_ to NC_ On-Resistance                                 | R <sub>ON</sub>                               | V <sub>NO_</sub> or V <sub>NC_</sub> = ±10V, I <sub>COM_</sub> = 1mA              | +25°C          |      | 125  | 175 | Ω     |
|                                                                          |                                               |                                                                                   | C, E           |      |      | 200 |       |
|                                                                          |                                               |                                                                                   | M              |      |      | 250 |       |
| COM_ to NO_ or COM_ to NC_ On-Resistance Match Between Channels (Note 4) | ΔR <sub>ON</sub>                              | V <sub>NO_</sub> or V <sub>NC_</sub> = ±10V, I <sub>COM_</sub> = 1mA              | +25°C          |      | 1    | 6   | Ω     |
|                                                                          |                                               |                                                                                   | C, E           |      |      | 10  |       |
|                                                                          |                                               |                                                                                   | M              |      |      | 15  |       |
| On-Resistance Flatness                                                   |                                               | V <sub>COM_</sub> = +5V, 0, -5V, I <sub>COM_</sub> = 1mA                          | +25°C          |      | 4    |     | Ω     |
| NO_ or NC_ Off-Leakage Current (Note 5)                                  | I <sub>NO_(OFF)</sub> , I <sub>NC_(OFF)</sub> | V <sub>NO_</sub> or V <sub>NC_</sub> = ±14V, V <sub>COM_</sub> = ∓14V             | +25°C          | -0.5 | 0.02 | 0.5 | nA    |
|                                                                          |                                               |                                                                                   | C, E           | -10  |      | 10  |       |
|                                                                          |                                               |                                                                                   | M              | -200 |      | 200 |       |
| COM_ On-Leakage Current (Note 5)                                         | I <sub>COM_(ON)</sub>                         | V <sub>COM_</sub> = ±14V, V <sub>NO_</sub> or V <sub>NC_</sub> = ±14V or floating | +25°C          | -0.5 | 0.01 | 0.5 | nA    |
|                                                                          |                                               |                                                                                   | C, E           | -20  |      | 20  |       |
|                                                                          |                                               |                                                                                   | M              | -400 |      | 400 |       |
| FAULT                                                                    |                                               |                                                                                   |                |      |      |     |       |
| Fault-Protected Analog Signal Range (Note 2)                             | V <sub>NO_</sub> , V <sub>NC_</sub>           | Applies with power on                                                             | +25°C          | -25  |      | +25 | V     |
|                                                                          |                                               | Applies with power off                                                            | +25°C          | -40  |      | +40 |       |
| COM_ Output Leakage Current, Supplies On                                 | I <sub>COM_</sub>                             | V <sub>NO_</sub> or V <sub>NC_</sub> = ±25V, no connection to “ON” channel        | +25°C          | -10  |      | 10  | nA    |
|                                                                          |                                               |                                                                                   | C, E           | -200 |      | 200 |       |
|                                                                          |                                               |                                                                                   | M              | -10  |      | 10  | μA    |
| NO_ or NC_ Off Input Leakage Current, Supplies On                        | I <sub>NO_</sub> , I <sub>NC_</sub>           | V <sub>NO_</sub> or V <sub>NC_</sub> = ±25V, V <sub>COM_</sub> = ∓10V             | +25°C          | -20  |      | 20  | nA    |
|                                                                          |                                               |                                                                                   | C, E           | -200 |      | 200 |       |
|                                                                          |                                               |                                                                                   | M              | -10  |      | 10  | μA    |

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

MAX4533

## ELECTRICAL CHARACTERISTICS—Dual Supplies (continued)

(V+ = +15V, V- = -15V, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted. Typical values are at T<sub>A</sub> = +25°C.) (Note 3)

| PARAMETER                                       | SYMBOL                                | CONDITIONS                                                                                            | T <sub>A</sub> | MIN  | TYP  | MAX  | UNITS |
|-------------------------------------------------|---------------------------------------|-------------------------------------------------------------------------------------------------------|----------------|------|------|------|-------|
| NO_ or NC_ Input Leakage Current, Supplies Off  | I <sub>NO_</sub> , I <sub>NC_</sub>   | V <sub>NO_</sub> or V <sub>NC_</sub> = ±40V, V+ = 0, V- = 0                                           | +25°C          | -20  | 0.1  | 20   | nA    |
|                                                 |                                       |                                                                                                       | C, E           | -200 |      | 200  |       |
|                                                 |                                       |                                                                                                       | M              | -10  |      | 10   | µA    |
| COM_ On-Clamp Output Current, Supplies On       | I <sub>COM_</sub>                     | V <sub>NO_</sub> or V <sub>NC_</sub> = +25V                                                           | +25°C          | 8    | 11   | 13   | mA    |
|                                                 |                                       | V <sub>NO_</sub> or V <sub>NC_</sub> = -25V                                                           | +25°C          | -12  | -10  | -7   |       |
| COM_ On-Clamp Output Resistance, Supplies On    | R <sub>COM_</sub>                     | V <sub>NO_</sub> or V <sub>NC_</sub> = ±25V                                                           | +25°C          |      | 1.0  | 2.5  | kΩ    |
|                                                 |                                       |                                                                                                       | C, E, M        |      |      | 3    |       |
| ±Fault Output Clamp Turn-On Delay Time (Note 6) |                                       | R <sub>L</sub> = 10kΩ, V <sub>NO_</sub> or V <sub>NC_</sub> = ±25V                                    | +25°C          |      | 20   |      | ns    |
| ±Fault Recovery Time (Note 6)                   |                                       | R <sub>L</sub> = 10kΩ, V <sub>NO_</sub> or V <sub>NC_</sub> = ±25V                                    | +25°C          |      | 2.5  |      | µs    |
| LOGIC INPUT                                     |                                       |                                                                                                       |                |      |      |      |       |
| IN_ Input Logic Threshold High                  | V <sub>IN_H</sub>                     |                                                                                                       | C, E, M        | 2.4  |      |      | V     |
| IN_ Input Logic Threshold Low                   | V <sub>IN_L</sub>                     |                                                                                                       | C, E, M        |      |      | 0.8  | V     |
| IN_ Input Current Logic High or Low             | I <sub>IN_H</sub> , I <sub>IN_L</sub> | V <sub>IN_</sub> = +0.8V or +2.4V                                                                     | +25°C          | -1   | 0.03 | 1    | µA    |
|                                                 |                                       |                                                                                                       | C, E, M        | -5   |      | 5    |       |
| SWITCH DYNAMIC CHARACTERISTICS                  |                                       |                                                                                                       |                |      |      |      |       |
| Turn-On Time                                    | t <sub>ON</sub>                       | V <sub>COM_</sub> = ±10V, R <sub>L</sub> = 2kΩ; Figure 2                                              | +25°C          |      | 100  | 250  | ns    |
|                                                 |                                       |                                                                                                       | C, E           |      |      | 400  |       |
|                                                 |                                       |                                                                                                       | M              |      |      | 600  |       |
| Turn-Off Time                                   | t <sub>OFF</sub>                      | V <sub>NO_</sub> = ±10V, R <sub>L</sub> = 2kΩ; Figure 2                                               | +25°C          |      | 60   | 150  | ns    |
|                                                 |                                       |                                                                                                       | C, E           |      |      | 300  |       |
|                                                 |                                       |                                                                                                       | M              |      |      | 450  |       |
| Break-Before-Make Time Delay                    | t <sub>BBM</sub>                      | V <sub>COM_</sub> = ±10V, R <sub>L</sub> = 1kΩ; Figure 3                                              | +25°C          | 10   | 50   |      | ns    |
| Charge Injection (Note 6)                       | Q                                     | C <sub>L</sub> = 100pF, V <sub>COM_</sub> = 0; Figure 4                                               | +25°C          |      | 1.5  |      | pC    |
| NO_ or NC_ Off-Capacitance                      | C <sub>N_(OFF)</sub>                  | f = 1MHz; Figure 5                                                                                    | +25°C          |      | 5    |      | pF    |
| COM_ On-Capacitance                             | C <sub>COM_(ON)</sub>                 | f = 1MHz; Figure 5                                                                                    | +25°C          |      | 12   |      | pF    |
| Off-Isolation (Note 7)                          | V <sub>ISO</sub>                      | R <sub>L</sub> = 50Ω, C <sub>L</sub> = 15pF, V <sub>N_</sub> = 1V <sub>RMS</sub> , f = 1MHz; Figure 6 | +25°C          |      | -62  |      | dB    |
| Channel-to-Channel Crosstalk (Note 8)           | V <sub>CT</sub>                       | R <sub>L</sub> = 50Ω, C <sub>L</sub> = 15pF, V <sub>N_</sub> = 1V <sub>RMS</sub> , f = 1MHz; Figure 6 | +25°C          |      | -66  |      | dB    |
| POWER SUPPLY                                    |                                       |                                                                                                       |                |      |      |      |       |
| Power-Supply Range                              | V+, V-                                |                                                                                                       |                | ±4.5 |      | ±18  | V     |
| V+ Supply Current                               | I+                                    | All V <sub>IN_</sub> = 0 or +5V, V <sub>NO_</sub> = V <sub>NC_</sub> = 0                              | +25°C          |      |      | 600  | µA    |
|                                                 |                                       |                                                                                                       | C, E, M        |      |      | 1000 |       |
| V- Supply Current                               | I-                                    | All V <sub>IN_</sub> = 0 or +5V, V <sub>NO_</sub> = V <sub>NC_</sub> = 0                              | +25°C          |      |      | 400  | µA    |
|                                                 |                                       |                                                                                                       | C, E, M        |      |      | 600  |       |
| GND Supply Current                              | I <sub>GND</sub>                      | All V <sub>IN_</sub> = 0 or +5V, V <sub>NO_</sub> = V <sub>NC_</sub> = 0                              | +25°C          |      |      | 300  | µA    |
|                                                 |                                       |                                                                                                       | C, E, M        |      |      | 450  |       |

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

## ELECTRICAL CHARACTERISTICS—Single Supply

(V+ = +12V, V- = 0, TA = TMIN to TMAX, unless otherwise noted. Typical values are at TA = +25°C.) (Note 3)

| PARAMETER                                                | SYMBOL                                         | CONDITIONS                                                                                    | T <sub>A</sub> | MIN  | TYP  | MAX | UNITS |
|----------------------------------------------------------|------------------------------------------------|-----------------------------------------------------------------------------------------------|----------------|------|------|-----|-------|
| ANALOG SWITCH                                            |                                                |                                                                                               |                |      |      |     |       |
| Fault-Free Analog Signal Range (Note 2)                  | V <sub>NO_</sub> , V <sub>VNC_</sub>           | V+ = +12V, V- = 0, V <sub>NO_</sub> or V <sub>VNC_</sub> = +12V or 0                          | C, E, M        | 0    |      | V+  | V     |
| COM_ to NO_, COM_ to NC_ On-Resistance                   | R <sub>ON</sub>                                | V+ = +12V, V <sub>NO_</sub> or V <sub>VNC_</sub> = +10V, I <sub>COM_</sub> = 1mA              | +25°C          | 260  | 390  |     | Ω     |
|                                                          |                                                |                                                                                               | C, E           |      | 450  |     |       |
|                                                          |                                                |                                                                                               | M              |      | 525  |     |       |
| COM_ -NO_ On-Resistance Match Between Channels (Note 4)  | ΔR <sub>ON</sub>                               | V+ = +12V, V <sub>NO_</sub> or V <sub>VNC_</sub> = +10V, I <sub>COM_</sub> = 1mA              | +25°C          | 4    | 10   |     | Ω     |
|                                                          |                                                |                                                                                               | C, E           |      | 20   |     |       |
|                                                          |                                                |                                                                                               | M              |      | 30   |     |       |
| NO_ or NC_ Off-Leakage Current (Notes 5, 9)              | I <sub>NO_(OFF)</sub> , I <sub>VNC_(OFF)</sub> | V+ = +12V, V <sub>COM_</sub> = +10V, +1V, V <sub>NO_</sub> or V <sub>VNC_</sub> = +1V, +10V   | +25°C          | -0.5 | 0.01 | 0.5 | nA    |
|                                                          |                                                |                                                                                               | C, E           | -10  | 10   |     |       |
|                                                          |                                                |                                                                                               | M              | -200 | 200  |     |       |
| COM_ On-Leakage Current (Notes 5, 9)                     | I <sub>COM_(ON)</sub>                          | V+ = +12V, V <sub>COM_</sub> = +10V, V <sub>NO_</sub> or V <sub>VNC_</sub> = +10V or floating | +25°C          | -0.5 | 0.01 | 0.5 | nA    |
|                                                          |                                                |                                                                                               | C, E           | -20  | 20   |     |       |
|                                                          |                                                |                                                                                               | M              | -400 | 400  |     |       |
| FAULT                                                    |                                                |                                                                                               |                |      |      |     |       |
| Fault-Protected Analog Signal Range (Note 2)             | V <sub>NO_</sub> , V <sub>VNC_</sub>           | Applies with power on                                                                         | +25°C          | -25  |      | +25 | V     |
|                                                          |                                                | Applies with power off                                                                        | +25°C          | -40  |      | +40 |       |
| COM_ Output Leakage Current, Supply On (Note 9)          | I <sub>COM_</sub>                              | V <sub>NO_</sub> or V <sub>VNC_</sub> = ±25V, V+ = +12V, no connection to “ON” channel        | +25°C          | -10  |      | 10  | nA    |
|                                                          |                                                |                                                                                               | C, E           | -200 |      | 200 |       |
|                                                          |                                                |                                                                                               | M              | -10  |      | 10  | μA    |
| NO_ or NC_ Off Input Leakage Current, Supply On (Note 9) | I <sub>NO_</sub> , I <sub>VNC_</sub>           | V <sub>NO_</sub> or V <sub>VNC_</sub> = ±25V, V <sub>COM_</sub> = 0, V+ = +12V                | +25°C          | -20  |      | 20  | nA    |
|                                                          |                                                |                                                                                               | C, E           | -200 |      | 200 |       |
|                                                          |                                                |                                                                                               | M              | -10  |      | 10  | μA    |
| NO_ or NC_ Input Leakage Current, Supply Off (Note 9)    | I <sub>NO_</sub> , I <sub>VNC_</sub>           | V <sub>NO_</sub> or V <sub>VNC_</sub> = ±40V, V+ = 0, V- = 0                                  | +25°C          | -20  | 0.1  | 20  | nA    |
|                                                          |                                                |                                                                                               | C, E           | -200 |      | 200 |       |
|                                                          |                                                |                                                                                               | M              | -10  |      | 10  | μA    |
| COM_ On-Clamp Output Current, Supply On                  | I <sub>COM_</sub>                              | V <sub>NO_</sub> or V <sub>VNC_</sub> = ±25V, V+ = +12V                                       | +25°C          | 2    | 3    | 5   | mA    |
| COM_ On-Clamp Output Resistance, Supply On               | R <sub>COM_</sub>                              | V <sub>NO_</sub> or V <sub>VNC_</sub> = ±25V, V+ = +12V                                       | +25°C          |      | 2.4  | 5   | kΩ    |
| LOGIC INPUT                                              |                                                |                                                                                               |                |      |      |     |       |
| IN_ Input Logic Threshold High                           | V <sub>IN_H</sub>                              |                                                                                               | C, E, M        | 2.4  |      |     | V     |
| IN_ Input Logic Threshold Low                            | V <sub>IN_L</sub>                              |                                                                                               | C, E, M        |      |      | 0.8 | V     |
| IN_ Input Current Logic High or Low                      | I <sub>IN_H</sub> , I <sub>IN_L</sub>          | V <sub>IN_</sub> = +0.8V or +2.4V                                                             | +25°C          | -1   | 0.03 | 1   | μA    |
|                                                          |                                                |                                                                                               | C, E, M        | -5   |      | 5   |       |

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

MAX4533

## ELECTRICAL CHARACTERISTICS—Single Supply (continued)

(V<sub>+</sub> = +12V, V<sub>-</sub> = 0, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted. Typical values are at T<sub>A</sub> = +25°C.) (Note 3)

| PARAMETER                                | SYMBOL                | CONDITIONS                                                                                                   | T <sub>A</sub>   | MIN | TYP | MAX        | UNITS |
|------------------------------------------|-----------------------|--------------------------------------------------------------------------------------------------------------|------------------|-----|-----|------------|-------|
| <b>SWITCH DYNAMIC CHARACTERISTICS</b>    |                       |                                                                                                              |                  |     |     |            |       |
| Turn-On Time                             | t <sub>ON</sub>       | V <sub>COM_</sub> = +10V,<br>R <sub>L</sub> = 2kΩ; Figure 2                                                  | +25°C<br>C, E, M | 200 | 500 | 1000       | ns    |
| Turn-Off Time                            | t <sub>OFF</sub>      | V <sub>COM_</sub> = +10V,<br>R <sub>L</sub> = 2kΩ; Figure 2                                                  | +25°C<br>C, E, M | 100 | 300 | 900        | ns    |
| Break-Before-Make Time Delay             | t <sub>BBM</sub>      | V <sub>COM_</sub> = +10V,<br>R <sub>L</sub> = 1kΩ; Figure 3                                                  | +25°C            | 5   | 100 |            | ns    |
| Charge Injection                         | Q                     | C <sub>L</sub> = 100pF,<br>V <sub>COM_</sub> = 0; Figure 4                                                   | +25°C            |     | 2   |            | pC    |
| NO_ or NC_ Off-Capacitance               | C <sub>NO_(OFF)</sub> | f = 1MHz; Figure 5                                                                                           | +25°C            |     | 5   |            | pF    |
| COM_ On-Capacitance                      | C <sub>COM_(ON)</sub> | f = 1MHz; Figure 5                                                                                           | +25°C            |     | 15  |            | pF    |
| Off-Isolation (Note 7)                   | V <sub>ISO</sub>      | R <sub>L</sub> = 50Ω, C <sub>L</sub> = 15pF,<br>V <sub>NO_</sub> = 1V <sub>RMS</sub> , f = 1MHz;<br>Figure 6 | +25°C            |     | -62 |            | dB    |
| Channel-to-Channel Crosstalk<br>(Note 8) | V <sub>CT</sub>       | R <sub>L</sub> = 50Ω, C <sub>L</sub> = 15pF,<br>V <sub>NO_</sub> = 1V <sub>RMS</sub> , f = 1MHz;<br>Figure 6 | +25°C            |     | -65 |            | dB    |
| <b>POWER SUPPLY</b>                      |                       |                                                                                                              |                  |     |     |            |       |
| Power-Supply Range                       | V <sub>+</sub>        |                                                                                                              | C, E, M          | 9   |     | 36         | V     |
| V <sub>+</sub> Supply Current            | I <sub>+</sub>        | All V <sub>IN_</sub> = 0 or +5V,<br>V <sub>NO_</sub> = V <sub>NC_</sub> = 0                                  | +25°C<br>C, E, M |     |     | 350<br>550 | μA    |
| V <sub>-</sub> and GND Supply Current    | I <sub>GND</sub>      | All V <sub>IN_</sub> = 0 or +12V,<br>V <sub>NO_</sub> = V <sub>NC_</sub> = 0                                 | +25°C<br>C, E, M |     |     | 200<br>350 | μA    |
|                                          |                       | All V <sub>IN_</sub> = 0 or +5V,<br>V <sub>NO_</sub> = V <sub>NC_</sub> = 0                                  | +25°C<br>C, E, M |     |     | 350<br>550 | μA    |
|                                          |                       |                                                                                                              |                  |     |     |            |       |
|                                          |                       |                                                                                                              |                  |     |     |            |       |

**Note 3:** The algebraic convention is used in this data sheet; the most negative value is shown in the minimum column.

**Note 4:** ΔRON = RON(MAX) - RON(MIN).

**Note 5:** Leakage parameters are 100% tested at maximum-rated hot temperature and guaranteed by correlation at T<sub>A</sub> = +25°C.

**Note 6:** Guaranteed by design.

**Note 7:** Off-isolation = 20log<sub>10</sub>(V<sub>COM\_</sub> / V<sub>NO\_</sub>), V<sub>COM\_</sub> = output, V<sub>NO\_</sub> = input to off switch.










**Note 8:** Between any two analog inputs.

**Note 9:** Leakage testing for single-supply operation is guaranteed by testing with dual supplies.

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

## Typical Operating Characteristics

( $V_+ = +15V$ ,  $V_- = -15V$ ,  $T_A = +25^\circ C$ , unless otherwise noted.)




# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

MAX4533


## Typical Operating Characteristics (continued)

( $V_+ = +15V$ ,  $V_- = -15V$ ,  $T_A = +25^\circ C$ , unless otherwise noted.)


**TURN-ON/TURN-OFF TIME vs. TEMPERATURE (SINGLE SUPPLY)**




**POWER-SUPPLY CURRENT vs. TEMPERATURE (DUAL SUPPLIES,  $V_{IN} = 0$ )**




**POWER-SUPPLY CURRENT vs. TEMPERATURE (DUAL SUPPLIES,  $V_{IN} = +5V$ )**




**POWER-SUPPLY CURRENT vs. TEMPERATURE (SINGLE SUPPLY)**




**LOGIC-LEVEL THRESHOLD vs. SUPPLY VOLTAGE**




**OVERVOLTAGE WITH  $\pm 25V$  INPUT**



**FAULT-FREE SIGNAL WITH  $\pm 15V$  INPUT**





**FAULT RECOVERY TIME**



# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

## Typical Operating Characteristics (continued)

( $V_+ = +15V$ ,  $V_- = -15V$ ,  $T_A = +25^\circ C$ , unless otherwise noted.)



## Pin Description

| PIN           | NAME                   | FUNCTION                                         |
|---------------|------------------------|--------------------------------------------------|
| 1, 10, 11, 20 | IN1, IN2, IN3, IN4     | Logic Control Digital Inputs                     |
| 2, 9, 12, 19  | NO1, NO2, NO3, NO4     | Normally Open Inputs*                            |
| 3, 8, 13, 18  | COM1, COM2, COM3, COM4 | Analog Switch Common Outputs*                    |
| 4, 7, 14, 17  | NC1, NC2, NC3, NC4     | Normally Closed Inputs*                          |
| 5             | V-                     | Negative Analog Supply Voltage Input             |
| 6             | GND                    | Digital Ground                                   |
| 15            | N.C.                   | No Connection. Not internally connected.         |
| 16            | V+                     | Positive Analog and Digital Supply-Voltage Input |

\*When the voltage on NO\_ or NC\_ does not exceed  $V_+$  or  $V_-$ , NO\_ (or NC\_) and COM\_ pins are bidirectional.

## Detailed Description

The MAX4533 is a fault-protected analog switch with special operation and construction. Traditional fault-protected switches are constructed using three-series CMOS devices. This combination produces good fault protection but fairly high on-resistance when the signals are within about 3V of each supply rail. These series devices are not capable of handling signals up to the power-supply rails.

The MAX4533 differs considerably from traditional fault-protected switches, with three advantages. First, it is constructed with two parallel FETs, allowing very low on-resistance when the switch is on. Second, they allow signals on the NC\_ or NO\_ pins that are within or slightly

beyond the supply rails to be passed through the switch to the COM\_ terminal, allowing rail-to-rail signal operation. Third, when a signal on NC\_ or NO\_ exceeds the supply rails by about 150mV (a fault condition), the voltage on COM\_ is limited to the appropriate polarity supply voltage. Operation is identical for both fault polarities. The fault-protection extends to  $\pm 25V$  with power on and  $\pm 40V$  with power off.

The MAX4533 has a parallel N-channel and P-channel MOSFET switch configuration with input voltage sensors. The simplified internal structure is shown in Figure 1. The parallel N1 and P1 MOSFETs form the switch element. N3 and P3 are sensor elements to sample the input voltage and compare it against the power-supply rails.

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch




Figure 1. Simplified Internal Structure

During normal operation of a conducting channel, N1 and P1 remain on with a typical  $125\Omega$  on-resistance between NO<sub>-</sub> (or NC<sub>-</sub>) and COM<sub>-</sub>. If the input voltage exceeds either supply rail by about 150mV, the parallel combination switches (N1, P1) are forced off through the driver and sensing circuitries. At the same time, the output (COM<sub>-</sub>) is clamped to the appropriate supply rail by the clamp circuitries (N2, P2). Two clamp circuits limit the output voltage to the supply voltages.

For simplicity, Figure 1 shows only one side of the SPDT switch configuration. The complete circuit is composed of two channels with their outputs connected.

## Normal Operation

Two comparators continuously compare the voltage on the NO<sub>-</sub> (or NC<sub>-</sub>) pin with V<sub>+</sub> and V<sub>-</sub> supply voltages. When the signal on NO<sub>-</sub> (or NC<sub>-</sub>) is between V<sub>+</sub> and V<sub>-</sub>, the switch behaves normally, with FETs N1 and P1 turning on and off in response to NO<sub>-</sub> (or NC<sub>-</sub>) signals (Figure 1). For any voltage between the supply rails, the switch is bidirectional; therefore, COM<sub>-</sub> and NC<sub>-</sub> (or NO<sub>-</sub>) are interchangeable. Only NO<sub>-</sub> and NC<sub>-</sub> can be exposed to overvoltages beyond the supply range and within the specified breakdown limits of the device.

## Fault Condition

The MAX4533 protects devices connected to its output (COM<sub>-</sub>) through its unique fault-protection circuitry. When the input voltage is raised above either supply rail, the internal sense and comparator circuitries (N3 and N-channel driver or P3 and P-channel driver) disconnect the output (COM<sub>-</sub>) from the input (Figure 1).

If the switch driven above the supply rail has an on state, the clamp circuitries (N2 or P2) connect the output to the appropriate supply rail. Table 1 summarizes the MAX4533's operation under normal and fault conditions. Row 5 shows a negative fault condition when the supplies are on. It shows that with supplies of  $\pm 15V$ , if the input voltage is between -15V and -25V, the output (COM<sub>-</sub>) clamps to the negative supply rail of -15V. With this technique, the SPDT switch is capable of withstanding a worse-case condition of opposite fault polarities at its inputs.

## Transient Fault Condition

When a fast rising or falling transient on NO<sub>-</sub> (or NC<sub>-</sub>) exceeds V<sub>+</sub> or V<sub>-</sub>, the output (COM<sub>-</sub>) follows the input (IN<sub>-</sub>) to the supply rail by only a few nanoseconds. This delay is due to the switch on-resistance and circuit capacitance to ground. However, when the input transient returns to within the supply rails there is a longer recovery time. For positive faults, the recovery time is typically 2.5 $\mu$ s. For negative faults, the recovery time is typically 1.3 $\mu$ s. These values depend on the COM<sub>-</sub> output resistance and capacitance. The delays are not dependent on the fault amplitude. Higher COM<sub>-</sub> output resistance and capacitance increase the recovery times.

## Fault Protection, Voltage, and Power Off

The maximum fault voltage on the NO<sub>-</sub> or NC<sub>-</sub> pins is  $\pm 40V$  from ground when the power is off. With  $\pm 15V$  supply voltages, the highest voltage on NO<sub>-</sub> (or NC<sub>-</sub>) can be +25V, and the lowest voltage on NO<sub>-</sub> (or NC<sub>-</sub>) can be -25V. Exceeding these limits can damage the chip.

## IN<sub>-</sub> Logic-Level Thresholds

The logic-level thresholds are TTL/CMOS-compatible when V<sub>+</sub> is +15V. Raising V<sub>+</sub> increases the threshold slightly; when V<sub>+</sub> reaches +25V, the level threshold is 2.8V—higher than the TTL output high-level minimum of 2.4V, but still compatible with CMOS outputs (see the *Typical Operating Characteristics*).

Increasing V<sub>-</sub> has no effect on the logic-level thresholds, but it does increase the gate-drive voltage to the signal FETs, reducing their on-resistance.

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

**Table 1. Switch States in Normal and Fault Conditions**

| POWER SUPPLIES (V+, V-) | INPUT RANGE                | NC_ | NO_ | OUTPUT                             |
|-------------------------|----------------------------|-----|-----|------------------------------------|
| On                      | Between Rails              | On  | Off | NC_                                |
| On                      | Between Rails              | Off | On  | NO_                                |
| On                      | Between V+ and (+40V - V+) | On  | Off | V+                                 |
| On                      | Between V+ and (+40V - V+) | Off | On  | V+                                 |
| On                      | Between V- and (-40V - V-) | On  | Off | V-                                 |
| On                      | Between V- and (-40V - V-) | Off | On  | V-                                 |
| Off                     | Between Rails              | Off | Off | Follows the load terminal voltage. |

## Failure Modes

The MAX4533 is not a lightning arrester or surge protector. Exceeding the fault-protection voltage limits on NO\_ or NC\_, even for very short periods, can cause the device to fail.

## Applications Information

### Ground

There is no connection between the analog signal paths and GND. The analog signal paths consist of an N-channel and P-channel MOSFET with their sources and drains paralleled and their gates driven out of phase to V+ and V- by the logic-level translators.

V+ and GND power the internal logic and logic-level translators and set the input logic thresholds. The logic-level translators convert the logic levels to switched V+ and V- signals to drive the gates of the switches. This

drive signal is the only connection between the power supplies and the analog signals. GND, IN\_, and COM\_ have ESD protection diodes to V+ and V-.

### Supply Current Reduction

When the logic signals are driven rail-to-rail from 0 to +12V or -15V to +15V, the supply current reduces to approximately half of the supply current when the logic input levels are at 0 to 5V.

### Power Supplies

The MAX4533 operates with bipolar supplies between  $\pm 4.5\text{V}$  and  $\pm 18\text{V}$ . The V+ and V- supplies need not be symmetrical, but their difference can not exceed the absolute maximum rating of +44V. The MAX4533 operates from a single supply between +9V and +36V when V- is connected to GND.

## Test Circuits/Timing Diagrams




Figure 2. Switching-Time Test Circuit

# Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch

## Test Circuits/Timing Diagrams (continued)

MAX4533




Figure 3. Break-Before-Make




Figure 4. Charge Injection




Figure 5.  $COM_-$ ,  $NO_-$ ,  $NC_-$  Capacitance

## **Quad, Rail-to-Rail, Fault-Protected, SPDT Analog Switch**

### **Test Circuits/Timing Diagrams (continued)**




Figure 6. Frequency Response, Off-Isolation, and Crosstalk

### **Ordering Information (continued)**

| PART       | TEMP. RANGE     | PIN-PACKAGE    |
|------------|-----------------|----------------|
| MAX4533CPP | 0°C to +70°C    | 20 Plastic DIP |
| MAX4533EAP | -40°C to +85°C  | 20 SSOP        |
| MAX4533EWP | -40°C to +85°C  | 20 Wide SO     |
| MAX4533EPP | -40°C to +85°C  | 20 Plastic DIP |
| MAX4533MJP | -55°C to +125°C | 20 CERDIP      |

## **Chip Information**

TRANSISTOR COUNT: 448

*Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.*