

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0906351403

Status:

Active

Overview:

QF-50™

Description:

1.27mm Pitch QF-50™, Single Beam, Vertical MIL/DIN Version, 0.38µm Gold (Au), 40 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0015 (PDF)


RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Ribbon Cable / Wire Trap Connectors
Series	90635
Comments	Preloaded Upper Housing
Component Type	Housing
Glow-Wire Compliant	No
Overview	QF-50™
Product Name	QF-50™
UPC	800753656017

Physical	
Circuits (Loaded)	40
Color - Resin	Black
Durability (mating cycles max)	300
Entry Angle	90° Angle
Flammability	94V-0
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	4.390/g
Number of Rows	2
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.381µm
Plating min - Termination	0.991µm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	IDT or Pierce
Wire Insulation Diameter	1.14mm max.
Wire Size AWG	26, 28
Wire/Cable Type	Ribbon Cable

Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	250V AC/DC

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/79/2015 (17

December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

90635 Series

Mates With

90663

Use With

90170

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Changehead for

0690080250

Parallel Action

Handtool 690080949

Arbor Press Fixture

0690200680

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-99020-0015
SDA-90635

Semi-Automatic 0691271150
Bench Press
PB15 C/W Cable
Sensor for 90635
Connectors

This document was generated on 02/02/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION