





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REV PER ECO-07-017102	20SEP07	PY	BW



.033 .027 [0.84 0.69]	.208 .168 [5.28 4.27]	.040 .020 [1.02 0.51]	.544 [13.82 .524 [13.31]	2.188 [55.58 2.168 [55.07]	.248 .238 [6.30 6.05]	.439 .419 [11.15 10.64]	.620 [15.75 .590 [14.99]	.428 [10.87 .418 [10.62]	2.411 [61.24 2.401 [60.99]	2.069 [52.55 2.059 [52.30]	2.650 [67.31 2.620 [66.55]	MS18277-1	50	5	M24308/23-11F	443976-5	1-443976-0								
			.432 .412 [10.97 10.46]	2.282 [57.96 2.262 [57.45]			.509 .479 [12.93 12.17]	.316 .306 [8.03 7.77]	2.505 [63.63 2.495 [63.37]	2.164 [54.97 2.154 [54.71]	2.744 [69.70 2.714 [68.94]	MS18276-1	37	4	M24308/23-10F	443976-4	443976-9								
				1.635 [41.53 1.615 [41.02]					1.857 [47.17 1.847 [46.91]	1.516 [38.51 1.506 [38.25]	2.103 [53.42 2.073 [52.65]	MS18275-1	25	3	M24308/23-9F	443976-3	443976-8								
				1.093 [27.76 1.073 [27.25]					1.317 [33.45 1.307 [33.20]	.976 [24.79 .966 [24.54]	1.556 [39.52 1.526 [38.76]	MS18274-1	15	2	M24308/23-8F	443976-2	443976-7								
				.769 [19.53 .749 [19.02]					.989 [25.12 .979 [24.87]	.648 [16.46 .638 [16.21]	1.228 [31.19 1.198 [30.43]	MS18273-1	9	1	M24308/23-7F	443976-1	443976-6								
				.544 [13.82 .524 [13.31]					2.188 [55.58 2.168 [55.07]	.620 [15.75 .590 [14.99]	.428 [10.87 .418 [10.62]	2.411 [61.24 2.401 [60.99]	2.069 [52.55 2.059 [52.30]	2.650 [67.31 2.620 [66.55]	MS18277-1	50	5	M24308/23-11F	443976-5	443976-5					
				.432 .412 [10.97 10.46]					2.282 [57.96 2.262 [57.45]	.509 .479 [12.93 12.17]	.316 .306 [8.03 7.77]	2.505 [63.63 2.495 [63.37]	2.164 [54.97 2.154 [54.71]	2.744 [69.70 2.714 [68.94]	MS18276-1	37	4	M24308/23-10F	443976-4	443976-4					
			1.635 [41.53 1.615 [41.02]				1.857 [47.17 1.847 [46.91]	1.516 [38.51 1.506 [38.25]	2.103 [53.42 2.073 [52.65]			MS18275-1	25	3	M24308/23-9F	443976-3	443976-3								
			1.093 [27.76 1.073 [27.25]				1.317 [33.45 1.307 [33.20]	.976 [24.79 .966 [24.54]	1.556 [39.52 1.526 [38.76]			MS18274-1	15	2	M24308/23-8F	443976-2	443976-2								
			.769 [19.53 .749 [19.02]				.989 [25.12 .979 [24.87]	.648 [16.46 .638 [16.21]	1.228 [31.19 1.198 [30.43]			MS18273-1	9	1	M24308/23-7F	443976-1	443976-1								
			N				M	L	J			H	G	F	E	D	C	B	A	INSERT ARRANGEMENT	NO OF POS	SHELL SIZE	MILITARY P/N ON CONNECTOR	AMP P/N ON CONNECTOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. <u>A.BAKER</u> 05MAY97 QWK ———		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: ——— INCHES ———		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P L C # — 1 P L C # — 2 P L C # — 3 P L C # — 4 P L C # — ANGLES # —		NAME ——— PRODUCT SPEC ——— APPLICATION SPEC ———	
		AMPLITUDE RECEPTACLE ASSY W/ SIZE 20 POSTED PC BOARD CONTACTS SERIES 190, SHELL SIZES 1 THRU 5		SIZE ——— GAGE CODE ——— DRAWING NO. ———	
MATERIAL ——— FINISH ———		WEIGHT ———		RESTRICTED TO ———	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 2 REV D	

