


DIMENSIONS: mm (in.)



## ■ SPECIFICATIONS

- Primary voltage: 120VAC 60Hz
- Exciting current, open circuit: 20mA max.
- DC resistance  $\pm$  15%:  $367\Omega$
- Secondary, no load voltage: 13.5VDC
- Loaded voltage: 9VDC @ 200mA
- Insulation resistance:  $100M\Omega$  @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute  
primary-core: 1,500VAC for 1 minute  
secondary-core: 500VAC for 1 minute
- Cord length: 6ft.

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[412-109024](#)