



SPECIFICATIONS

SILIKROME® Material	GRADE	
	COMMERCIAL	MILITARY
	Silicone Rubber ASTM D 1418	Silicone Rubber conforming to A-A-59588 Class II GR 50
Temperature Range	-112°F to +400°F (-80°C to +204°C)	-160°F to +450°F (-106°C to +260°C)
	-112°F to +575°F (-80°C to +302°C)	
Shelf Life	25 Years (minimum)	
Resistant to	Salt spray, sunlight, ozone, cleaning solutions, and most acids	
Physical Characteristics	Flexible, non-breakable, re-usable. Acts as shock mount. Protects against shattering. Easy to mount.	



SECTION AA

B	REDRAWN and MAT'L CHANGED				S. GOK	05.28.09
A	CAD COMPUTER GENERATED					01.10.03
REV.	DESCRIPTION					DATE
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.	TITLE:	SILIKROMES® COLORED FILTERS FOR INCANDESCENT T-1 LAMPS	ENG.	S. GOK	05.28.09	
			DWN.	N.K.S.	06.04.65	
			CHKD.	J. CELLA	05.28.09	
MAT'L: SEE ABOVE		APM-HEXSEAL CORPORATION	SCALE	DWG. NO.	1813/22	
COLOR: SPECIFY			10 : 1			

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

APM HEXSEAL:

[1813/22](#) [1813/22R5](#) [1813/22LW19-4](#) [1813/22 A2 C](#) [1813/22 B1 C](#) [1813/22 G1 C](#) [1813/22 G1-12 C](#) [1813/22 LW1](#)
[C](#) [1813/22 R2 C](#) [1813/22 Y1 C](#)