






	10	9	8	7	6	5	4	3	2	1
	QTY OF CIRCUITS "XX"	DIM. "A"	DIM. "B"	ASSEMBLY MATERIAL NO. (STANDARD)	ASSEMBLY MATERIAL NO. (-50 OPTION)					
F	02	21.1 [.83]	9.53 [.375]	387244102	387244902					
	03	30.7 [1.21]	19.05 [.750]	387244103	387244903					
	04	40.2 [1.58]	28.58 [1.125]	387244104	387294904					
	05	49.7 [1.96]	38.10 [1.500]	387244105	387244905					
	06	59.2 [2.33]	47.63 [1.875]	387244106	387244906					
	07	68.8 [2.71]	57.15 [2.250]	387244107	387244907					
	08	78.3 [3.08]	66.68 [2.625]	387244108	387244908					
	09	87.8 [3.46]	76.20 [3.000]	387244109	387244909					
E	10	97.3 [3.83]	85.73 [3.375]	387244110	387244910					
	11	106.9 [4.21]	95.25 [3.750]	387244111	387244911					
	12	116.4 [4.58]	104.78 [4.125]	387244112	387244912					
	13	125.9 [4.96]	114.30 [4.500]	387244113	387244913					
	14	135.4 [5.33]	123.83 [4.875]	387244114	387244914					
	15	145.0 [5.71]	133.35 [5.250]	387244115	387244915					
	16	154.5 [6.08]	142.88 [5.625]	387244116	387244916					



ISOMETRIC VIEW
SCALE 1:1
3 CIRCUIT SHOWN



4 REF -50 OPTION
(WHERE APPLICABLE)



- NOTES:
1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. PRODUCT SPECIFICATION: NOT REQUIRED
 4. PACKAGING: NOT REQUIRED
 5. MATES WITH: NONE
 6. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
 7. ALL COMPONENTS ARE ROHS COMPLIANT.

4	XX	SCREW W/WASHER, #6-32X.250, PANHD, PH-SL	STEEL	ZN, CLEAR CHROMATE
3	XX	SCREW, #6-32X.250, BHD, PHL-SLOT	STEEL	ZN, CLEAR CHROMATE
2	XX	TERMINAL, PC	BRASS	TIN PLATE
1	1	INSULATOR, SR, CS, MOLDED, -C	PBT	BLACK

ITEM	QTY	DESCRIPTION	MATERIAL	FINISH
------	-----	-------------	----------	--------

INITIAL RELEASE EC NO: ETC2006-0335 2006/03/27 DRW:CYRK 2006/03/31 CHKD:RDEROSS 2006/03/31 APPR:RDEROSS	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION																
		<table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>± ---</td> <td>±.0015</td> </tr> <tr> <td>3 PLACES</td> <td>± 0.038</td> <td>±.005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.13</td> <td>±.01</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.3</td> <td>± ---</td> </tr> </table>			mm	INCH	4 PLACES	± ---	±.0015	3 PLACES	± 0.038	±.005	2 PLACES	± 0.13	±.01	1 PLACE	± 0.3	± ---	DRAWN BY C. YORK DATE 2006/03/24 CHECKED BY RDEROSS DATE 2006/03/24 APPROVED BY RDEROSS DATE 2006/03/24		TITLE SR BTS, PC, CS ASSY 9.53 MM [.375] CENTERS			
			mm	INCH																				
		4 PLACES	± ---	±.0015																				
		3 PLACES	± 0.038	±.005																				
2 PLACES	± 0.13	±.01																						
1 PLACE	± 0.3	± ---																						
ANGULAR ± 2 °		MATERIAL NO. SEE CHART		MOLEX INCORPORATED																				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		DOCUMENT NO. SD-38724-002																				
A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						