







Copyright FCI.



rev	ecn no	dr	date
K	S40325	BSL	1994-12-20
L	S80115	BSL	1998-05-14
M	V94400	BSL	1999-12-01
N	S05-0064	KBM	2005-03-01
P	S10-0136	NBR	2010-06-28
-	-	-	-
-	-	-	-

							CONFIDENTIAL				
www.fciconnect.com			surface - 		tolerance std		projection	MM / INCH 			
			ISO 1302		ISO 406 ISO 1101						
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	BS LOW	2000-01-06	ANGULAR	LINEAR	X.X/.XX	±0.3/.01	size	Scale			
Eng	BS LOW	2000-01-06			X.XX/.XXX	±0.13/.005	A3	10:1			
Chr	KH LEE	2010-06-28	0° ±2°		X.XXX/.XXXX	±0.051/.0020	ECN	S10-0136			
Appr	JOEY NG	2010-06-28	Product family			LPVCC	Spec ref -				
			title			LOW PROFILE VCC SMT 3.00 ASSY			dwg no	92911	Rev. P
						WITH 0.46/.018 LOCATING FEATURES					
			catalog no			-			CUSTOMER		sheet 1 of 3


PRODUCT NO	POSITIONS	DIM. A	DIM. B
92911-X04	2 X 2	2.00/.079	3.92/.154
-X06	2 X 3	4.00/.158	5.92/.233
-X08	2 X 4	6.00/.236	7.92/.312
-X10	2 X 5	8.00/.315	9.92/.391
-X12	2 X 6	10.00/.394	11.92/.469
-X14	2 X 7	12.00/.472	13.92/.548
-X16	2 X 8	14.00/.551	15.92/.627
-X18	2 X 9	16.00/.630	17.92/.706
-X20	2 X 10	18.00/.709	19.92/.784
-X22	2 X 11	20.00/.787	21.92/.863
-X24	2 X 12	22.00/.866	23.92/.942
-X26	2 X 13	24.00/.945	25.92/1.020
-X28	2 X 14	26.00/1.024	27.92/1.099
-X30	2 X 15	28.00/1.102	29.92/1.178

PLATING OPTIONS OVER CONTACT AREA

0 = 0.2μ/8μ" Au

1 = 0.76μ/30μ" Au

3 = 0.38μ/15μ" Au



RECOMMENDED PAD LAYOUT





FIG. 1
SEE NOTE 7 (b) & (d)

www.fciconnect.com			surface -  ISO 1302		tolerance std ISO 406 ISO 1101		projection 		MM / INCH 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	BS LOW	2000-01-06	ANGULAR	LINEAR	X.X/.XX	±0.3/.01	size	A3	Scale		
Eng	BS LOW	2000-01-06			X.XX/.XXX	±0.13/.005			10:1		
Chr	KH LEE	2010-06-28	0°	±2°	X.XXX/.XXX	±0.051/.0020	ECN		S10-0136		
Appr	JOEY NG	2010-06-28	Product family				LPVCC	Spec ref		-	
		title	LOW PROFILE VCC SMT 3.00 ASSY					dwg no		92911	Rev. P
			WITH 0.46/.018 LOCATING FEATURES								
			catalog no					-		CUSTOMER	

1

2

3

4


NOTES:

- 1 HOUSING MATERIAL : HIGH TEMP PLASTIC
- 2 TERMINAL MATERIAL : BeCu.
- 3 TERMINAL RETENTION 0.5Kg/1.1 Lbs.

④ 'V' CUT OPTIONAL - MANUFACTURING PROCESS OPTION.

⚠ ⑤ SOLDER TAIL PLATING:
a) SOLDER TAIL OF P/N: 92911 - XXX IS TIN/LEAD PLATED.
b) SOLDER TAIL OF P/N: 92911 - XXXLF IS GOLD FLASH PLATED.

6 PRODUCT DESCRIPTION CODE:



⑦ PACKAGING :
(a) XXXXX-XXX --- STD PACKAGING IN TUBE.
(b) XXXXX-XXXTR --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITH PICK-UP CAP (SEE FIG 1).
(c) XXXXX-XXXTRN --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITHOUT PICK-UP CAP.
(d) XXXXX-XXXCR --- TAPE AND REEL (NON-CONDUCTIVE) PACKAGING WITH PICK-UP CAP (SEE FIG 1).
(e) XXXXX-XXXCRN --- TAPE AND REEL (NON-CONDUCTIVE) PACKAGING WITHOUT PICK-UP CAP.

8 THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

⑨ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

⚠ ⑩ A ⚠ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

										CONFIDENTIAL		
www.fciconnect.com				surface		-	tolerance std		projection	MM / INCH		
				ISO 1302		✓	ISO 406 ISO 1101					
				TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	BS LOW	2000-01-06	ANGULAR	LINEAR	X.X/.XX		±0.3/.01		size	Scale		
Eng	BS LOW	2000-01-06			X.XX/.XXX		±0.13/.005		A3	10:1		
Chr	KH LEE	2010-06-28			0°	±2°	X.XXX/.XXXX		±0.051/.0020		ECN	S10-0136
Appr	JOEY NG	2010-06-28	Product family				LPVCC		Spec ref	-		
			title	LOW PROFILE VCC SMT 3.00 ASSY					dwg no	92911	Rev.	
				WITH 0.46/.018 LOCATING FEATURES								
				catalog no								
					-					CUSTOMER		sheet 3 of 3

CONFIDENTIAL

1

2

3

PDM: Rev:P

STATUS: Released

Printed: Nov 27, 2010