



PRODUCT NUMBER
65039-YXX(E)LF

DESIGN CODE _____
0 = STANDARD
2 = OPTIONAL RIB
SEE SHEET 2

PIN STYLE _____
SEE SHEET 2

INDICATES THE PRODUCT IS RoHS
COMPLIANT, SEE NOTE 6

65039-YXXLF OR 65039-YXXELF ARE
EXACTLY THE SAME PRODUCTS.
EXTENSION "E" JUST FOR OLD EUROPEAN
DESIGN AND MANUFACTURING SITE



NOTES:


1. MOLDING MATERIAL : MODIFIED POLYPHENYLENE
COLOR BLACK, UL 94 VO
2. LATCH MUST WITHSTAND 18N MIN PULL OUT FORCE
3. STANDARD PACKAGING IN POLYBAGS
4. TERMINALS MUST BE CRIMPED PROPERLY FOR
SATISFACTORY LATCHING :
- FOR CRIMPING INSTRUCTIONS, SEE TA-75 AND TA-295
- FOR TERMINAL APPLICATION SEE TA-531.

PRODUCT SPECIFICATION: BUS-12-067.

5. THIS HOUSING IS INTENDED FOR USE WITH
MINI PV TERMINAL WITH 22-36 GAUGE WIRE

6. RoHs COMPLIANT PRODUCT SPECIFICATIONS :

- MEETS PACKAGING SPECS AS PER GS-14-920
- PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.



PRELIMINARY

mat'l. code SEE NOTES				surface	tolerance	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified			BERCONN
BE	V07-0483	HTB	07.07.24	ISO 1302	✓ ISO 406 ISO 1101		
BF	F12-0064	LMU	12.06.08	angles	.X ±0.3	mm	
BG	B-14321	LMU	13.03.21	linear	.XX ±0.13		
					.XXX ±0.05	scale 5:1	
BH	B-18693	LMU	14.08.29	dr	L.MULIN	12.06.08	
				engn	L.MULIN	12.06.08	
				chr			
				oppd	JCO	12.06.08	
sheet	revision	BH	BG				
index	sheet	1	2				

FCI

Copyright FCI

title
MINI LATCH SR
POLARIZED HSG 2.54mm

dwg no
65039


sheet 1 of 2

size
A3

type
CUSTOMER

Drawing

PIN STYLE	No. OF POS.	DIM J	DIM K
36	1x01	N/A	2.39
35	1x02	2.54	4.93
34	1x03	5.08	7.47
33	1x04	7.62	10.01
32	1x05	10.16	12.55
31	1x06	12.70	15.09
30	1x07	15.24	17.63
29	1x08	17.78	20.17
28	1x09	20.32	22.71
27	1x10	22.86	25.25
26	1x11	25.40	27.79
25	1x12	27.94	30.33
24	1x13	30.48	32.87
23	1x14	33.02	35.41
22	1x15	35.56	37.95
21	1x16	38.10	40.49
20	1x17	40.64	43.03
19	1x18	43.18	45.57
18	1x19	45.72	48.11
17	1x20	48.26	50.65
16	1x21	50.80	53.19
15	1x22	53.34	55.73
14	1x23	55.88	58.27
13	1x24	58.42	60.81
12	1x25	60.96	63.35
11	1x26	63.50	65.89
10	1x27	66.04	68.43
09	1x28	68.58	70.97
08	1x29	71.12	73.51
07	1x30	73.66	76.05
06	1x31	76.20	78.59
05	1x32	78.74	81.13
04	1x33	81.28	83.67
03	1x34	83.82	86.21
02	1x35	86.36	88.75
01	1x36	88.90	91.29



PRELIMINARY

mat'l. code				surface	tolerance	projection	product family
ISO 1302	✓	ISO 406	ISO 1101	tolerances unless otherwise specified			BERCONN
ltr	ecn no	dr	date	angles	linear	mm	title
BE	Y07-0483	HTB	07.07.24	.x ±0.3	.xx ±0.13	scale 5:1	MINI LATCH SR
BF	F12-0064	LMU	12.06.08		.xxx ±0.05		POLARIZED HSG 2.54mm
BG	B-18693	LMU	14.08.29	dr	L.MULIN	dwg no	65039
				engn	L.MULIN	sheet 2 of	A3
				chr		size	
				oppd	JCO	type	CUSTOMER
sheet	revision					Drawing	
index	sheet						



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[65039-003LF](#)