






Copyright FCI.

PRODUCT NUMBER
70430-XYX
70430-XYXLF



PLATING IN CONTACT AREA


DASH NUMBER	PERFORMANCE LEVEL
-1YY	TELCORDIA CO & IEC CLASS I
-2YY	TELECOM CLASS
-3YY	TELCORDIA CO & IEC CLASS I
-5YY	TELCORDIA UE
-1YYLF	TELCORDIA CO & IEC CLASS I
-2YYLF	TELECOM CLASS
-5YYLF	TELCORDIA UE



NOTES:

- FOR DIM A, AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL
PHOSPHOR BRONZE:
- PLATING ON PRESS-FIT TAIL:
70430-XYX IS SnPb
70430-XYXLF IS Sn (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
PART NUMBER DESIGNATION J& BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES. IF TRAY PACKAGING IS REQUIRED, SUFFIX "P" WILL BE ADDED TO THE END OF THE PART NUMBER. EXAMPLE: XXXXX-XXXP
- PRODUCT SPECIFICATION: GS-12-180
APPLICATION SPECIFICATION: BUS-20-075
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN 'LF' MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

rev	ecn no	dr	date
AW	DG-006740-1	TER	2011-10-08
AR	V06-0948	DCH	2006-09-12
AS	DG09-0256	TER	2009-08-19
AT	DG09-0366	TER	2009-11-24
AU	DG10-0002	TER	2010-01-05
AV	DG-003807-1	TER	2011-05-11

spec ref		*		dr	Terran Huang	2010/07/08	projection 	mm 	size	A4	scale	11:10
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Terran Huang	2011/10/09			ecn no	ELX-DG-006740-1		
				chr	Tao Huang	2011/10/18			rel level			Released
				appr	Pei-Ming Zheng	2011/10/18	product family		METRAL			
surface	3.200 linear	0.X	±0.3		title METRAL POWER HEADER 1 MOD, 5 ROW PRESS-FIT			dwg no	70430		rev AV	
		0.XX	±0.13									
		0.XXX	±0.051									
		angular	0°	±2°	www.fci.com	cat. no.		-		Product - Customer Drw		sheet 1 of 6

Print File - REV C - 2009-06-09


PDS: Rev :AW

STATUS:Released

Printed: Oct 18, 2011



Copyright FCI.



KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
P01	6.50	4.30
P02	7.25	4.30
P03	8.00	4.30
P04	6.50	13.60
P05	7.25	13.60
P06	8.00	13.60
P07	6.5	17.00
P08	7.25	17.00
P11	7.25	12.20
P12	8.00	12.20
P16	5.00	4.30
P17	5.75	4.30
P29	7.25	11.80

REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

spec ref		*		dr	Terran Huang	2010/07/08	projection	mm	size	A4	scale	21:10		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Terran Huang	2011/10/09			ecn no	ELX-DG-006740-1				
				chr	Tao Huang	2011/10/18								
				appr	Pei-Ming Zheng	2011/10/18								
product family							METRAL		rel level		Released			
surface	3.200 linear	0.X	±0.3		title	METRAL POWER HEADER				dwg no	70430		rev	AV
		0.XX	±0.13											
		0.XXX	±0.051											
	angular	0°	±2°											

Prof/E File - REV C - 2009-06-09



Copyright FCI.

A

B

C

D

METRAL P/N	ROW	CONTACT CODE MOD. I	
		I	2
70430-X21 SEE NOTE 4 FOR LEAD-FREE CODE	E	P02	P02
	D	P02	P02
	C	P02	P02
	B	P02	P02
	A	P03	P03

METRAL P/N	ROW	CONTACT CODE MOD. I	
		I	2
70430-X22 SEE NOTE 4 FOR LEAD-FREE CODE	E	P06	P06
	D	P06	P06
	C	P06	P05
	B	P06	P05
	A	P06	P06

METRAL P/N	ROW	CONTACT CODE MOD. I	
		I	2
70430-X23 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P03
	D	P03	P03
	C	P03	P02
	B	P03	P02
	A	P03	P03

METRAL P/N	ROW	CONTACT CODE MOD. I	
		I	2
70430-X24 SEE NOTE 4 FOR LEAD-FREE CODE	E	P01	P03
	D	P01	P03
	C	P01	P03
	B	P01	P03
	A	P01	P03

spec ref	*	dr	Terran Huang	2010/07/08	projection	mm	size	A4	scale	1:10
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Terran Huang	2011/10/09			ecn no	ELX-DG-006740-1		
		chr	Tao Huang	2011/10/18			rel level	Released		
		appr	Pei-Ming Zheng	2011/10/18	product family	METRAL				
surface	3.200 linear			title		METRAL POWER HEADER		dwg no		70430
	0.X									
	0.XX									
	0.XXX			I MOD, 5 ROW PRESS-FIT		Product - Customer Drw		sheet 4 of 6		rev
	angular									
	0°	www.fci.com		cat. no.						AW
	±0.3									
	±0.13									
	±0.051									
	±2°									



Copyright FCI.




Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2			1	2
70430-X61 SEE NOTE 4 FOR LEAD-FREE CODE	E	P01	P01	70430-X65 SEE NOTE 4 FOR LEAD-FREE CODE	E	P02	P01
	D	P01	P01		D	P02	P02
	C	P01	P01		C	P02	P02
	B	P01	P01		B	P02	P02
	A	-	-		A	P02	P02

METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2			1	2
70430-X62 SEE NOTE 4 FOR LEAD-FREE CODE	E	P01	P01	70430-X66 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P01
	D	P01	P01		D	P03	P01
	C	P01	P03		C	P03	P03
	B	P01	P01		B	P03	P03
	A	P01	P01		A	P03	P03

METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2			1	2
70430-X63 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P02	70430-X67 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P01
	D	P03	P02		D	P03	P03
	C	P03	P03		C	P02	P02
	B	P03	P03		B	P02	P02
	A	P03	P03		A	P02	P02

METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2			1	2
70430-X64 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P01	70430-X68 SEE NOTE 4 FOR LEAD-FREE CODE	E	P01	P03
	D	P03	P03		D	P03	P03
	C	P03	P02		C	P02	P03
	B	P03	P02		B	P02	P03
	A	P03	P02		A	P02	P03

spec ref *				dr Terran Huang 2010/07/08		projection 	mm 	size A4	scale 11:10	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Terran Huang 2011/10/09				ecn no ELX-DG-006740-1		
				chr Tao Huang 2011/10/18				rel level Released		
				appr Pei-Ming Zheng 2011/10/18				product family METRAL		
surface 3.200 linear 	linear	0.X	±0.3		title METRAL POWER HEADER 1 MOD, 5 ROW PRESS-FIT	dwg no 70430	rev AV			
		0.XX	±0.13							
		0.XXX	±0.051							
	angular	0°	±2°	www.fci.com	cat. no.					-