


TO-3PN

Pin Definition:

1. Gate
2. Collector
3. Emitter



PRODUCT SUMMARY

V_{CES} (V)	V_{GES} (V)	I_C (A)
1200	± 20	25

General Description

The TSG25N120CN using proprietary trench design and advanced NPT technology, the 1200V NPT IGBT offers superior conduction and switching performances, high avalanche ruggedness and easy parallel operation. This device is well suited for the resonant or soft switching application such as induction heating, microwave oven, etc.


Features

- 1200V NPT Trench Technology
- High Speed Switching
- Low Conduction Loss

Ordering Information

Part No.	Package	Packing
TSG25N120CN C0	TO-3PN	30pcs / Tube

Block Diagram



NPT Trench IGBT

Absolute Maximum Rating ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Limit	Unit
Collector-Emitter Voltage	V_{CES}	1200	V
Gate-Emitter Voltage	V_{GES}	± 20	V
Continuous Current	I_C	$T_C=25^\circ\text{C}$ 50	A
		$T_C=100^\circ\text{C}$ 25	A
Pulsed Collector Current *	I_{CM}	75	A
Diode Forward Current ($T_C=100^\circ\text{C}$)	I_F	25	A
Diode Pulse Forward Current	I_{FM}	75	A
Max Power Dissipation	P_D	$T_J=25^\circ\text{C}$ 312	W
		$T_J=100^\circ\text{C}$ 125	
Operating Junction Temperature	T_J	-55 to +150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 to +150	$^\circ\text{C}$

* Repetitive rating: Pulse width limited by max. junction temperature

Thermal Performance

Parameter		Symbol	Limit	Unit
Thermal Resistance - Junction to Case	IGBT	$R\theta_{JC}$	0.4	$^{\circ}\text{C/W}$
	DIODE		2.2	
Thermal Resistance - Junction to Ambient		$R\theta_{JA}$	40	

Electrical Specifications (T_c=25 $^{\circ}\text{C}$ unless otherwise noted)

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Static						
Collector-Emitter Breakdown Voltage	$V_{GE} = 0V, I_C = 1mA$	BV_{CES}	1200	--	--	V
Zero Gate Voltage Collector Current	$V_{CE} = 1200V, V_{GE} = 0V$	I_{CES}	--	--	1	mA
Gate-Emitter Leakage Current	$V_{GE} = 20V, V_{CE} = 0V$	I_{GES}	--	--	±250	nA
Gate-Emitter Threshold Voltage	$V_{GE} = V_{CE}, I_C = 25mA$	$V_{GE(TH)}$	3.0	5.0	7.0	V
Collector-Emitter Saturation Voltage	$V_{GE} = 15V, I_C = 25A, T_J = 25^{\circ}C$	$V_{CE(SAT)}$	--	1.9	2.5	V
	$V_{GE} = 15V, I_C = 25A, T_J = 125^{\circ}C$	$V_{CE(SAT)}$	--	2.2	--	V
Dynamic						
Input Capacitance	$V_{CE} = 30V, V_{GE} = 0V,$ $f = 1.0MHz$	C_{IES}	--	4000	--	pF
Output Capacitance		C_{OES}	--	105	--	
Reverse Transfer Capacitance		C_{RES}	--	72	--	
Switching						
Turn-On Delay Time	$V_{CC} = 600V, I_C = 25A,$ $R_G = 10\Omega, V_{GE} = 15V$ Inductive Load, $T_J = 25^{\circ}C$	$t_{d(on)}$	--	57	--	nS
Rise Time		t_r	--	65	--	
Turn-Off Delay Time		$t_{d(off)}$	--	240	--	
Fall Time		t_f	--	86	160	
Turn-On Switching Loss		E_{on}	--	4.15	6.22	mJ
Turn-Off Switching Loss		E_{off}	--	0.87	1.31	
Total Switching Loss		E_{ts}	--	5.02	7.53	
Turn-On Delay Time	$V_{CC} = 600V, I_C = 25A,$ $R_G = 10\Omega, V_{GE} = 15V$ Inductive Load, $T_J = 125^{\circ}C$	$t_{d(on)}$	--	41	--	nS
Rise Time		t_r	--	57	--	
Turn-Off Delay Time		$t_{d(off)}$	--	265	--	
Fall Time		t_f	--	168	--	
Turn-On Switching Loss		E_{on}	--	4.46	6.69	mJ
Turn-Off Switching Loss		E_{off}	--	1.74	2.61	
Total Switching Loss		E_{ts}	--	6.2	9.3	
Total Gate Charge	$V_{CC} = 600V, I_C = 25A,$ $V_{GE} = 15V$	Q_g	--	170	255	nC
Gate-Emitter Charge		Q_{ge}	--	27	41	
Gate-Collector Charge		Q_{gc}	--	60	90	


Electrical Specifications of the DIODE (Tc=25°C unless otherwise noted)

Parameter	Conditions		Symbol	Min	Typ	Max	Unit
Diode Forward Voltage	I _F = 25A,	T _J =25 ^o C	V _{FM}	--	2.0	2.5	V
		T _J =125 ^o C		--	2.18	--	V
Reverse Recovery Time	I _F = 25A, dI/dt=200A/us	T _J =25 ^o C	t _{fr}	--	300	480	ns
		T _J =125 ^o C		--	360	--	
T _J =25 ^o C		I _{fr}	--	27	41	A	
T _J =125 ^o C			--	31	--		
Reverse Recovery Charge		T _J =25 ^o C	Q _{fr}	--	4000	6000	nC
		T _J =125 ^o C		--	5580	--	


Not Recommended

Electrical Characteristics Curve ($T_c = 25^\circ\text{C}$, unless otherwise noted)


Output Characteristics




Saturation voltage characteristics




Saturation voltage vs. collector current




Saturation voltage vs. gate bias



Saturation voltage vs. gate bias




Capacitance characteristics




Electrical Characteristics Curve (Ta = 25°C, unless otherwise noted)


Turn on time vs. gate resistance




Turn off time vs. gate resistance




Switching loss vs. gate resistance




Turn on time vs. collector current



Turn off time vs. collector current




Switching loss vs. collector current




Electrical Characteristics Curve (Tc = 25°C, unless otherwise noted)


Gate charge characteristics




SOA Characteristics




RBSOA




Conduction characteristics



Reverse recovery current vs. forward current




Stored recovery charge vs. forward current




Electrical Characteristics Curve ($T_a = 25^\circ\text{C}$, unless otherwise noted)


Reverse recovery time vs. forward current



Normalized Thermal Transient Impedance, Junction-to-Ambient



TO-3PN Mechanical Drawing



Unit: Millimeters

Not Recommended

Not Recommended

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.