

Features

- Low Loss
- Excellent Return Loss
- High Rejection


Description

Surface mount, silver (Ag) coated ceramic filter. Developed for use in TCAS applications.

Weight: 11.96 grams typical

Material: Filter is composed of a ceramic block plated with Ag.

Filter complies with RoHS standards.


**Electrical Specifications**

Parameter	Frequency (MHz)	Typical @ 25°C	Spec. @ 25°C
Passband Insertion Loss	1020-1040	2.4 dB	3.0 dB max
Passband Return Loss	1020-1040	15.0 dB	12.0 dB min
Attenuation	990	37.0 dB	32.0 dB min
	1060	40.0 dB	32.0 dB min

Note: Supplier shall test each filter to the critical electrical specifications of the above table. Any subsequent audits may deviate from in value due to measurement repeatability among different test systems. Such deviations shall not exceed the following limits:


Specification Allowance	
Insertion Loss	0.1 dB
Return Loss	1.0 dB
Stopbands	1.0 dB

Mechanical Drawing




Dim	Nominal (mm)	Tolerance (mm) +/- or max
A	33.580	max
B	11.252	max
C	7.850	max
D	10.808	0.127
E	10.808	0.127
F	2.616	0.127
G	0.635	0.127
I	2.032	0.127
J	0.635	0.127

Electrical response



PCB Layout



Packaging and Marking

This product is shipped in pre-formed foam trays.

