DATA SHEET

BF510 to 513
N-channel silicon field-effect transistors

Product specification

December 1997

N-channel silicon field-effect transistors BF510 to 513

DESCRIPTION

Asymmetrical N-channel planar epitaxial junction field-effect transistors in the miniature plastic envelope intended for applications up to the v.h.f. range in hybrid thick and thin-film circuits. Special features are the low feedback capacitance and the low noise figure. These features make the product very suitable for applications such as the r.f. stages in f.m. portables (BF510), car radios (BF511) and mains radios (BF512) or the mixer stage (BF513).

PINNING - SOT23

1 = gate
2 = drain
3 = source

MARKING CODE

BF510 = S6p
BF511 = S7p
BF512 = S8p
BF513 = S9p



Fig.1 Simplified outline and symbol.

QUICK REFERENCE DATA

Drain-source voltage	V_{DS}	max.		20			V
Drain current (DC or average)	I_D	max.		30			mA
Total power dissipation							
up to T_{amb} = 40 °C	P_{tot}	max.		250			mW
			BF510	**511**	**512**	**513**	
Drain current		>	0.7	2.5	6	10	mA
V_{DS} = 10 V; V_{GS} = 0	I_{DSS}	<	3.0	7.0	12	18	mA
Transfer admittance (common source)							
V_{DS} = 10 V; V_{GS} = 0; f = 1 kHz	$\lvert y_{fs} \rvert$	>	2.5	4	6	7	mS
Feedback capacitance							
V_{DS} = 10 V; V_{GS} = 0	C_{rs}	typ.	0.3	0.3	–	–	pF
V_{DS} = 10 V; I_D = 5 mA	C_{rs}	typ.	–	–	0.3	0.3	pF
Noise figure at optimum source admittance							
G_S = 1 mS; $-B_S$ = 3 mS; f = 100 MHz							
V_{DS} = 10 V; V_{GS} = 0	F	typ.	1.5	1.5	–	–	dB
V_{DS} = 10 V; I_D = 5 mA	F	typ.	–	–	1.5	1.5	dB

RATINGS

Limiting values in accordance with the Absolute Maximum System (IEC 134)

Drain-source voltage	V_{DS}	max.	20	V
Drain-gate voltage (open source)	V_{DGO}	max.	20	V
Drain current (DC or average)	I_D	max.	30	mA
Gate current	$\pm I_G$	max.	10	mA
Total power dissipation up to T_{amb} = 40 °C (note 1)	P_{tot}	max.	250	mW
Storage temperature range	T_{stg}	−65 to +	150	°C
Junction temperature	T_j	max.	150	°C

THERMAL RESISTANCE

From junction to ambient (note 1)	$R_{th\ j\text{-}a}$	=	430	K/W

Note

1. Mounted on a ceramic substrate of 8 mm × 10 mm × 0.7 mm.

STATIC CHARACTERISTICS

T_{amb} = 25 °C

			BF510	511	512	513	
Gate cut-off current							
$-V_{GS}$ = 0.2 V; V_{DS} = 0	$-I_{GSS}$	<	10	10	10	10	nA
Gate-drain breakdown voltage							
I_S = 0; $-I_D$ = 10 μA	$-V_{(BR)GDO}$	>	20	20	20	20	V
Drain current							
V_{DS} = 10 V; V_{GS} = 0	I_{DSS}	>	0.7	2.5	6	10	mA
		<	3.0	7.0	12	18	mA
Gate-source cut-off voltage							
I_D = 10 μA; V_{DS} = 10 V	$-V_{(P)GS}$	typ.	0.8	1.5	2.2	3	V

DYNAMIC CHARACTERISTICS

Measuring conditions (common source): V_{DS} = 10 V; V_{GS} = 0; T_{amb} = 25 °C for BF510 and BF511
V_{DS} = 10 V; I_D = 5 mA; T_{amb} = 25 °C for BF512 and BF513

y-parameters (common source)			BF510	511	512	513	
Input capacitance at f = 1 MHz	C_{is}	<	5	5	5	5	pF
Input conductance at f = 100 MHz	g_{is}	typ.	100	90	60	50	μS
Feedback capacitance at f = 1 MHz	C_{rs}	typ.	0.4	0.4	0.4	0.4	pF
		<	0.5	0.5	0.5	0.5	pF
Transfer admittance at f = 1 kHz	$\lvert y_{fs} \rvert$	>	2.5	4.0	4.0	3.5	mS
V_{GS} = 0 instead of I_D = 5 mA	$\lvert y_{fs} \rvert$	>	–	–	6.0	7.0	mS
Transfer admittance at f = 100 MHz	$\lvert y_{fs} \rvert$	typ.	3.5	5.5	5.0	5.0	mS
Output capacitance at f = 1 MHz	C_{os}	<	3	3	3	3	pF
Output conductance at f = 1 MHz	g_{os}	<	60	80	100	120	μS
Output conductance at f = 100 MHz	g_{os}	typ.	35	55	70	90	μS
Noise figure at optimum source admittance G_S = 1 mS; $-B_S$ = 3 mS; f = 100 MHz	F	typ.	1.5	1.5	1.5	1.5	dB



Fig.2 V_{GS} = 0 for BF510 and BF511; I_D = 5 mA for BF512 and BF513; f = 1 MHz; T_{amb} = 25 °C.



Fig.3 V_{DS} = 10 V; f = 1 kHz; T_{amb} = 25 °C; typical values.



Fig.4 Power derating curve.

PACKAGE OUTLINE

Plastic surface-mounted package; 3 leads **SOT23**



DIMENSIONS (mm are the original dimensions)

UNIT	A	A_1 max.	b_p	c	D	E	e	e_1	H_E	L_p	Q	v	w
mm	1.1 0.9	0.1	0.48 0.38	0.15 0.09	3.0 2.8	1.4 1.2	1.9	0.95	2.5 2.1	0.45 0.15	0.55 0.45	0.2	0.1

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT23		TO-236AB				~~04-11-04~~ 06-03-16

DATA SHEET STATUS

DOCUMENT STATUS[1]	PRODUCT STATUS[2]	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

Notes

1. Please consult the most recently issued document before initiating or completing a design.
2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

DEFINITIONS

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

DISCLAIMERS

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

NXP Semiconductors

provides High Performance Mixed Signal and Standard Product solutions that leverage its leading RF, Analog, Power Management, Interface, Security and Digital Processing expertise

Customer notification

This data sheet was changed to reflect the new company name NXP Semiconductors, including new legal definitions and disclaimers. No changes were made to the technical content, except for package outline drawings which were updated to the latest version.

Contact information

For additional information please visit: **http://www.nxp.com**
For sales offices addresses send e-mail to: **salesaddresses@nxp.com**

Printed in The Netherlands R77/02/pp9 Date of release: December 1997