




Features

- For use with Analog Device's AD20msp930 ADSL chipsets
- Excellent Total Harmonic Distortion (THD) performance
- Thru-hole package and small size
- Designed to meet UL1950 and EN60950 supplementary insulation requirements for operating voltages up to 250 Vrms

- Operating temperature -40 °C to +85 °C
- Lead free version available (see How to Order)
- Lead free versions are RoHS compliant*

Applications

- ADSL - Analog AD20msp930

PT563-1 & PT564-1 ADSL Line Transformers



Electrical Specifications @ 25 °C

Turns Ratio (1-4):(10-7)	
PT563-1	1:1.1 ±2 %
PT564-1	1:1.2 ±2 %
OCL @ 10 kHz, 0.1 V	
(1-4) with (2-3) shorted	
PT563-1	1.75 mH min.
PT564-1	1.75 mH min.
(10-7) with (8-9) shorted	
PT563-1	2.03 mH min.
PT564-1	2.42 mH min.
Leakage Inductance @ 100 kHz 0.1 V	
(1-4) with (2-3), (8-9), (10-7) shorted	
.....	7.5 µH max.
Longitudinal Balance	
10 kHz to 1.1 MHz	50 dB min.
Insertion Loss @ 300 kHz	
.....	< 0.5 dB
Isolation Voltage	
.....	
DC Resistance	
(1-4)	1.5 Ω max.
(10-7)	1.3 Ω max.
THD Linearity @ 30 kHz	
.....	-80 dB typ.
Application	
PT563-1	CO
PT564-1	CPE

Packaging Specifications

Tray60 pcs./tray


Product Dimensions



DIMENSIONS ARE: $\frac{\text{MM}}{(\text{INCHES})}$

TOLERANCE: $\pm \frac{0.25}{(.010)}$

Electrical Schematic



How to Order

Model **PT56x-1**

Termination _____

Blank = Tin-lead
L = Tin only (lead free)