

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19193-0198

Status:

Active

Overview:

VersaKrimp™ Terminals and Splices

Description:

VersaKrimp™ Ring Tongue Terminal for 8 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19193
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	VersaKrimp™ Terminals and Splices
Product Name	VersaKrimp™
Type	Ring
UPC	800755050530

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.972/g
Packaging Type	Bag
Stud Size	6 (M3.5)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	8
Wire Size mm²	0.60 - 10.5

Material Info

Old Part Number	D-356-06
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19193-012




image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19193Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hydraulic Dieless Crimping Tool	0638161700
Hand Crimp Tool RHT1080 Hand Crimp Tool	0640013900
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640034400
Manual Putt Pump Hydraulic System, Die set required	0640074400
Die Set (large) for the HHLS Hydraulic Crimper	0192860117
	0192900001

This document was generated on 12/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION