





MATERIAL NO.	NUMBER OF CIRCUITS "XX"	DIM. "A" ±.13 (.010)	DIM. "B"
39920-0102	02	29.21 (1.15)	15.01 (.591)
39920-0103	03	44.20 (1.74)	30.00 (1.181)
39920-0104	04	59.18 (2.33)	45.01 (1.772)
39920-0105	05	74.17 (2.92)	59.99 (2.362)
39920-0106	06	89.15 (3.51)	75.01 (2.953)
39920-0107	07	104.14 (4.10)	89.99 (3.543)
39920-0108	08	119.13 (4.69)	105.00 (4.134)
39920-0109	09	134.11 (5.28)	119.99 (4.724)
39920-0110	10	149.10 (5.87)	135.00 (5.315)
39920-0111	11	164.34 (6.47)	150.01 (5.906)
39920-0112	12	179.32 (7.06)	165.00 (6.496)



M5 COMBO HEAD SCREW, 6.35 (1/4) BLADE, #2 POZI



ACTUAL SIZE



NOTES:

1. MATERIAL: SEE TABLE.
2. FINISHES: SEE TABLE.
3. PRODUCT SPECIFICATION: NOT REQUIRED.
4. PACKAGING: NOT REQUIRED.
5. MATES WITH: NONE.
6. ALL FEATURES ARE TYPICAL UNLESS OTHERWISE NOTED.
7. DESIGNED TO MEET NEC & UL 1059 CLASS C 600 VOLTS.
8. "XX" REFERS TO THE NUMBER OF CIRCUIT POSITIONS.

6	XX	SCREW, M5, POZI-SLOT	BRONZE	TIN
5	XX	TERMINAL	COPPER	TIN
4	XX	TERMINAL	COPPER	TIN
3	XX	CAGE	BRASS	NICKEL
2	1	COVER	THERMOPLASTIC	BLACK
1	1	BODY	THERMOPLASTIC	BLACK
ITEM	BQTY.	DESCRIPTION	MATERIAL	FINISH

EC NO. 11485	DRWN: RK 6-15-04
CH: K	APPR:
G	

DESCRIPTION	QUALITY SYMBOLS
MAJOR	=
CRITICAL	=
REV	

GENERAL TOLERANCES: (UNLESS SPECIFIED)	SCALE 3:2	DESIGN UNITS ☐ mm ☒ INCH
4 PLACES	mm	INCH
3 PLACES	±.038	±.0015
2 PLACES	±.13	±.01
1 PLACE	±.3	
ANGULAR:	±2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DRAWN BY & DATE GHR 2-3-00	CHECKED BY & DATE R. KEMP 12-11-00
APPROVED BY & DATE L. ROTHBAUS 5-10-01	CAD FILENAME 9205XX
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	

PROJECT NO. E-537	SHT	REV
DIMENSIONS: ☒ mm ☐ INCH ☐ mm ONLY	REVISE ON CAD ONLY	
TITLE: SR, BTS, #3 AWG, 85A, 600V		
MOLEX INCORPORATED		
MATERIAL NO. SEE CHART	DRAWING NO. SD-39920-005	SHEET NO. 1 OF 1
		SIZE B