





LOC	DIST	REVISIONS					
CM	54	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H2	REVISED PER ECO-14-011424	23SEP14	MGM	CO



RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD 



.050	1.27	.500	12.70
.040	1.02	.310	7.87
.035	0.89	.295	7.49
.032	0.81	.225	5.72
.025	0.64	.200	5.08
.020	0.51	.160	4.06
.015	0.38	.140	3.56
.010	0.25	.125	3.18
.008	0.20	.120	3.05
.005	0.13	.110	2.79
.003	0.08	.100	2.54
.001	0.03	.063	1.60
IN	MM	IN	MM

CONVERSION TABLE

643599-2 SHOWN	OBSOLETE	3	-643599-2
		2	643599-1
		POST NUMBER OMITTED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 2-23-93 L. SMITH CHK 2-23-93 R. SWING		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± .— 1 PLC ± .— 2 PLC ± .— 3 PLC ± .005 4 PLCS ± .— ANGLES ± .030°		NAME MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE RIGHT ANGLE POST, TIN PLATED, 5 POSITION, OMITTED POST	
		APVD 3-11-93 R. SOPER PRODUCT SPEC — APPLICATION SPEC —		SIZE CASE CODE DRAWING NO A1 00779 C-643599	
MATERIAL 		FINISH 		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 8:1 SHEET 1 OF 1 REV H	