





| O.P. (MM)  | P.T. (MM) |
|------------|-----------|
| 14.7 ± 0.5 | 2.0 MAX.  |

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



## NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=± 0.4  
X.XX=± 0.25
- RATING: 15A @125/250VAC UL, CUL, VDE APPROVED
- OPERATING FORCE: 100± 30 GRAMS
- OPERATING TEMP: -25°C TO 85°C
- ELECTRICAL LIFE: 50,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES TYP.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
- CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT



|     |        |                         |          |    |
|-----|--------|-------------------------|----------|----|
| C   | 15738  | EDIT CIRCUIT DRAWING    | 2/7/06   | PH |
| B   | 15693  | EDIT TERMINAL           | 1/18/06  | PH |
| A   | 15611  | RELEASED FOR PRODUCTION | 12/16/05 | PH |
| REV | PCR NO | DESCRIPTION             | DATE     | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

**E-SWITCH®**

TITLE LS0851500F100C2C

SCALE 1.5:1

DATE 12/16/2005

DR PH

DWG Q950027

REV C