

13	12	11	10	9	8	7	6	5	4	3	2	1																																																																																	
MATERIAL NUMBER 1300390341		OLD PART NUMBER DND3020																																																																																											
SCHEMATIC																																																																																													
VOLTAGE RATING		250 VAC/VDC																																																																																											
AMPERAGE RATING		4 AMPS																																																																																											
PROTECTION		IP67																																																																																											
OPERATING TEMPERATURE		-20°C TO 80°C																																																																																											
UL CERTIFICATIONS		UL RECOGNIZED, FILE NO. E152210																																																																																											
CSA CERTIFICATIONS		CSA CERTIFIED, FILE NO. LR6837																																																																																											
<table><tr><th>ITEM</th><th>COMPONENT</th><th>MATERIAL</th><th>FINISH</th></tr><tr><td>1</td><td>INSERT</td><td>TPE</td><td>GRAY</td></tr><tr><td>2</td><td>CONTACT SOCKET</td><td>COPPER ALLOY</td><td>GOLD OVER NICKEL</td></tr><tr><td>3</td><td>CONTACT PIN</td><td>COPPER ALLOY</td><td>GOLD OVER NICKEL</td></tr><tr><td>4</td><td>COUPLING NUT</td><td>ZINC DIE CAST</td><td>BLACK E-COATED</td></tr><tr><td>5</td><td>OVERMOLD</td><td>TPE</td><td>GRAY</td></tr><tr><td>6</td><td>INSERT</td><td>NYLON 6/6</td><td>BLACK</td></tr></table>				ITEM	COMPONENT	MATERIAL	FINISH	1	INSERT	TPE	GRAY	2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL	3	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL	4	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED	5	OVERMOLD	TPE	GRAY	6	INSERT	NYLON 6/6	BLACK	<table><tr><td rowspan="4">REV'D MAT NO IN TITLE BLOCK EC NO: IPG2013-1735 DRWN: RSTONE 2013/05/10 CH'KD: BW APPR: BWOODMAN B</td><td rowspan="4">QUALITY SYMBOL =0 =0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE IN/MM</td><td>SCALE ---</td><td>DESIGN UNITS INCH</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td>4 PLACES</td><td>mm</td><td>INCH</td><td>DRAWN BY RSTONE</td><td>DATE 2013/05/10</td><td colspan="4" rowspan="2">TITLE MINI-CHANGE 5 POLE TEE DEVICENET W/M12 DROP</td></tr><tr><td>3 PLACES</td><td>mm</td><td>INCH</td><td>CHECKED BY BW</td><td>DATE 2013/05/14</td></tr><tr><td>2 PLACES</td><td>mm</td><td>INCH</td><td colspan="2">APPROVED BY ---</td><td>DATE ---</td><td colspan="4">MATERIAL NO. SEE CHART</td></tr><tr><td>1 PLACE</td><td>mm</td><td>INCH</td><td colspan="2">ANGULAR ±---°</td><td colspan="2">DOCUMENT NO. SD-130039-010</td><td colspan="2">SHEET NO. 1 OF 1</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="4"></td><td colspan="2"></td></tr></table>									REV'D MAT NO IN TITLE BLOCK EC NO: IPG2013-1735 DRWN: RSTONE 2013/05/10 CH'KD: BW APPR: BWOODMAN B	QUALITY SYMBOL =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		4 PLACES	mm	INCH	DRAWN BY RSTONE	DATE 2013/05/10	TITLE MINI-CHANGE 5 POLE TEE DEVICENET W/M12 DROP				3 PLACES	mm	INCH	CHECKED BY BW	DATE 2013/05/14	2 PLACES	mm	INCH	APPROVED BY ---		DATE ---	MATERIAL NO. SEE CHART				1 PLACE	mm	INCH	ANGULAR ±---°		DOCUMENT NO. SD-130039-010		SHEET NO. 1 OF 1		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
ITEM	COMPONENT	MATERIAL	FINISH																																																																																										
1	INSERT	TPE	GRAY																																																																																										
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL																																																																																										
3	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL																																																																																										
4	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED																																																																																										
5	OVERMOLD	TPE	GRAY																																																																																										
6	INSERT	NYLON 6/6	BLACK																																																																																										
REV'D MAT NO IN TITLE BLOCK EC NO: IPG2013-1735 DRWN: RSTONE 2013/05/10 CH'KD: BW APPR: BWOODMAN B	QUALITY SYMBOL =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION																																																																																					
		4 PLACES	mm	INCH	DRAWN BY RSTONE	DATE 2013/05/10	TITLE MINI-CHANGE 5 POLE TEE DEVICENET W/M12 DROP																																																																																						
		3 PLACES	mm	INCH	CHECKED BY BW	DATE 2013/05/14																																																																																							
		2 PLACES	mm	INCH	APPROVED BY ---		DATE ---	MATERIAL NO. SEE CHART																																																																																					
1 PLACE	mm	INCH	ANGULAR ±---°		DOCUMENT NO. SD-130039-010		SHEET NO. 1 OF 1																																																																																						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																											
13	12	11	10	9	8	7	6	5	4	3	2	1																																																																																	