





Customer Information Sheet

DRAWING No.: M22-634XX42 IF IN DOUBT - ASK © NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm



SPECIFICATIONS:
MATERIAL:
MOULDING = PA9T, UL94V-0, BLACK
CONTACT = PHOSPHOR BRONZE
FINISH:
NICKEL ALL OVER, 100% TIN ON TAILS,
GOLD FLASH ON CONTACT AREA.
ELECTRICAL:
CURRENT RATING = 2A
INSULATION RESISTANCE = 1000MΩ MIN.
CONTACT RESISTANCE = 20mΩ MAX.
VOLTAGE PROOF = 500V AC
MECHANICAL:
INSERTION FORCE = 1.96N MAX
WITHDRAWAL FORCE = 0.20N MIN.
DURABILITY = 300 CYCLES
ENVIRONMENTAL:
OPERATING TEMPERATURE = -40°C TO +105°C
PACKING:
TUBE
FOR COMPLETE MECHANICAL/ELECTRICAL SPECIFICATION,
SEE COMPONENT SPECIFICATION C018XX (LATEST ISSUE)



ORDER CODE:
M22-634XX42
No. OF CONTACTS PER ROW: 03 TO 20
FINISH: 42 = SELECTIVE GOLD + 100% TIN

MSP	16	14.08.17	20547
NAME	ISS.	DATE	C/NOTE
APPROVED:		M.PERREN	
CHECKED:		S.BENNETT	
DRAWN:		W.J.BOURNE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

NOTES:
1. COPLANARITY OF CONTACTS TO BE 0.10mm MAX.

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL: SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
2mm PITCH DIL SMT
LOW PROFILE SKT ASSEMBLY

DRAWING NUMBER:
M22-634XX42

SHT
2 OF 2