




©1959 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS				
SYM	ZONE	DESCRIPTION	DATE	APPROVAL
AC		OBSOLETE - 3 & -7 ECN D-260	9/10/74	DS
AD		REVISED ECN S4142	9-17-87	THW
AE		OBSOLETE - 8 PER ECN S4350	12-15-87	THW
AF		OBSOLETE - 1-0 PER ECN S4623	5-17-88	THW
AG		OBS - 2 & -9 PER ECN S4359	2/7/89	THW
AH		REV PER ECN BD 2619	3-20-89	THW
AJ		OBS - 4, -5 & -6 PER ECN BD 3038	10-11-89	J.T.

OBSOLETE	200331-9	.00005 MIN GOLD OVER .00003 MIN NICKEL	1-200331-0	OBSOLETE
OBSOLETE	200331-7	.00005 MIN RHOIUM OVER .00005 MIN POROUS NICKEL		
OBSOLETE	200331-6	.0001 MIN GOLD OVER .00005 MIN NICKEL		
OBSOLETE	200331-5	.000015 MIN GOLD OVER .00005 MIN NICKEL		
OBSOLETE	200331-4	.0001 MIN GOLD OVER .0001 MIN SILVER		
OBSOLETE	200331-3	.00004 MIN GOLD OVER .00003 MIN NICKEL		
OBSOLETE	200331-2	.0001 MIN SILVER OVER .00003 MIN NICKEL		
	200331-1	.00003 MIN GOLD OVER .00005 MIN NICKEL	200331-8	OBSOLETE
	PART NO.	FINISH	TAPE MTD ASSY NO	

NOTE:
1. PLATING THICKNESS TO BE MEASURED ON SURFACES ACCESSIBLE WITH 1/4 INCH DIAMETER SPHERE.
2. WIRE SIZE: 20 TO 24

QTY REQD	PART OR IDENTIFYING NO.	NOMENCLATURE OR DESCRIPTION	LIST OF MATERIALS OR PARTS LIST	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		SIGNATURE	DATE	 AMP INCORPORATED HARRISBURG, PENNSYLVANIA
FRACTIONS ± 1/64 DECIMALS ± .015 ANGLES ± 1°		DR <i>M. Smith</i>	8-21-63	
MATERIAL		CHK <i>J. Kaufman</i>	9-22-63	
SEE CALL OUT		DSGN ENGR <i>F. B. Williams Jr.</i>	8-23-63	
HEAT TREAT		APPR <i>CLC</i>	9/23/63	# 20 CONTACT SOCKET TYPE II
FINISH		DSGN APPD		
		OTHER APPD		
AMP INFO		CODE IDENT NO	SIZE	NUMBER
M 10 LOC B0331		00779	B	200331
		SCALE 10-1	WT	CALC
			ACTUAL	SHEET 1 OF 1