


C4AT, Film, Metallized Polypropylene, Power, 20 uF, 5%, 250 V, 70C, Lead Spacing = 37.5mm



Dimensions	
L	42.5mm NOM
H	37mm NOM
T	28mm NOM
S	37.5mm +/-0.4mm
S1	10.2mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

General Information	
Supplier:	KEMET
Series:	C4AT
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Switching
RoHS:	Yes
Lead:	4 Wire Leads

Specifications	
Capacitance:	20 uF
Capacitance Tolerance:	5%
Voltage DC:	250 VDC
Voltage AC:	160 VAC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Dissipation Factor:	0.05%
Max dV/dt:	20 V/us
Resistance:	3.1 mOhms (100KHz)
Current:	22 Amps (100kHz 70C), 400 Amps (Peak)

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	36

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.