



KEEP OUT ZONE

UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)
SEE NOTE 8

SEE PART NUMBER CHART
AND
PART NUMBER LOGIC
(18 HOLES PER COLUMN)

$\phi 0.10$

NOTES:

1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP)
GLASS-FILLED, UL94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
SELECTIVE TIN ON PCB TAILS.
NICKEL OVERALL.
2. FINISH: 30μ MIN GOLD IN CONTACT AREA.
3. REFER TO MOLEX PRODUCT SPECIFICATION PS-TBD FOR PERFORMANCE SPECIFICATIONS AND ADDITIONAL PCB INFORMATION.
4. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF MOLEX COSMETIC SPEC PS-45499-002.
5. PARTS PACKAGED PER PK-70873-7703.
6. MATES WITH IMPACT DC SERIES NO. 172374.
7. REFER TO MOLEX PCB ROUTING GUIDE AS-TBD FOR ANTIPAD AND ROUTING RECOMMENDATIONS.
8. *THESE DIMENSIONS REPRESENT THE AREA NEEDED TO ACCOMMODATE CONNECTOR INSERTION AND REPAIR ON THE PC BOARD. THIS IS REFERRED TO AS THE "CONNECTOR KEEP OUT ZONE" AND DOES NOT REPRESENT THE ACTUAL PERIMETER OF THE CONNECTOR. WHEN LAYING OUT A PC BOARD FOR CONNECTORS STACK TOGETHER, USE A 1.9mm PROGRESSION.*

PART NUMBER LOGIC

172375-****

MODULE TYPE
1 = UNGUIDED, TIN



P = PIN LENGTH
7 = 4.90 (SMALL COMPL. PIN 0.36±0.05 PTH)

OF COLUMNS
7 = 14 COLUMN



END WALL OPTIONS
0 = OPEN ENDS

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM 'A'	DIM 'B'
172375-1707	14	84	26.5	24.70

X - RELEASED EC NO: UCP2013-4229 DRWN: JLONG CHKD: APPR: JLONG REV	2014/01/17 2014/01/24	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
							MM ONLY		4:1	METRIC			
							DRAWN BY DATE		TITLE				
							MSANDBERG 2007/12/26		IMPACT ZX2 6 PAIR HEADER				
							CHECKED BY DATE		UNGUIDED ASSEMBLY				
							JLONG 2014/01/17		SALES DRAWING				
							APPROVED BY DATE		molex				
							JLAURX 2010/02/22						
							MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
							SEE TABLE		SD-172375-0001		1 OF 1		
			SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										



- ROW A
- ROW B
- ROW C
- ROW D
- ROW E
- ROW F
- ROW G
- ROW H
- ROW J
- ROW K
- ROW L
- ROW M
- ROW N
- ROW O
- ROW P
- ROW R
- ROW S
- ROW T




KEEP OUT ZONE

UNGUIDED BACKPLANE HOLE PATTERN (CONNECTOR SIDE) SEE NOTE 9

SEE PART NUMBER CHART AND PART NUMBER LOGIC (18 HOLES PER COLUMN)

NOTCH DESIGNATES ROW A




- NOTES:
1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP) GLASS-FILLED, UL94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
 2. FINISH: 30μ MIN GOLD IN CONTACT AREA.
SELECTIVE TIN ON PCB TAILS.
NICKEL OVERALL.
 3. REFER TO MOLEX PRODUCT SPECIFICATION PS-76060-999 FOR PERFORMANCE SPECIFICATIONS AND ADDITIONAL PCB INFORMATION.
 4. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF MOLEX COSMETIC SPEC PS-45499-002.
 5. PARTS PACKAGED PER PK-70873-7703.
 6. SEE SHEETS 2 & 3 FOR PART NUMBERS AND BOARD RELATIONSHIPS.
 7. MATES WITH IMPACT DC SERIES NO. 76150.
 8. REFER TO MOLEX PCB ROUTING GUIDE AS-76060-990 FOR ANTIPAD AND ROUTING RECOMMENDATIONS.
 9. "THESE DIMENSIONS REPRESENT THE AREA NEEDED TO ACCOMMODATE CONNECTOR INSERTION AND REPAIR ON THE PC BOARD. THIS IS REFERRED TO AS THE "CONNECTOR KEEP OUT ZONE" AND DOES NOT REPRESENT THE ACTUAL PERIMETER OF THE CONNECTOR. WHEN LAYING OUT A PC BOARD FOR CONNECTORS STACK TOGETHER, USE A 1.9mm PROGRESSION."

REVISED (MINOR) EC NO: UCP2014-0887 DRWN: BINGHAM 2013/08/25 CHKD: ILAUX 2013/08/25 APPR: ILAUX 2013/09/25 G1	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY	DATE	TITLE IMPACT 6 PAIR HEADER UNGUIDED ASSEMBLY SALES DRAWING molex DOCUMENT NO. SD-76145-001				
					4 PLACES	± ---		± ---		MSANDBERG	2007/12/26
			3 PLACES	± ---	± ---	CHECKED BY		DATE		SHEET NO. 1 OF 3	
			2 PLACES	± 0.13	± ---	JLAURX		2007/12/26			
			1 PLACE	± 0.25	± ---	APPROVED BY		DATE			
			0 PLACE	±	±	JLAURX		2010/02/22			
			ANGULAR ±1/2°		MATERIAL NO.			DOCUMENT NO.			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE						
			SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							


PART NUMBER TABLE

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM 'A'	DIM 'B'	DUAL END WALL OPTION
76145-#12*	10	60	21.7	17.10	
76145-#72*	14	84	29.3	24.70	
76145-#62*	16	96	33.1	28.50	




DUAL END
WALL OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM 'A'	DIM 'B'	LEFT END WALL OPTION
76145-#11*	10	60	20.3	17.10	
76145-#71*	14	84	27.9	24.70	
76145-#61*	16	96	31.7	28.50	




LEFT END
WALL OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM 'A'	DIM 'B'	RIGHT END WALL OPTION
76145-#13*	10	60	20.3	17.10	
76145-#73*	14	84	27.9	24.70	
76145-#63*	16	96	31.7	28.50	



RIGHT END
WALL OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM 'A'	DIM 'B'	OPEN WALL OPTION
76145-#10*	10	60	18.9	17.10	
76145-#70*	14	84	26.5	24.70	
76145-#60*	16	96	30.3	28.50	



OPEN
WALL OPTION




PART NUMBER LOGIC

76145-****

MODULE TYPE	P-PIN LENGTH
1 = UNGUIDED, TIN	3 = 4.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
	4 = 4.90 (SHORT COMPLIANT, 0.46±0.05 PTH)
	5 = 5.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
	6 = 4.50 (MICRO COMPLIANT, 0.39±0.05 PTH)
	7 = 4.90 (MICRO COMPLIANT, 0.39±0.05 PTH)
	8 = 5.50 (MICRO COMPLIANT, 0.39±0.05 PTH)
# OF COLUMNS	END WALL OPTIONS
1 = 10 COLUMN	0 = OPEN ENDS
6 = 16 COLUMN	1 = LEFT END WALL
7 = 14 COLUMN	2 = DUAL END WALL
	3 = RIGHT END WALL

SEE SHEET 1 EC NO: UCP2014-0887 DRWN: BINGHAM 2013/08/25 CHKD: JLAURX 2013/08/25 APPR: JLAURX 2013/09/25	G1	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE IMPACT 6 PAIR HEADER UNGUIDED ASSEMBLY SALES DRAWING molex	DOCUMENT NO. SD-76145-001	SHEET NO. 2 OF 3														
				F=0	mm	INCH	DRAWN BY MSANDBERG	DATE 2007/12/26																			
									F=0					3 PLACES	± ---	± ---	CHECKED BY JLAURX	DATE 2007/12/26									
																			F=0	2 PLACES	± 0.13	± ---	APPROVED BY JLAURX	DATE 2010/02/22			
																									1 PLACE	± 0.25	± ---
				ANGULAR ±1/2°		MATERIAL NO.		SEE TABLE																			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			

IMPACT 6 PAIR
BOARD RELATIONSHIPS



SEE SHEET 1 EC NO: UCP2014-0887 DRWN: BINGHAM 2013/08/25 CHKD: JLAURX 2013/08/25 APPR: JLAURX 2013/09/25	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE IMPACT 6 PAIR HEADER UNGUIDED ASSEMBLY SALES DRAWING molex
				mm	INCH	DRAWN BY MSANDBERG	DATE 2007/12/26				
			4 PLACES ± --- ± ---	3 PLACES ± --- ± ---	CHECKED BY JLAURX	DATE 2007/12/26					
			2 PLACES ± 0.13 ± ---	1 PLACE ± 0.25 ± ---	APPROVED BY JLAURX	DATE 2010/02/22					
			0 PLACE ± ±	ANGULAR ±1/2°		MATERIAL NO.	DOCUMENT NO.	SHEET NO.			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-76145-001		3 OF 3	
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					