

4

3

2

1

LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-11-004587			11MAR11	RK	HMR




MATERIALS:
HOUSING: POLYAMIDE, UL94V-0, BLACK.
TERMINALS: COPPER ALLOY, TIN PLATED.
SCREWS: STEEL, ZINC PLATED, UNLESS OTHERWISE STATED.

ELECTRICAL:
RATING: 20A, UL & CSA.


MECHANICAL:
WIRE RANGE: 12-22 AWG.
MAXIMUM TIGHTENING TORQUE: 7 IN-LBS.

ENVIRONMENTAL:
CONTINUOUS OPERATING TEMP.: -40°C TO +105°C

- 1 PRELIMINARY PART NUMBER.
- 2 SCREWS ARE NICKEL PLATED BRASS.



1546834-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 8/17/04	 TE Connectivity						
		CHK S YODER 8/17/04							
DIMENSIONS: INCHES		APVD S YODER 8/17/04	NAME NC6-P107-XX ASSEMBLY						
		PRODUCT SPEC —							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC —	SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
0 PLC ± — 1 PLC ± — 2 PLC ± .02 3 PLC ± .010 4 PLC ± — ANGLES ± —		WEIGHT —	A3		00779	C-1437664-4	—		
MATERIAL —		FINISH —	CUSTOMER DRAWING						
			SCALE		NTS	SHEET	1 OF 1	REV	B1