



STS5DPF20L

P-CHANNEL 20V - 0.045Ω - 5A SO-8

STripFET™ II MOSFET

Table 1: General Features

TYPE	V _{DSS}	R _{DS(on)}	I _D
STS5DPF20L	20 V	< 0.055 Ω	5 A

- TYPICAL R_{DS(on)} = 0.045 Ω
- CONDUCTION LOSSES REDUCED
- SWITCHING LOSSES REDUCED
- LOW THRESHOLD DRIVE
- STANDARD OUTLINE FOR EASY AUTOMATED SURFACE MOUNT ASSEMBLY

DESCRIPTION

This MOSFET is the latest development of STMicroelectronics unique "Single Feature Size™" strip-based process. The resulting transistor shows extremely high packing density for low on-resistance, rugged avalanche characteristics and less critical alignment steps therefore a remarkable manufacturing reproducibility.

APPLICATIONS

- DC/DC CONVERTERS
- BATTERY MANAGEMENT IN NOMADIC EQUIPMENT
- POWER MANAGEMENT IN CELLULAR PHONES
- DC MOTOR DRIVE

Figure 1: Package




Figure 2: Internal Schematic Diagram




Table 2: Order Codes

PART NUMBER	MARKING	PACKAGE	PACKAGING
STS5DPF20L	S5DPF20L	SO-8	TAPE & REEL

Table 3: Absolute Maximum ratings

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source Voltage ($V_{GS} = 0$)	20	V
V_{DGR}	Drain-gate Voltage ($R_{GS} = 20\text{ k}\Omega$)	20	V
V_{GS}	Gate- source Voltage	± 16	V
I_D	Drain Current (continuous) at $T_C = 25^\circ\text{C}$ Single Operating	5	A
I_D	Drain Current (continuous) at $T_C = 100^\circ\text{C}$ Single Operating	4	A
$I_{DM}(\bullet)$	Drain Current (pulsed)	20	A
P_{TOT}	Total Dissipation at $T_C = 25^\circ\text{C}$ Dual Operating	1.6	W
	Total Dissipation at $T_C = 25^\circ\text{C}$ Single Operating	2	W
T_j T_{stg}	Operating Junction Temperature	150	$^\circ\text{C}$
	Storage Temperature	-55 to 150	$^\circ\text{C}$

($\bullet$) Pulse width limited by safe operating area

Note: For the P-CHANNEL MOSFET actual polarity of voltages and current has to be reversed

Table 4: Thermal Data

Rthj-case	Thermal Resistance Junction-case Single Operating Dual Operating	62.5 78	$^\circ\text{C/W}$ $^\circ\text{C/W}$
T_I	Maximum Lead Temperature For Soldering Purpose	300	$^\circ\text{C}$

ELECTRICAL CHARACTERISTICS ($T_{CASE} = 25^\circ\text{C}$ UNLESS OTHERWISE SPECIFIED)

Table 5: On/Off

Symbol	Parameter	Test Conditions	Min.	Typ.	Max	Unit
$V_{(BR)DSS}$	Drain-source Breakdown Voltage	$I_D = 250\text{ }\mu\text{A}$, $V_{GS} = 0$	20			V
I_{DSS}	Zero Gate Voltage Drain Current ($V_{GS} = 0$)	$V_{DS} = \text{Max Rating}$ $V_{DS} = \text{Max Rating}$, $T_C = 125^\circ\text{C}$			1 10	μA μA
I_{GSS}	Gate-body Leakage Current ($V_{DS} = 0$)	$V_{GS} = \pm 16\text{V}$			± 100	nA
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = 250\text{ }\mu\text{A}$	1	1.6	2.5	V
$R_{DS(on)}$	Static Drain-source On Resistance	$V_{GS} = 10\text{ V}$, $I_D = 2.5\text{ A}$ $V_{GS} = 4.5\text{ V}$, $I_D = 2.5\text{ A}$		0.045 0.070	0.055 0.075	Ω Ω

Table 6: Dynamic

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
$g_{fs}(1)$	Forward Transconductance	$V_{DS} = 15\text{ V}$, $I_D = 2.5\text{ A}$		10		S
C_{iss} C_{oss} C_{rss}	Input Capacitance Output Capacitance Reverse Transfer Capacitance	$V_{DS} = 16\text{V}$, $f = 1\text{ MHz}$, $V_{GS} = 0$		1350 490 130		pF pF pF

(1) Pulsed: Pulse duration = 300 μs , duty cycle 1.5%

ELECTRICAL CHARACTERISTICS(CONTINUED)**Table 7: Switching On**

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$ t_r	Turn-on Delay Time Rise Time	$V_{DD} = 15\text{ V}$, $I_D = 2\text{ A}$, $R_G = 4.7\ \Omega$, $V_{GS} = 4.5\text{ V}$ (see Figure 15))		25 35		ns ns
Q_g Q_{gs} Q_{gd}	Total Gate Charge Gate-Source Charge Gate-Drain Charge	$V_{DD} = 24\text{ V}$, $I_D = 4\text{ A}$, $V_{GS} = 5\text{ V}$ (see, Figure 18)		12.5 5 3	16	nC nC nC

Table 8: Switching Off

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
$t_{d(off)}$ t_f	Turn-off Delay Time Fall Time	$V_{DD} = 15\text{ V}$, $I_D = 2.5\text{ A}$, $R_G = 4.7\ \Omega$, $V_{GS} = 4.5\text{ V}$ (see, Figure 15)		125 35		ns ns

Table 9: Source-Drain Diodef

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
I_{SD}	Source-drain Current				5	A
$I_{SDM}\ (2)$	Source-drain Current (pulsed)				20	A
$V_{SD}\ (1)$	Forward On Voltage	$I_{SD} = 5\text{ A}$, $V_{GS} = 0$			1.2	V
t_{rr} Q_{rr} I_{RRM}	Reverse Recovery Time Reverse Recovery Charge Reverse Recovery Current	$I_{SD} = 5\text{ A}$, $di/dt = 100\text{ A}/\mu\text{s}$ $V_{DD} = 15\text{ V}$, $T_j = 150^\circ\text{C}$ (see, Figure 16)		45 36 1.6		ns nC A

(1) Pulsed: Pulse duration = 300 μs , duty cycle 1.5 %.

(2) Pulse width limited by safe operating area.

Figure 3: Safe Operating




Figure 4: Output Characteristics




Figure 5: Transconductance




Figure 6: Thermal Impedance




Figure 7: Transfer Characteristics




Figure 8: Static Drain-Source On Resistance




Figure 9: Gate Charge vs Gate-Source Voltage




Figure 10: Normalized Gate Threshold Voltage vs Temperature




Figure 11: Source-Drain Diode Forward Characteristics




Figure 12: Capacitances Variations




Figure 13: Normalized On Resistance vs Temperature




Figure 14: Unclamped Inductive Load Test Circuit




Figure 15: Switching Times Test Circuit For Resistive Load




Figure 16: Test Circuit For Inductive Load Switching and Diode Recovery Times




Figure 17: Unclamped Inductive Wafeform





Figure 18: Gate Charge Test Circuit



SO-8 MECHANICAL DATA

DIM.	mm.			inch		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A			1.75			0.068
a1	0.1		0.25	0.003		0.009
a2			1.65			0.064
a3	0.65		0.85	0.025		0.033
b	0.35		0.48	0.013		0.018
b1	0.19		0.25	0.007		0.010
C	0.25		0.5	0.010		0.019
c1	45 (typ.)					
D	4.8		5.0	0.188		0.196
E	5.8		6.2	0.228		0.244
e		1.27			0.050	
e3		3.81			0.150	
F	3.8		4.0	0.14		0.157
L	0.4		1.27	0.015		0.050
M			0.6			0.023
S	8 (max.)					




Table 10: Revision History

Date	Revision	Description of Changes
10-Sep-2004	2	Complete Version

Obsolete Product(s) - Obsolete Product(s)

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a registered trademark of STMicroelectronics

All other names are the property of their respective owners

© 2004 STMicroelectronics - All Rights Reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America