



MICRO SWITCH
FREERPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 81929




SWITCH-ENCLOSED

CATALOG LISTING
442EN223-6



LEVER MAY BE ADJUSTED FOR AN INFINITE NUMBER OF POSITIONS THRU 360°. ADJUSTMENT IS MADE BY LOOSENING THE LOCK NUT AND THEN THE LOCKSCREW AND TURNING GEAR UNTIL LEVER IS IN DESIRED POSITION. LOCKSCREW AND LOCK NUT ON SHAFT IS THEN TIGHTENED TO POSITIVELY LOCK LEVER IN POSITION


LEVER ADJUSTMENT DETAIL
SCALE 2:1



6X NO.22 WIRE LEAD PER M22759/32-22-9
MARKED WITH CIRCUIT IDENTIFICATION AND
WIRE GAGE (1-22,2-22 ETC) PER MIL-W-5088

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY
OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT
TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE, UNLESS NOTED. TOLERANCES ARE ±

NO PLACES	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
ONE PLACE	X	1/16	X	0.003
TWO PLACES	X, XX	0.4/0.16	X, XX	0.38/0.15
THREE PLACES	X, XX, XXX	0.15/0.06	X, XX, XXX	0.15/0.05
ANGLES				

DESIGN UNITS SI METRIC US CUSTOMARY

RAW MATERIAL-COMMERCIAL STANDARD

MICRO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE
PROTECTIVE COATINGS ARE APPLIED

WEIGHT 7.3 OZ MAX

NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
- 3 - CIRCUIT DIAGRAM, DATE CODE, FED. MFG. CODE
AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
- 4 - UNIT PROVIDES NO SHAFT RESTORING TORQUE. THE ACTUATING
DEVICE MUST CONTROL MOVEMENT OF THE SHAFT
DO NOT APPLY MORE THAN 20-25 INCH-POUNDS OF TORQUE WHEN
TIGHTENING LOCKING NUT
HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
- 5 - SILVER PROJECTION, GOLD PLATED CONTACTS
- 6 -
- 7 -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[442EN223-6](#)