

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.


LOC	DIST	P	F	LTR	DESCRIPTION	DATE	APPROVED
G	25			L	REV; EC 0230-0327-95	03 SEPT 96	DS/EH
				M	REV PER CG3A-0255-03	23 APR 03	JR/TM

NOTES:


1. DOTTED CIRCLES SHOW APPROX. LOCATION OF WIRE RANGE IDENTIFIERS.
2. 4.06 (.160) MAX. INSULATION DIA.
3. UL AND CSA LOGOS TO APPEAR ON HOUSING AS SHOWN.
4. * PART NUMBER OBSOLETE.
5. 100 PIECES IN A BOX.
6. 5 PIECES IN A PRINTED POLY BAG WITH A PEG HOLE.

WIRE STOP
SEE TABLE
COLUMN B.

WIRE STOP
SEE TABLE
COLUMN A.



BOTTOM VIEW



53440-2 PER NOTE 6	0.51 [.020]	NO	YES	RED	0.5-0.8	[20-18]	53440-0* OBS.
53440-2 PER NOTE 5	0.51 [.020]	NO	YES	RED	0.5-0.8	[20-18]	53440-9
53440-1 PER NOTE 6	0.71 [.020]	NO	YES	BLUE	0.8-2	[18-14]	53440-8* OBS.
53440-1 PER NOTE 5	0.71 [.028]	NO	YES	BLUE	0.8-2	[18-14]	53440-7
OBSOLETE	0.51 [.020]	NO	NO	RED	0.5-0.8	[20-18]	53440-6*
OBSOLETE	0.71 [.028]	NO	NO	BLUE	0.8-2	[18-14]	53440-5*
OBSOLETE	0.71 [.028]	YES	YES	BLUE	0.8-2	[18-14]	53440-4*
OBSOLETE	0.51 [.020]	YES	YES	RED	0.5-0.8	[20-18]	53440-3*
	0.51 [.020]	NO	YES	RED	0.5-0.8	[20-18]	53440-2
	0.71 [.028]	NO	YES	BLUE	0.8-2	[18-14]	53440-1
PACKAGING	C	B	A	COLOR	mm ² AWG WIRE SIZE	PART NO	

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN (IN)
TOLERANCES ON:
2 PLC DEC *
3 PLC DEC *
ANGLES *

DR MIDDLETON CAD
8/23/90
CHK B.J.H.
4-20-92
APPD

APPD F. HARNED
8/90
PRODUCT SPEC

MATERIAL
BRASS (MIL-C-50)
ON (MIL-M-20693A)

FINISH

AMP SPEC 112-16

APPLICATION SPEC

WEIGHT
2.18 g

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

ELECTRO - TAP

SIZE

A

CAGE CODE

00779

DRAWING NO

C-53440

SCALE

NTS

SHEET

1 of 1