

Cable lug - C-BCI 1,5/2,8 - 3240015

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flat pin cable lug, red, 0.5 - 1.5 mm², for only horizontal crimping with CRIMPFOX-RCI 6

Why buy this product

- 'EASY ENTRY' for easy and reliable conductor entry
- Halogen-free
- Electrolytic tin plating



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 046356 452632
GTIN	4046356452632
Weight per Piece (excluding packing)	0.800 g
Custom tariff number	85369010
Country of origin	China

Technical data

Dimensions

Length (b)	28 mm
Width (a)	2.8 mm
Maximum stripping length	7 mm
Length contact range	17.5 mm
Length of insulation sleeve (c)	10.5 mm
Inner dimension of the insulating collar (d)	4 mm

Cable lug - C-BCI 1,5/2,8 - 3240015

Technical data

Dimensions

Material thickness (g)	0.8 mm
------------------------	--------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
Short-term temperature	120 °C
Max. permanent temperature	105 °C

General


Color	red
Stripping length	7 mm
Components	Halogen-free
Flammability rating according to UL 94	V2
Material	Copper
Insulating material	PA
Coating	Tin-plated

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Drawings

Dimensional drawing



Approvals

Approvals

Approvals

EAC / EAC

Cable lug - C-BCI 1,5/2,8 - 3240015

Approvals

Ex Approvals

Approval details

EAC



7500651.22.01.00246

EAC



EAC-Zulassung