


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW	LABELS PER ROLL
C090X025KBT	GMK 4	0.900 [22.86] X X	3	10000
C090X025KCT				
C090X025YJT	GMY2	0.250 [6.35]		
C090X025TJT	GMT4 - W			



NOTES:

1. SEE MFG. DWG. NO. A61366.
2. MILLIMETER ARE IN [].

TYP. 2 PLS.										CAD FILENAME/LAYERS 100472MY_C10448_C090X025KBT_00.prt			
										PANDUIT CORP. TINLEY PARK, ILLINOIS CUSTOMER DRAWING OPTIMUM C090X025**T THERMAL TRANSFER LABELS 2			
2	5/21/07	RVU		ADDED NEW P/N, C090X025YJT. AND C090X025TJT. MISC. REVISION.	5003	R				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .03 (.XXX) ± .010 (.XX) ± .015 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
1	4/16/07	RVU		ADDED P/N: C090S025KCT. C090X025KBT, MAT'L SHOULD BE GMK4.	4954	R							
0	1-18-07	RVU		RELEASE TO PRODUCTION.	4845	R				DRAWN BY RVU	MAT'L; SEE TABLE		
A	8-23-06	RVU		DRAWING RELEASE	0000	R				DATE 8-23-06		DRAWING NO. C10448	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D		SIZE	