


ZLTMM-112-75-L-D-285



LTMM-113-02-T-D

(2,00 mm) .0787"

LTMM, ZLTMM SERIES

SHROUDED HEADER & STACKER

Mates with:
SQT, SQW, ESQT, SMM

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?LTMM or www.samtec.com?ZLTMM

Insulator Material:
High Temperature Nylon

Terminal Material:
Phosphor Bronze

Plating:

Sn or Au over
50µ" (1,27 µm) Ni

Operating Temp Range:
-55°C to +105°C with Tin;
-55°C to +125°C with Gold

RoHS Compliant:
Yes

Processing:

Lead-Free Solderable:
Yes

SMT Lead Coplanarity:
(0,10 mm) .004" max

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

OTHER SOLUTIONS

- Shrouded IDC headers and stackers to mate with TCSD Series. See STMM and ZSTMM Series.

ALSO AVAILABLE (MOQ Required)

- Other sizes
 - Other platings
- Contact Samtec.

Note: This Series is non-standard, non-returnable.

LTMM	1	NO. PINS PER ROW	02	PLATING OPTION	D	TAIL OPTION	OTHER OPTION
04, 05, 06, 07, 08, 10, 12, 13, 15, 17, 20, 22, 25 (Standard sizes)				-F = Gold flash on post, Matte Tin on tail -L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail -T = Matte Tin	Leave blank for Through-hole -RA = Right Angle -SM = Surface Mount	-“XX” = Polarized Position -LC = Locking Clip (-SM only) (Manual placement required) -K = (7,50 mm) .295" DIA Film Pick & Place Pad (-SM only) -TR = Tape & Reel (-SM only)	

ZLTMM	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	BODY HEIGHT	OTHER OPTION
04, 05, 06, 07, 08, 10, 12, 13, 15, 17, 20, 22, 25 (Standard sizes)				-F = Gold flash on post, Matte Tin on tail -L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail -T = Matte Tin	-“XXX” = Body Height	-“XX” = Polarized Position	

LEAD STYLE	B (OAL)	MAX BODY HEIGHT
-75	(9,58) 0.377	(7,42) 0.292
-62	(10,08) 0.397	(7,92) 0.312
-65	(10,49) 0.413	(8,33) 0.328
-73	(12,09) 0.476	(9,93) 0.391
-63	(14,10) 0.555	(11,94) 0.470
-66	(15,09) 0.594	(12,93) 0.509
-69	(15,60) 0.614	(13,44) 0.529
-74	(17,09) 0.673	(14,94) 0.588
-70	(17,60) 0.693	(15,44) 0.608
-71	(21,08) 0.830	(18,92) 0.745
-72	(21,62) 0.851	(19,46) 0.766

Note: For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685