

Products

- Products Overview
- Product Search**
- Evaluate
  - FAQ's
- Design a Solution
  - Catalog Cut Sheet
  - PDFHSTT0548-Q
  - Part Drawings
  - PDFGB0239KH- H ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips

Part Number > HSTT19-M

Your search criteria matched only one product, shown below

**HSTT19-M**



Flexible Polyolefin DRY-SHRINK™ Heat Shrink Tubing

- General Purpose heat shrink tubing for dry locations
- Applications include insulating, protecting, harnessing and identifying wires.
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 275°F (-55°C to 135°C)
- Flammability Rating: Flame retardant EXCEPT clear
- Voltage: 600 V
- UL Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear) (material performance only)

Part Number	HSTT19M
RoHS Compliancy Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink
Material	Polyolefin cross-linked
Color	Black
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 1 (material performance only)
UL Recognized	E122770
Length (ft.)	1000
Length (m)	304.8
CE Compliant	No
Length Per Reel (ft.)	1000
Length Per Reel (m)	304.8
Max. Recovered I.D. (In.)	0.093
Max. Recovered I.D. (mm)	2.4
Min. Expanded I.D. (In.)	0.187
Min. Expanded I.D. (mm)	4.8
Nominal Diameter / Size	0.187
Nominal Recovered Wall Thickness (In.)	0.020
Nominal Recovered Wall Thickness (mm)	0.5
Pricing Description	Heat Shrink Thin, .19"(4.8mm) Dia, Black
Shrink Ratio	2:1
Temperature Range	-67°F – 275°F (-55°C – 135°C)
Type	Heat Shrink
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.