


DIMENSIONS IN INCHES. DO NOT SCALE PRINT.		MATL -		HT TR -		FIN -	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR T.KINT 01FEB00 APP 01FEB00 CHK T.ELBIN		 AMP Incorporated Marlborough, PA 17105-3508			
2 PLC DEC ±		01FEB00 REL -					
3 PLC DEC ±		B.HIGHMAN					
4 PLC DEC ±							
ANGLES ±		NAME SIDE FEED HDM APPLICATOR MACHINE REF					
SURF TEXTURE: ✓		SCALE - [D] DWG NO 1385019 SHEET 1 OF 1 REV A					
REMOVE BURRS, BREAK SHARP EDGES R.015 MAX							
CAGE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING					RESTRICTED TO -



POST FEED 1 5/8 STROKE

PRE FEED 1/8 STROKE

PRE FEED 1 5/8 STROKE

ROTATED 180°

ROTATED 180°

ROTATED 180°

H

H

LOC A

DIST 66

LEADMAKER

K TERMINATOR

G TERMINATOR

BENCH MACHINE

1. RECOMMENDED SPARE PARTS.
 2. GREASE LIGHTLY.
 3. GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE.
 4. LUBRICATE DAILY USING NO. 20 MACHINE OIL.
5. ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46.

[illegible]