


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			Y	REV PER ECO-12-018372	30OCT2012	JM	LH

FINISHED WIRE DATA		
CONDUCTORS	WIRE AWG	23 AWG SOLID
	MATERIAL	SOLID BARE COPPER
INSULATION	MATERIAL	FLUOROPOLYMER
JACKET	MATERIAL	FR PVC

COLOR CODE

PAIR COLOR CODE	
1	WHT-BLU/BLU
2	WHT-ORG/ORG
3	WHT-GRN/GRN
4	WHT-BRN/BRN



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- SEQUENTIAL FOOTAGE RETURNED TO ZERO FOR EACH LENGTH ON PUTUP LENGTHS 3000 FT OR LESS.
- MATERIALS ARE SELECTED BASED ON THEIR ABILITY TO CONFORM TO UL 444 LATEST ISSUE.
- INSULATION COLORS SHALL BE BLUE, ORANGE, GREEN, BROWN AND WHITE WITH CORRESPONDING COLORED STRIPES. INSULATION COLOR MAY BE TRANSLUCENT.
- XX=JACKET COLOR. BL=BLUE, WT=WHITE, GY=GRAY, GN=GREEN, YL=YELLOW, OR=ORANGE, RD=RED, VT=VIOLET, BK=BLACK.
- PRINT COLOR SHALL BE DARK BLUE EXCEPT WHITE ON BLACK JACKET.
- DATE CODE.
- GOVERNING SPECIFICATIONS - LATEST REVISIONS
TIA-568-C.2 CAT 6
NEC 800
UL 444 - CMP
- REPLACE "02" FOR THE FOLLOWING FOOTAGES: 04=2,000', 05=2,500'. CALL FOR ADDITIONAL OPTIONS.

TE CONNECTIVITY 620 SERIES 4/23 AWG T256 CMP C(UL)US ETL VERIFIED TIA-568-C.2 CAT 6 PAT 6153826, 6743983 XXXX FT

CATALOG NUMBER	WEIGHT		PACKAGING
	LBS/KFT	KG/KM	
TE620P-XX02	30	44	1,000' REEL
TE620P-XXII	29	43	1,000' REELEX BOX
TE620P-XXRB	32	47	1,000' REEL-IN-A-BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± .1
2 PLC ± .02
3 PLC ± .005
4 PLC ± .0005
ANGLES ± -
FINISH -

DWN
L.D.SIMPSON
CHK
R.W.SPEER
APVD
R.W.SPEER
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
-

21AUG2001
31AUG00
31AUG00

CUSTOMER DRAWING

TE Connectivity

CABLE, CATEGORY 6, 4UTP, 23 AWG, CMP

SIZE
A2
CAGE CODE
00779
DRAWING NO
C=219567
RESTRICTED TO
-

SCALE
NTS
SHEET
1 of 1
REV
Y