





Lead Lengths 40mm +5/-0mm



TOR

PART No	T68-40A	AL 47
SIZE (OD/ID/Ht)	17.5/9.4/6.35	
COATING	NA	
MATERIAL	IRON POWDER	
K VALUE	NA	

Cu Wire


PART No	COP207	WEIGHT (g) 4.5
SIZE (Dia)	0.28	
COATING	SOL 2	
COAT MATERIAL	NA	

Winding

No Turns	292
No Layers	CONTINUOUS
No Strands	ONE
Direction	AS PER SKETCH

TEST	Nom	Tolerance	Min	Max
Inductance (mH)	4	+20/-20%	3.2	4.8
Res (Ohm)	1.8	+15/-15%	1.53	2.07
Hi Pot (V AC)	NA			

ALL DIMENSIONS IN MM / ANGLES IN DECIMAL DEGREES



ROXBURGH ELECTRONICS LTD

TITLE ASSEMBLY FOR SF1120

DrgNo SF1120-CHK

ISSUE 2

PROCUREMENT SPECIFICATION
FOR SF1120-CHK

CUSTOMER

REFERENCE

Sheet 1 of 1 Aprvd Date 15/08/00 Aprvd By JRT Drwn by BFS SCALE NTS CNN--- Location N: \DWG\PS\CHK\CHK00094

© ROXBURGH ELECTRONICS LTD, FOXHILLS INDUSTRIAL PARK, SCUNTHORPE, NORTH LINCOLNSHIRE, DN15 8QJ TEL +44 1724 281770 F +44 1724 270230