


D-SUBMINIATURE CONNECTORS: K22X Series Right Angle PCB Mount 0.318" Footprint

K22X Series Dimensions Dimensions in mm



Shell Size In mm	A ±.010 ±.025	A1 ±.010 ±.025	B ±.005 ±.013	C ±.015 ±.038
9 (E)	.643 16.33	.666 16.92	.984 24.99	1.213 30.81
15 (A)	.971 24.66	.994 25.25	1.312 33.32	1.541 39.14
25 (B)	1.511 38.38	1.534 38.96	1.852 47.04	2.088 53.04
37 (C)	2.159 54.84	2.182 55.42	2.500 63.50	2.729 69.32

A = Exterior of Female Shell (S)
A1 = Interior of Male Shell (P)



Generated Part Number

K22X-E9P-N

Part Number Builder

K22X	-	E9	P	N	
Series		Shell Size Contact	Contact Type	Mounting Option	Plating Option

Series

K22X - D-Subminiature Connector, Right Angle

Shell Size-Contact Option

E - 9 Contacts
A - 15 Contacts
B - 25 Contacts
C - 37 Contacts

Contact Type

P - Pin Contact (Plug)
S - Socket Contact (Receptacle)

Mounting Option

N - With Boardlocks and #4-40 UNC Threaded Inserts
NJ - With Boardlocks and # 4-40 Jackscrews Installed

Plating Option

Blank - Gold Flash
30 - 30μ" Gold