

5 pieces 3-5/8 In. 36 TPI Basic for Metal T-Shank Jig Saw Blades **T118G**

- For sheet metal 17-26 gauge, very thin metals 1/64 In. to 3/64 In. thick (ferrous and non-ferrous)
- 36 TPI tooth design for smooth cuts in very thin materials
- High-speed steel construction for maximum life in straight cuts
- 3-5/8 In. overall length, 2-5/8 In. working length
- Proper lubricant is recommended when cutting metal
- 5 piece pack



Specifications: T118G 5 pieces 3-5/8 In. 36 TPI Basic for Metal T-Shank Jig Saw Blades

Type	Basic for Metal
Teeth Per Inch	36
Overall Length	3-5/8"
Type of Cut	Straight cuts
Quantity	5
Application	Sheet metal 17-26 gauge, very thin metals 1/64"-3/64" (ferrous and non-ferrous)
Tooth Design	Wavy set and milled
Material	High Speed Steel
Working Length	2-5/8"
Blade Thickness	0.04"
Blade Height	0.3"
*Note	If cutting metal, use cutting oil to cool blade. Use only with GCFI-protected outlets or adapters