

"Low Side Chopper" IGBT SOT-227 (Trench IGBT), 100 A


SOT-227

FEATURES

- Trench IGBT technology
- Very low $V_{CE(on)}$
- Square RBSOA
- HEXFRED® clamping diode
- 10 μ s short circuit capability
- Fully isolated package
- Speed 4 kHz to 30 kHz
- Very low internal inductance (≤ 5 nH typical)
- Industry standard outline
- Compliant to RoHS directive 2002/95/EC


RoHS
COMPLIANT

PRODUCT SUMMARY

V_{CES}	1200 V
I_C DC	100 A at 71 °C
$V_{CE(on)}$ typical at 100 A, 25 °C	2.36 V

BENEFITS

- Designed for increased operating efficiency in power conversion: UPS, SMPS, welding, induction heating
- Easy to assemble and parallel
- Direct mounting on heatsink
- Plug-in compatible with other SOT-227 packages
- Low EMI, requires less snubbing

ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Collector to emitter voltage	V_{CES}		1200	V
Continuous collector current	I_C	$T_C = 25\text{ °C}$	134	A
		$T_C = 80\text{ °C}$	92	
Pulsed collector current	I_{CM}		270	
Clamped inductive load current	I_{LM}		270	
Diode continuous forward current	I_F	$T_C = 25\text{ °C}$	87	
		$T_C = 80\text{ °C}$	59	
Gate to emitter voltage	V_{GE}		± 20	V
Power dissipation, IGBT	P_D	$T_C = 25\text{ °C}$	463	W
		$T_C = 80\text{ °C}$	260	
Power dissipation, diode	P_D	$T_C = 25\text{ °C}$	338	
		$T_C = 80\text{ °C}$	190	
RMS isolation voltage	V_{ISOL}	Any terminal to case, $t = 1$ min	2500	V

Vishay High Power Products "Low Side Chopper" IGBT SOT-227
(Trench IGBT), 100 A

ELECTRICAL SPECIFICATIONS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Collector to emitter breakdown voltage	$V_{BR(CES)}$	$V_{GE} = 0\text{ V}$, $I_C = 1\text{ mA}$	1200	-	-	V
Collector to emitter voltage	$V_{CE(on)}$	$V_{GE} = 15\text{ V}$, $I_C = 50\text{ A}$	-	1.79	2.33	
		$V_{GE} = 15\text{ V}$, $I_C = 100\text{ A}$	-	2.36	2.85	
		$V_{GE} = 15\text{ V}$, $I_C = 50\text{ A}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	2.05	2.62	
		$V_{GE} = 15\text{ V}$, $I_C = 100\text{ A}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	2.8	3.42	
Gate threshold voltage	$V_{GE(th)}$	$V_{CE} = V_{GE}$, $I_C = 500\text{ }\mu\text{A}$	5	5.8	7	
Temperature coefficient of threshold voltage	$V_{GE(th)}/\Delta T_J$	$V_{CE} = V_{GE}$, $I_C = 1\text{ mA}$ ($25\text{ }^{\circ}\text{C}$ to $125\text{ }^{\circ}\text{C}$)	-	- 15.6	-	mV/ $^{\circ}\text{C}$
Collector to emitter leakage current	I_{CES}	$V_{GE} = 0\text{ V}$, $V_{CE} = 1200\text{ V}$	-	0.5	100	μA
		$V_{GE} = 0\text{ V}$, $V_{CE} = 1200\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	0.052	2	mA
Diode reverse breakdown voltage	V_{BR}	$I_R = 1\text{ mA}$	1200	-	-	V
Diode forward voltage drop	V_{FM}	$I_C = 50\text{ A}$, $V_{GE} = 0\text{ V}$	-	2.53	3.55	V
		$I_C = 100\text{ A}$, $V_{GE} = 0\text{ V}$	-	3.32	4.35	
		$I_C = 50\text{ A}$, $V_{GE} = 0\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	2.66	3.70	
		$I_C = 100\text{ A}$, $V_{GE} = 0\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	3.70	4.50	
Diode reverse leakage current	I_{RM}	$V_R = V_R$ rated	-	4	50	μA
		$T_J = 125\text{ }^{\circ}\text{C}$, $V_R = V_R$ rated	-	0.6	3	mA
Gate to emitter leakage current	I_{GES}	$V_{GE} = \pm 20\text{ V}$	-	-	± 200	nA

SWITCHING CHARACTERISTICS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Total gate charge (turn-on)	Q_g	$I_C = 100\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = 15\text{ V}$	-	400	-	nC
Gate to emitter charge (turn-on)	Q_{ge}		-	120	-	
Gate to collector charge (turn-on)	Q_{gc}		-	170	-	
Turn-on switching loss	E_{on}	$I_C = 100\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = 15\text{ V}$, $R_g = 5\text{ }\Omega$, $L = 500\text{ }\mu\text{H}$	-	21.9	-	mJ
Turn-off switching loss	E_{off}		-	5.48	-	
Total switching loss	E_{tot}		-	27.38	-	
Turn-on switching loss	E_{on}		-	23.6	-	
Turn-off switching loss	E_{off}	$I_C = 100\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = 15\text{ V}$, $R_g = 5\text{ }\Omega$, $L = 500\text{ }\mu\text{H}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	7.65	-	ns
Total switching loss	E_{tot}		-	31.25	-	
Turn-on delay time	$t_{d(on)}$		-	195	-	
Rise time	t_r		-	259	-	
Turn-off delay time	$t_{d(off)}$		-	188	-	
Fall time	t_f		-	212	-	
Reverse bias safe operating area	RBSOA	$T_J = 150\text{ }^{\circ}\text{C}$, $I_C = 270\text{ A}$, $R_g = 22\text{ }\Omega$, $V_{GE} = 15\text{ V}$ to 0 V , $V_{CC} = 900\text{ V}$, $V_P = 1200\text{ V}$	Fullsquare			
Short circuit safe operating area	SCSOA	$T_J = 150\text{ }^{\circ}\text{C}$, $R_g = 22\text{ }\Omega$, $V_{GE} = 15\text{ V}$ to 0 V , $V_{CC} = 900\text{ V}$, $V_P = 1200\text{ V}$	10			μs
Diode reverse recovery time	t_{rr}	$I_F = 50\text{ A}$, $di_F/dt = 200\text{ A}/\mu\text{s}$, $V_R = 200\text{ V}$	-	129	161	ns
Diode peak reverse current	I_{rr}		-	11	14	A
Diode recovery charge	Q_{rr}		-	700	1046	nC
Diode reverse recovery time	t_{rr}	$I_F = 50\text{ A}$, $di_F/dt = 200\text{ A}/\mu\text{s}$, $V_R = 200\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	208	257	ns
Diode peak reverse current	I_{rr}		-	17	21	A
Diode recovery charge	Q_{rr}		-	1768	2698	nC

**"Low Side Chopper" IGBT SOT-227 Vishay High Power Products
(Trench IGBT), 100 A**

THERMAL AND MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNITS
Maximum junction and storage temperature range	T_J, T_{Stg}	- 40	-	150	°C
Thermal resistance, junction to case	R_{thJC}	-	-	0.27	°C/W
		-	-	0.37	
Thermal resistance, case to sink per module	R_{thCS}	-	0.05	-	
Mounting torque, 6-32 or M3 screw		-	-	1.3	Nm
Weight		-	30	-	g




Fig. 1 - Maximum DC IGBT Collector Current vs. Case Temperature




Fig. 3 - Typical IGBT Collector Current Characteristics




Fig. 2 - IGBT Reverse Bias SOA
 $T_J = 150\text{ °C}, V_{GE} = 15\text{ V}$




Fig. 4 - Typical IGBT Zero Gate Voltage Collector Current




Fig. 5 - Typical IGBT Threshold Voltage




Fig. 8 - Typical Diode Forward Characteristics




Fig. 6 - Typical IGBT Collector to Emitter Voltage vs. Junction Temperature, $V_{GE} = 15$ V




Fig. 9 - Typical IGBT Energy Loss vs. I_c
 $T_J = 125$ °C, $L = 500$ μ H, $V_{CC} = 600$ V,
 $R_g = 5$ Ω , $V_{GE} = 15$ V




Fig. 7 - Maximum DC Forward Current vs. Case Temperature




Fig. 10 - Typical IGBT Switching Time vs. I_c
 $T_J = 125$ °C, $L = 500$ μ H, $V_{CC} = 600$ V,
 $R_g = 5$ Ω , $V_{GE} = 15$ V

**"Low Side Chopper" IGBT SOT-227 Vishay High Power Products
(Trench IGBT), 100 A**




Fig. 11 - Typical IGBT Energy Loss vs. R_g
 $T_J = 125\text{ }^{\circ}\text{C}$, $I_C = 100\text{ A}$, $L = 500\text{ }\mu\text{H}$,
 $V_{CC} = 600\text{ V}$, $V_{GE} = 15\text{ V}$




Fig. 13 - Typical t_{rr} Diode vs. dI_F/dt
 $V_R = 200\text{ V}$, $I_F = 50\text{ A}$




Fig. 12 - Typical IGBT Switching Time vs. R_g
 $T_J = 125\text{ }^{\circ}\text{C}$, $L = 500\text{ }\mu\text{H}$, $V_{CC} = 600\text{ V}$,
 $I_C = 100\text{ A}$, $V_{GE} = 15\text{ V}$




Fig. 14 - Typical I_{rr} Diode vs. dI_F/dt
 $V_R = 200\text{ V}$, $I_F = 50\text{ A}$







Fig. 15 - Typical Q_{rr} Diode vs. dI_F/dt
 $V_R = 200\text{ V}$, $I_F = 50\text{ A}$

Fig. 16 - Maximum Thermal Impedance Z_{thJC} Characteristics (IGBT)Fig. 17 - Maximum Thermal Impedance Z_{thJC} Characteristics (Diode)

"Low Side Chopper" IGBT SOT-227 Vishay High Power Products (Trench IGBT), 100 A



* Driver same type as D.U.T.; $V_C = 80\%$ of $V_{CE(max)}$
 * Note: Due to the 50 V power supply, pulse width and inductor will increase to obtain I_d

Fig. 18a - Clamped Inductive Load Test Circuit




Fig. 18b - Pulsed Collector Current Test Circuit




Fig. 19a - Switching Loss Test Circuit




Fig. 19b - Switching Loss Waveforms Test Circuit

GT100LA120U

Vishay High Power Products "Low Side Chopper" IGBT SOT-227
(Trench IGBT), 100 A




ORDERING INFORMATION TABLE

Device code	G	T	100	L	A	120	U
	①	②	③	④	⑤	⑥	⑦

- 1** - Insulated Gate Bipolar Transistor (IGBT)
- 2** - T = Trench IGBT
- 3** - Current rating (100 = 100 A)
- 4** - Circuit configuration (L = Low side chopper)
- 5** - Package indicator (A = SOT-227)
- 6** - Voltage rating (120 = 1200 V)
- 7** - Speed/type (U = Ultrafast IGBT)

CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95036
Packaging information	www.vishay.com/doc?95037



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.