





NOTE: 1. ELECTRIC PERFORMANCE.
DIELECTRIC STRENGTH: 500V DC/0.01Sec.
INSULATION RESISTANCE: 100M OHMS Min.
CONNECTION RESISTANCE: 2 OHMS Max.

2. HOUSING 687520000:
POLYESTER(PBT), UL94V-0(BLACK)
TERMINAL 675810000
AU FLASH PLATING

887511311	675810001 30u" Gold-plated
887511310	675810000 GOLD FLASH
MATERIAL NO.	TERMINAL

TABLE

4	UL1007 *18 BLK 887711300
3	UL1007 *18 RED 887711301
2	UL1007 *18 BLK 887711300
1	UL1007 *18 YEL 887711303
Item	WIRE TYPE

CONNECTION DIAGRAM

EC NO: DG2008-0074 DRWN:ZWSHAO CHKD: APPR:BLAU	2008/02/20 2008/02/20 2008/02/21	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
					mm	INCH	DRAWN BY ZWSHAO		DATE 2008/02/20		TITLE SATA POWER CABLE			
				4 PLACES	± ---	± ---	CHECKED BY ARKAN		DATE 2008/02/20					
				3 PLACES	± ---	± ---	APPROVED BY BLAU		DATE 2008/02/20		MOLEX MOLEX INCORPORATED			
				2 PLACES	± ---	± ---								
				1 PLACE	± ---	± ---	MATERIAL NO. 887511310/887511311			DOCUMENT NO. SD-88755-001			SHEET NO. 1 OF 1	
				ANGULAR ±---°										
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A4		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOTBE USED WITHOUT WRITTEN PERMISSION					

