




PRODUCT NUMBER
SEE TABLE



SEE SHEET 3 FOR
LOCATOR/HOLDDOWN
VARIATIONS

.014 [0.36]
AT TIPS



mat'l. code				surface		tolerance		projection	product family				
-				ISO 1302 ✓		ISO 406 ISO 1101			RIBCAGE				
ltr	ecn no	dr	date	tolerances unless otherwise specified						title RIBCAGE III T/M VERT. HEADER ASS'Y			
L	J10329	CRG	6/6/01	angles	linear	.XX±.01/0.3							INCH/MM
M	M05-0123	MHT	6/6/05			.XXX±.005/0.13							
N	M06-0225	ERE	06/12/06			.XXXX±.0020/0.051							
P	M06-0370	MHT	9/26/06	0±2"		scale 4:1				dwg no		sheet 1 of 6	size
R	M09-0058	MHT	4/04/09	enrg	D. WHITING	6/6/95		95776		A3			
S	N10-0122	YO	5/10/10	chr	D. WHITING	6/6/95							
T	ELX-N-009749	YO	1/31/12	appd	D. WHITING	6/6/95							
sheet revision				T	T	T	T				T	type Product Customer Drawing	
index sheet				1	2	3	4	5	6				




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW



SECTION Y-Y

mat'l. code -					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	 INCH/MM scale 4:1	product family RIBCAGE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified				title RIBCAGE III T/M VERT. HEADER ASS'Y				
T					angles	linear	.XX±.01/0.3 .XXX±.005/0.13 0氣2? .XXXX±.0020/0.051						
					dr	M. CORNMAN	6/6/95						
					enr	D. WHITING	6/6/95		dwg no		sheet2 of 6	size	
					chr	D. WHITING	6/6/95		95776		A3		
					appd	D. WHITING	6/6/95		type		Product	Customer Drawing	
sheet index		revision sheet											


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS

STYLE
1




STYLE
2




$\phi .0520$ [1.321]
 $\phi .004/0.10$ (M) A B (ALL PEG CONFIGURATIONS)
 $.040$ [1.02]

STYLE
4




$.008[0.20] \times 45^\circ$
 $\phi .034 \pm .001$ [0.86 $\pm$ 0.03]
 $.0520^{+.0005}_{-.0010}$ [1.321 $\pm$ 0.013 / -0.025]
 $.0030$ [0.076]
 $.040^{+.001}_{-.002}$ [1.02 $\pm$ 0.03 / -0.05]
 $.008 \pm .003$ [0.20 $\pm$ 0.08]

STYLE
6



$.0520^{+.0005}_{-.0010}$ [1.321 $\pm$ 0.013 / -0.025]
 $.040^{+.001}_{-.002}$ [1.02 $\pm$ 0.03 / -0.05]
 $.0520^{+.0005}_{-.0010}$ [1.321 $\pm$ 0.013 / -0.025]
 $.040^{+.001}_{-.002}$ [1.02 $\pm$ 0.03 / -0.05]

STYLE
7




$.006 \pm 0.002$ [0.15 $\pm$ 0.05]
 $.0065 \pm .001$ [0.165 $\pm$ 0.025]
 $\phi .040$ [1.016]
 $.052 \pm .001$ [1.32 $\pm$ 0.02]
R.002 [0.05] MAX

mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title				
T					angles	linear	.XX±.01/0.3	RIBCAGE III T/M						
							.XXX±.005/0.13	VERT. HEADER ASS'Y						
					0氣2?		.XXXX±.0020/0.051	scale 4:1		dwg no		sheet3 of 6	size	
					dr	M. CORNMAN	6/6/95	95776		A3				
					enrg	D. WHITING	6/6/95							
					chr	D. WHITING	6/6/95							
					appd	D. WHITING	6/6/95					type		Product Customer Drawing
sheet index		revision sheet												


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
6




STYLE
2



STYLE
7



STYLE
4




mat'l. code -					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE								
ltr ecn no dr date					tolerances unless otherwise specified							title							
T					angles		linear		.XX±.01/0.3 .XXX±.005/0.13 0氣2? .XXX±.0020/0.051		INCH/MM		RIBCAGE III T/M VERT. HEADER ASS'Y						
											scale 4:1								
					dr		M. CORNMAN		6/6/95				dwg no		sheet4 of 6		size		
					enrg		D. WHITING		6/6/95				95776		A3				
					chr		D. WHITING		6/6/95										
					appd		D. WHITING		6/6/95										
sheet index		revision sheet																	


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ☒	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
							VERT. HEADER ASS'Y		
							dwg no		
							sheet 5 of 6		
							size		
							95776		
							A3		
							type		
							Product Customer Drawing		
sheet	revision								
index	sheet								

PDS: Rev :T

STATUS: Released

Printed: Sep 12, 2013

