

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 2031986

REVISION CS


DO NOT SCALE
FROM THIS PRINTTABLE 1
TERMINAL SPECIFICATIONS

TERMINAL SPEC	PIN #1	PIN #2 (a)	PIN #3	"C"
-05 (a)	T-1S6-21-XXX-2	N/A	N/A	.105 [2.67] (a)
-06 (a)	T-1S6-18-XXX-2	N/A	N/A	.105 [2.67] (a)
-07 (a)	T-1S6-07-XXX-2	N/A	N/A	.230 [5.84] (a)
-08 (a)	T-1S6-08-XXX-2	T-1S6-09-XXX-2	T-1S6-11-XXX-2	.230 [5.84] (a)(b)
-09 (a)	T-1S6-09-XXX-2	T-1S6-11-XXX-2	T-1S6-20-XXX-2	.230 [5.84] (a)
-10 (a)	T-1S6-10-XXX-2	T-1S6-12-XXX-2	T-1S6-13-XXX-2	.230 [5.84] (a)
-11 (a)	T-1S6-11-XXX-2	T-1S6-20-XXX-2	T-1S6-19-XXX-2	.230 [5.84] (a)
-12 (a)	T-1S6-12-XXX-2	T-1S6-13-XXX-2	T-1S6-14-XXX-2	.230 [5.84] (a)
-13 (a)	T-1S6-13-XXX-2	T-1S6-14-XXX-2	N/A	.230 [5.84] (a)
-14 (a)	T-1S6-08-XXX-2	N/A	N/A	.320 [8.13] (a)
-15 (a)	T-1S6-09-XXX-2	N/A	N/A	.520 [13.21] (a)
-16 (a)	T-1S6-09-XXX-2	T-1S6-11-XXX-2	T-1S6-20-XXX-2	.320 [8.13] (a)(b)
-17 (a)	T-1S6-10-XXX-2	N/A	N/A	.620 [15.75] (a)
-18 (a)	T-1S6-11-XXX-2	N/A	N/A	.720 [18.29] (a)
-19 (a)	T-1S6-12-XXX-2	N/A	N/A	.820 [20.83] (a)
-20 (a)	T-1S6-13-XXX-2	N/A	N/A	1.020 [25.91] (a)
-21 (a)	T-1S6-14-XXX-2	N/A	N/A	1.220 [30.99] (a)
-22 (a)	T-1S6-15-XXX-2	T-1S6-10-XXX-2	T-1S6-12-XXX-2	.230 [5.84] (a)(b)
-23 (a)	T-1S6-16-XXX-2	N/A	N/A	.230 [5.84] (a)
-24 (a)	T-1S6-17-XXX-2	N/A	N/A	.265 [6.73] (a)
-25 (a)	T-1S6-15-XXX-2	T-1S6-10-XXX-2	T-1S6-12-XXX-2	.320 [8.13] (a)(b)
-26 (a)	T-1RS7-01-XXX-2	N/A	N/A	.230 [5.84] (a)
-27 (a)	T-1S6-19-XXX-2	N/A	N/A	.230 [5.84] (a)
-28 (a)	T-1S6-20-XXX-2	T-1S6-19-XXX-2	N/A	.230 [5.84] (a)
-29 (a)	T-1S6-19-XXX-2	N/A	N/A	.320 [8.13] (a)
-30 (a)	T-1S6-20-XXX-2	T-1S6-19-XXX-2	N/A	.320 [8.13] (a)

- (1) .230 POST FOR -RA or -RE OPTION
(2) OMIT WITH -Q ROW SPECIFICATION
(3) NOT AVAILABLE IN -RA OR -RE OPTION.
(4) NOT AVAILABLE IN -RE OPTION.
(5) AVAILABLE IN -LL OPTION.
(6) AVAILABLE IN -LA OPTION.
(7) ON STYLE -08 -LA, RA; "C" = $230 \pm .008$ [5.84 ± .26]
(8) 1.220 POST FOR STRAIGHT PIN VERSION.

* SQUARE END OF PIN (T-1RS7-01-XXX-2) SHOULD BE LOCATED AT "C" DIMENSION DURING FILL PROCESS.
(SEE FIG. 4)

ASSEMBLY INSTRUCTIONS



NOTES:

- TERMINAL PUSHOUT FORCE: 3 LBS. MIN.
- HEIGHT VARIATION BETWEEN A PIN AND ANY ADJACENT PIN SHALL BE .005 [.13] MAX (R.A. TAIL N/A).
- ASSEMBLE GOLD PLATE END AS SHOWN.
- STYLE -26: ROUND END TO APPEAR ON BOTTOM.
- .020 [.51] MAX. ALLOWABLE FLASH AFTER REMOVAL OF CROSS-BARS.
- (C) REPRESENTS CRITICAL DIMENSION.
- "C" ± .008 [± .20] FOR STYLE -08, OPTION -LA & -RA ONLY.
- TOW & SWAY SPEC. OF 2" APPLIES TO ALL POSITIONS, POST & TAIL, IN ALL DIRECTIONS.
- ALL DIMENSIONS TO BE ABOUT CL WITHIN ±.005 [.13].
- MEASURE FROM THE TIPS OF THE TERMINALS.
- TSW-50-D BODY CAN BE USED IF RTSW-50-D IS UNAVAILABLE
- ORIENTATE PINS TO PREVENT BANDOLIER MARKS FROM SHOWING IN THE POST AREA. (SEE TABLE 7)
- COUNT ONLY USABLE PINS AS POSITIONS

TABLE 2 BODY SPECIFICATION	
ROW/OPTION	USE BODY
-S, -S-NA/-NE	TSW-50-S
-S, -RA/-RE	TSW-50-S-RA
-D, -D-NA/-NE	RTSW-50-D
-D, -RA	TSW-50-D-RA
-T, -T-NA/-NE	TSW-50-T
-T, -RA, -Q-RA	TSW-50-T-RA
-Q	TSW-50-T

NOTE DELTED

TABLE 4

PIN STYLE	"L"
T-1S6-07-XXX-2	.430 [10.92]
T-1S6-08-XXX-2	.530 [13.48]
T-1S6-09-XXX-2	.730 [18.54]
T-1S6-10-XXX-2	.830 [21.08]
T-1S6-11-XXX-2	.930 [23.62]
T-1S6-12-XXX-2	1.030 [26.16]
T-1S6-13-XXX-2	1.230 [31.24]
T-1S6-14-XXX-2	1.430 [36.32]
T-1S6-15-XXX-2	.630 [16.00]
T-1S6-16-XXX-2	.445 [11.30]
T-1S6-17-XXX-2	.480 [12.19]
T-1S6-18-XXX-2	.300 [7.62]
T-1S6-19-XXX-2	1.330 [33.78]
T-1S6-20-XXX-2	1.130 [28.70]
T-1S6-21-XXX-2	.335 [8.51]
T-1RS7-01-XXX-2	.456 [11.58]

* REF FOR
PIN LENGTH

UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE DECIMALS ±.1 [.3]
TWO PLACE DECIMALS ±.01 [.3]
THREE PLACE DECIMALS ±.005 [.13]
FOUR PLACE DECIMALS ±.0020 [.051]
ANGLES
± 2°

TITLE: ASSEMBLY,
.025 [.64] SQ. POST
TERMINAL STRIP

DWG NO:
TSW-XXX-XX-XXX-X-XX-XXX
SHEET 1 OF 4

TSW-XXX-XX-XXX-X-XX-XXX

TERMINAL SPACE SPEC.
(SEE ASSEMBLY INSTR.)

- 1= .100 [2.54] (FILL EVERY POS.)
-2= .200 [5.08] (FILL E/O POS.
STARTING W/ 1st & ENDING
W/ LAST POS. IN BODY)

BODY LENGTH SPEC.
EXPRESSED IN # OF POS

- 1: -01 THRU -50 (-S, -D, -T)
"A" = NO. OF POS. x .100 [2.54]
-2: -02 THRU -25 (-S, -D, -T)
"A" = NO OF POS. x .200 [5.08]
- .100 [5.08]

TERMINAL SPECIFICATION
SEE TABLE 1

PLATING SPECIFICATIONS

- G: GOLD
- T: TIN
- S: SELECTIVE HEAVY GOLD
- H: HEAVY GOLD
- L: SELECTIVE LIGHT GOLD
- P: GOLD FLASHED PALLADIUM NICKEL
- F: FLASH SELECTIVE GOLD
- E: EXTRA HEAVY GOLD (AVAILABLE IN STYLES -07, -08, -09, -13 & -14 STRAIGHT) (-08 DOUBLE RIGHT ANGLE)
- TL: TIN/LEAD (AVAILABLE ONLY ON LEAD STYLES -07, -08 & -09)
- STL: SELECTIVE TIN/LEAD (AVAILABLE ONLY ON LEAD STYLES -07, -08, -10, -16, -17, -21, & -24 STRAIGHT THROUGH HOLE ONLY).
- TM: MATTE TIN (SEE PLATING INSTRUCTIONS)
- SM: HEAVY SELECTIVE GOLD, MATTE TIN TAIL (SEE PLATING INSTRUCTIONS)
- LM: LIGHT SELECTIVE GOLD, MATTE TIN TAIL (SEE PLATING INSTRUCTIONS)
- FM: FLASH SELECTIVE GOLD, MATTE TIN TAIL (SEE PLATING INSTRUCTIONS)

ROW SPECIFICATION (SEE TABLE #2)

- S: SINGLE
- D: DOUBLE
- T: TRIPLE
- Q: TRIPLE ROW, FILL OUTER ROWS ONLY






FIG 4

FIG 1

-1: .100[5.08] TERMINAL SPACING



-2: .200[5.08] TERMINAL SPACING



MATERIAL:

BODIES:
DUPONT CRASTIN SK652 FR
COLOR: BLACK
TERMINALS:
PHOSPHOR BRONZE

EXISPROD\ASSEMBLY\100
TSW-ASM1

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322


MADE BY:
KOLB 8-24-88

TSW-XXX-XX-XXX-X-XX-XXX
SHEET 1 OF 4


PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING, RECORDING,
OR BY ANY INFORMATION STORAGE
AND RETRIEVAL SYSTEM, WITHOUT THE
WRITTEN CONSENT OF SAMTEC INC.

REV CS

FIG. 2
LOCKING LEAD
(NOTE: END VIEWS SHOWN.)



UNLESS OTHERWISE NOTED			TITLE: ASSEMBLY, .025 [.64] SQ. POST TERMINAL STRIP	DWG NO: TSW-XXX-XX-XXX-X-XX-XXX SHEET 2 OF 4
DIMENSIONS ARE IN INCHES		TOLERANCES ARE:		
ONE PLACE DECIMALS ±.1 [.3]	THREE PLACE DECIMALS ± .005 [.13]	ANGLES ± 2°		
TWO PLACE DECIMALS ±.01 [.3]	FOUR PLACE DECIMALS ± .0020 [.051]			



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
KOLB 8-24-88

TSW-XXX-XX-XXX-X-XX-XXX
SHEET 2 OF 4

REV CS

FIG. 3

(-LA OPTION IS SHOWN ON ALL RIGHT ANGLES FOR DIMENSIONAL AND LOCATION PURPOSES.)

NOTES: 1.) END VIEWS SHOWN.
2.) SEE NOTE 7 (SHEET 1)





TABLE 5 "E"									
LEAD STYLE	RA SINGLE	RE SINGLE	RA DOUBLE	RA TRIPLE	NA SINGLE	NE SINGLE	NA DOUBLE	NA TRIPLE	
08	.090 [2.29]	N/A	.090 [2.29]	.090 [2.29]	.109 [2.77]	N/A	.109 [2.77]	.109 [2.77]	
09	.290 [7.37]	.190 [4.83]	.290 [7.37]	.290 [7.37]	.309 [7.85]	.209 [4.34]	.309 [7.85]	.309 [7.85]	
10	.390 [9.91]	.290 [7.37]	.390 [9.91]	.390 [9.91]	.409 [10.39]	.309 [6.88]	.409 [10.39]	.409 [10.39]	
11	.490 [12.45]	.390 [9.91]	.490 [12.45]	.490 [12.45]	.509 [12.93]	.409 [9.42]	.509 [12.93]	.509 [12.93]	
12	.590 [14.99]	.490 [12.45]	.590 [14.99]	.590 [14.99]	.609 [15.47]	.509 [11.96]	.609 [15.47]	.609 [15.47]	
13	.790 [20.07]	.690 [17.53]	.790 [20.07]	N/A	.809 [20.55]	.709 [17.04]	.809 [20.55]	N/A	
16	.200 [5.08]	.100 [2.54]	.200 [5.08]	.200 [5.08]	.219 [5.56]	.119 [1.80]	.219 [5.56]	.219 [5.56]	
21	.990 [25.15]	.890 [22.61]	N/A	N/A	1.009 [25.63]	.909 [22.12]	N/A	N/A	
22	.190 [4.83]	.090 [2.29]	.190 [4.83]	.190 [4.83]	.209 [5.31]	.109 [1.80]	.209 [5.31]	.209 [5.31]	
25	.100 [2.54]	N/A	.100 [2.54]	.100 [2.54]	.119 [3.02]	N/A	.119 [3.02]	.119 [3.02]	
27	.890 [22.61]	.790 [20.07]	N/A	N/A	.909 [23.09]	.809 [19.58]	N/A	N/A	
28	.690 [17.53]	.590 [14.99]	.690 [17.53]	N/A	.709 [18.01]	.609 [14.50]	.709 [18.01]	N/A	
29	.800 [20.32]	N/A	N/A	N/A	.819 [20.80]	N/A	N/A	N/A	
30	.600 [15.24]	N/A	.600 [15.24]	N/A	.619 [15.72]	N/A	.619 [15.72]	N/A	

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING,
RECORDING, OR BY ANY
INFORMATION STORAGE AND
RETRIEVAL SYSTEM, WITHOUT
WRITTEN CONSENT OF SAMTEC INC.

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED		TOLERANCES ARE:	
ONE PLACE DECIMALS $\pm .1$	[.3]	THREE PLACE DECIMALS $\pm .005$	[.13]	ANGLES	$\pm 2^\circ$
TWO PLACE DECIMALS $\pm .01$	[.3]	FOUR PLACE DECIMALS $\pm .0020$	[.051]		

TITLE: ASSEMBLY,
.025 [.64] SQ. POST
TERMINAL STRIP

DWG NO:
TSW-XXX-XX-XXX-X-XX-XXX
SHEET 3 OF 4



CRIMP DETAIL

SCALE: 2x
[TYP- ALL CRIMPS]

EXISPROD\ASSEMBLY
100\TSW-ASM3

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: KOLB 8-24-88

TSW-XXX-XX-XXX-X-XX-XXX
SHEET 3 OF 4


REV CS

UNLESS OTHERWISE NOTED			TITLE: ASSEMBLY, .025 [.64] SQ. POST TERMINAL STRIP	DWG NO: TSW-XXX-XX-XXX-X-XX-XXX SHEET 4 OF 4
DIMENSIONS ARE IN INCHES		TOLERANCES ARE:		
ONE PLACE DECIMALS ±.1 [.3]	THREE PLACE DECIMALS ± .005 [.13]	ANGLES ± 2°		
TWO PLACE DECIMALS ±.01 [.3]	FOUR PLACE DECIMALS ± .0020 [.051]			

TABLE 7 (-T PLATING ONLY)

NUMBER OF BAND MARKS ALLOWED IN POST AREA				NUMBER OF BAND MARKS ALLOWED IN POST AREA			
LEAD STYLE	PIN #1	PIN #2	PIN #3	LEAD STYLE	PIN #1	PIN #2	PIN #3
*-05	*0	N/A	N/A	*-17	2	N/A	N/A
-06	1	N/A	N/A	*-18	2	N/A	N/A
-07	1	N/A	N/A	*-19	2	N/A	N/A
-08	0	0	0	*-20	2	N/A	N/A
-08-RA	0	0	0	*-21	2	N/A	N/A
-09	0	0	0	-21-RA	0	N/A	N/A
-09-RA	0	0	0	-21-RE	0	N/A	N/A
-09-RE	0	0	0	-22	0	0	0
-10	0	0	0	-22-RA	0	0	0
-10-RA	0	0	0	-22-RE	0	0	0
-10-RE	0	0	0	-23	1	N/A	N/A
-11	0	0	0	-24	1	N/A	N/A
-11-RA	0	0	0	-25	1	1	1
-11-RE	0	0	0	*-25-RA	1	0	0
-12	0	0	0	*-26	1	N/A	N/A
-12-RA	0	0	0	*-27	0	N/A	N/A
-12-RE	0	0	0	*-27-RA	0	N/A	N/A
-13	0	0	N/A	*-27-RE	0	N/A	N/A
-13-RA	0	0	N/A	*-28	0	0	N/A
-13-RE	0	0	N/A	*-28-RA	0	0	N/A
-14	1	N/A	N/A	*-28-RE	0	0	N/A
*-15	2	N/A	N/A	*-29	1	N/A	N/A
*-16	1	1	1	*-29-RA	1	N/A	N/A
*-16-RA	1	1	1	*-30	1	1	N/A
*-16-RE	1	1	1	*-30-RA	1	1	N/A

* PINS TO BE FLIPPED OPPOSITE OF SELECTIVE PLATING BEFORE BEING INSERTED



(SEE NOTE 12)
(SEE TABLE 7)

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING, RECORDING,
OR BY ANY INFORMATION STORAGE
AND RETRIEVAL SYSTEM, WITHOUT THE
WRITTEN CONSENT OF SAMTEC INC.

EXISPROD\ASSEMBLY
100\TSW-ASM4**samtec**520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322MADE BY:
KOLB 8-24-88TSW-XXX-XX-XXX-X-XX-XXX
SHEET 4 OF 4