



| ALL DIMENSIONS ARE IN (mm) |                     |            |                   |         |        |        |
|----------------------------|---------------------|------------|-------------------|---------|--------|--------|
| Part Number                | Wire Size           | Wire Class | Wire Strip Length | l ±2.76 | o ±.50 | i ±.50 |
| SCMSX10-C                  | 10 mm <sup>2</sup>  | 5f & 6f    | 19.0              | 35.0    | 7.20   | 5.50   |
| SCMSX16-C                  | 16 mm <sup>2</sup>  | 5f & 6f    | 26.0              | 49.0    | 9.10   | 6.90   |
| SCMSX25-L                  | 25 mm <sup>2</sup>  | 5f & 6f    | 19.5              | 36.0    | 10.40  | 8.20   |
| SCMSX35-L                  | 35 mm <sup>2</sup>  | 5f & 6f    | 30.0              | 57.0    | 12.70  | 9.80   |
| SCMSX50-L                  | 50 mm <sup>2</sup>  | 5f & 6f    | 27.5              | 52.0    | 14.20  | 11.50  |
| SCMSX70-L                  | 70 mm <sup>2</sup>  | 5f & 6f    | 28.5              | 54.0    | 17.40  | 13.50  |
| SCMSX95-Q                  | 95 mm <sup>2</sup>  | 5f & 6f    | 30.0              | 57.0    | 19.40  | 15.20  |
| SCMSX120-Q                 | 120 mm <sup>2</sup> | 5f & 6f    | 30.0              | 57.0    | 21.00  | 16.50  |
| SCMSX150-X                 | 150 mm <sup>2</sup> | 5f & 6f    | 32.0              | 61.0    | 23.00  | 18.60  |
| SCMSX185-X                 | 185 mm <sup>2</sup> | 5f & 6f    | 37.5              | 72.0    | 26.00  | 20.80  |
| SCMSX240-X                 | 240 mm <sup>2</sup> | 5f & 6f    | 39.0              | 75.0    | 29.00  | 23.50  |
| SCMSX300-5                 | 300 mm <sup>2</sup> | 5f         | 49.0              | 95.0    | 33.00  | 26.20  |

- NOTES:
1. Material: High conductivity seamless copper tube.
  2. Plating: Parts are annealed and tin plated.
  3. WireType: Class 5 and 6 Flexible Stranded Copper Conductor per DIN VDE 0295, IEC 60228, and HD 383.
  4. UL Listed & CSA Certified Wire Connectors for applications up to 35kv, when crimped per instruction sheet included with Panduit packaging. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
  5. UL & CSA Temperature Rating: 90°C

[illegible]