


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-08-004464	03MAR08	HMR	JR

1 STAMP AMP 16-14* APPROX AS SHOWN




AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
16-14 AWG STRANDED	16-14 AWG STRANDED	NOT CERTIFIED



36216
PART NO

MAX RECOMMENDED OPERATING TEMPERATURE	170° C MAX
VOLTAGE RATING	NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE	1.04-2.62mm ² [2,050-5,180] CIR MILLS STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN TA BRINKMAN 2-24-93		 Tyco Electronics Corporation Harrisburg, PA 17105-3608																		
DIMENSIONS: INCHES			CHK DA PATTERSON 2-24-93																				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD DE MILLER 2-24-93		NAME TERMINAL, SLOTTED RING TONGUE, BUDGET																	
	0 PLC ± -			PRODUCT SPEC																			
	1 PLC ± -			—																			
	2 PLC ± -			APPLICATION SPEC																			
	3 PLC ± -			—																			
4 PLC ± -			—		SIZE			CAGE CODE			DRAWING NO			RESTRICTED TO									
MATERIAL			FINISH			WEIGHT		A2		00779		C-36216		—									
COPPER PER ASTM B-152 ANNEALED			TIN PLATE 0.00254[.000100] MIN PER ASTM B-545.			CUSTOMER DRAWING						SCALE		8:1		SHEET		1 OF 1		REV		A1	