

## FEED-THROUGH STANDOFF FEET Panel Mount

For wire-to-wire connections in HVAC, appliance, equipment, power distribution and other industrial applications with restricted budget and space requirements.

Easy to use feed-through terminal strips are a cost-effective alternative to barrier strips or other types of terminal blocks. Simply strip the wire, insert, and tighten the screw. Eurostrips feature tubular screw clamps, with wire protectors, and recessed metal parts for finger protection. The stainless steel wire protectors exhibit excellent memory and the most effective connection.

Eurostrips described on this and the preceding page are available with standoff feet for increased wiring efficiency. They can be panel mounted or left to free float. Offered in easy-to-cut 12-pole strips, they can also be ordered precut with the required number of poles.

- Tubular screw clamp
- Panel mount or free float
- Housing material:
  - Polyamide 66/6
  - V-O flammability
- Color: opaque white
- Marking plates or factory imprinted

HE1H



Standoff feet with wire protector


HE4HN



Standoff feet with wire protector


|                        |                                                                                                                                                                      |           |                                                                                                                                                                         |           |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|
| Pole Spacing           | 8 mm                                                                                                                                                                 |           | 10 mm                                                                                                                                                                   |           |
| Mounting Hole Diameter | 3 mm                                                                                                                                                                 |           | 3.6 mm                                                                                                                                                                  |           |
| Stripping Length       | 5 mm                                                                                                                                                                 |           | 6 mm                                                                                                                                                                    |           |
| Approvals              |   |           |   |           |
| Wire Range             | 1-2.5 mm <sup>2</sup>                                                                                                                                                | 24-12 AWG | 2.5-4 mm <sup>2</sup>                                                                                                                                                   | 24-10 AWG |
| Voltage Rating         | 400 V                                                                                                                                                                | 600 V     | 400 V                                                                                                                                                                   | 600 V     |
| Current Rating         | 6 A                                                                                                                                                                  | 20 A      | 10 A                                                                                                                                                                    | 30 A      |
| Torque                 | 0.5 Nm                                                                                                                                                               | 4.4 lb-in | 0.8 Nm                                                                                                                                                                  | 7.0 lb-in |
| Other Approvals        |    |           |   |           |

| No. of Poles | Cat. No.   | Std. Pk. | Cat. No.    | Std. Pk. |
|--------------|------------|----------|-------------|----------|
| 2            | HE1HWPR/02 | 100      | HE4HNWPR/02 | 100      |
| 3            | HE1HWPR/03 | 100      | HE4HNWPR/03 | 100      |
| 4            | HE1HWPR/04 | 100      | HE4HNWPR/04 | 100      |
| 5            | HE1HWPR/05 | 100      | HE4HNWPR/05 | 100      |
| 6            | HE1HWPR/06 | 50       | HE4HNWPR/06 | 50       |
| 7            | HE1HWPR/07 | 50       | HE4HNWPR/07 | 50       |
| 8            | HE1HWPR/08 | 50       | HE4HNWPR/08 | 50       |
| 9            | HE1HWPR/09 | 50       | HE4HNWPR/09 | 50       |
| 10           | HE1HWPR/10 | 50       | HE4HNWPR/10 | 50       |
| 11           | HE1HWPR/11 | 50       | HE4HNWPR/11 | 50       |
| 12           | HE1HWPR/12 | 50       | HE4HNWPR/12 | 50       |



Dimensions mm

|          |                  |
|----------|------------------|
| A = 8.0  | I = 6.6          |
| B = M2.6 | J = 6.5          |
| C = 5.2  | K = 10.3         |
| D = 2.8  | L = 94 (12 pole) |
| E = Ø3   | M = 16           |
| F = Ø5   | N = 16.2         |
| G = 8.0  | O = 10.1         |
| H = Ø2.8 |                  |



Dimensions mm

|          |                   |
|----------|-------------------|
| A = 10.0 | I = 6.7           |
| B = M3   | J = 8.5           |
| C = 6.4  | K = 12.1          |
| D = 3.5  | L = 117 (12 pole) |
| E = Ø3.6 | M = 19.1          |
| F = Ø5.7 | N = 20            |
| G = 10.0 | O = 14.0          |
| H = Ø3.6 |                   |

HE6H



Standoff feet with wire protector

12 mm

4.2 mm

7 mm



4-6 mm<sup>2</sup>

20-10 AWG

400 V

600 V

16 A

40 A

0.8 Nm

7.0 lb-in



| Cat. No.   | Std. Pk. |
|------------|----------|
| HE6HWPR/02 | 100      |
| HE6HWPR/03 | 100      |
| HE6HWPR/04 | 100      |
| HE6HWPR/05 | 100      |
| HE6HWPR/06 | 50       |
| HE6HWPR/07 | 50       |
| HE6HWPR/08 | 50       |
| HE6HWPR/09 | 50       |
| HE6HWPR/10 | 25       |
| HE6HWPR/11 | 25       |
| HE6HWPR/12 | 25       |

HE10H



Standoff feet with wire protector

15 mm

4.3/5.7 mm

8.5 mm



6-10 mm<sup>2</sup>

18-8 AWG

400 V

600 V

25 A

50 A

1.2 Nm

10.6 lb-in



| Cat. No.    | Std. Pk. |
|-------------|----------|
| HE10HWPR/02 | 40       |
| HE10HWPR/03 | 40       |
| HE10HWPR/04 | 40       |
| HE10HWPR/05 | 40       |
| HE10HWPR/06 | 20       |
| HE10HWPR/07 | 20       |
| HE10HWPR/08 | 20       |
| HE10HWPR/09 | 10       |
| HE10HWPR/10 | 10       |
| HE10HWPR/11 | 10       |
| HE10HWPR/12 | 10       |

HE16H



Standoff feet with wire protector

15 mm

4.3/5.7 mm

8.5 mm



10-16 mm<sup>2</sup>

18-6 AWG

400 V

600 V

35-63 A


63 A

2.0 Nm

17.7 lb-in




| Cat. No.    | Std. Pk. |
|-------------|----------|
| HE16HWPR/02 | 40       |
| HE16HWPR/03 | 40       |
| HE16HWPR/04 | 40       |
| HE16HWPR/05 | 40       |
| HE16HWPR/06 | 20       |
| HE16HWPR/07 | 20       |
| HE16HWPR/08 | 20       |
| HE16HWPR/09 | 10       |
| HE16HWPR/10 | 10       |
| HE16HWPR/11 | 10       |
| HE16HWPR/12 | 10       |




Dimensions mm

|          |                   |
|----------|-------------------|
| A = 12.0 | I = 9             |
| B = M3.5 | J = 9.6           |
| C = 7.7  | K = 13.9          |
| D = 4.3  | L = 140 (12 pole) |
| E = Ø4.2 | M = 21.8          |
| F = Ø6.3 | N = 22.6          |
| G = 12.0 | O = 15            |
| H = Ø4.1 |                   |



Dimensions mm

|              |                   |
|--------------|-------------------|
| A = 15.0     | I = 10.7          |
| B = M4       | J = 11.3          |
| C = 9.3      | K = 17.5          |
| D = 5.7      | L = 175 (12 pole) |
| E = Ø4.3/5.7 | M = 27.8          |
| F = Ø8.2     | N = 25.1          |
| G = 15.0     | O = 16            |
| H = Ø5.0     |                   |



Dimensions mm

|              |                   |
|--------------|-------------------|
| A = 15.0     | I = 10.7          |
| B = M5       | J = 11.3          |
| C = 9.3      | K = 17.5          |
| D = 5.7      | L = 175 (12 pole) |
| E = Ø4.3/5.7 | M = 27.8          |
| F = Ø8.2     | N = 25.1          |
| G = 15.0     | O = 16            |
| H = Ø5.6     |                   |