




- △ COORDINATE DIMENSION APPLIES FROM BASIC LOCATION.
- △ 10 AND 14 POSITION SIZES CONTAIN ONLY ONE SLOT FOR SNAP-IN POLARIZER (MILITARY POLARIZATION) LOCATED AS SHOWN.
- △ 10 POSITION SIZES CONTAIN ONLY ONE SLOT FOR DUAL POLARIZATION, LOCATED AS SHOWN.
- △ 4 POSTS:
GOLD FLASH OVER
0.38μm [.000015] MIN PALLADIUM-NICKEL PLATE ON THE LOCALIZED PLATE AREA,
2.54μm [.000100] MIN TIN-LEAD PLATE ON THE SOLDER-TAIL,
1.27μm [.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
OR
0.38μm [.000015] MIN GOLD PLATE ON THE LOCALIZED PLATE AREA,
2.54μm [.000100] MIN TIN-LEAD PLATE ON THE SOLDER-TAIL,
1.27μm [.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- △ DISTANCE REQUIRED BY EJECTION LATCHES IN THE OPEN POSITION.
- △ HOUSING: GLASS FILLED NYLON OR POLYESTER, 94V-0 RATED, BLACK.
CONTACT: PHOSPHOR BRONZE OR BRASS.

60.96 [2.400]	72.64 [2.860]	82.80 [3.260]	78.74 [3.100]	68.58 [2.700]	50	1-111749-0
48.26 [1.900]	59.94 [2.360]	70.10 [2.760]	66.04 [2.600]	55.88 [2.200]	40	111749-9
40.64 [1.600]	52.32 [2.060]	62.48 [2.460]	58.42 [2.300]	48.26 [1.900]	34	111749-8
27.94 [1.100]	39.62 [1.560]	49.78 [1.960]	45.72 [1.800]	35.56 [1.400]	24	111749-5
22.86 [.900]	34.54 [1.360]	44.70 [1.760]	40.64 [1.600]	30.48 [1.200]	20	111749-4
15.24 [.600]	26.92 [1.060]	37.08 [1.460]	33.02 [1.300]	22.86 [.900]	14	111749-2
10.16 [.400]	21.84 [.860]	32.00 [1.260]	27.94 [1.100]	17.78 [.700]	10	111749-1
E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. REIFSNYDER 18 MAR 99		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK C. REIFSNYDER 18 MAR 99		NAME C. REIFSNYDER 18 MAR 99	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-40018		HEADER ASSEMBLY UNIVERSAL AMP LATCH	
MATERIAL		APPLICATION SPEC —		SIZE CODE/DRAWING NO A1 00779	
FINISH		WEIGHT —	RESTRICTED TO		REV B
CUSTOMER DRAWING		SCALE: 4:1	SHEET 1 OF 1		REV B