






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	ECO-05-007262	09JAN06	BSV	MM



- 1

.000030 ON CONTACT AREA, .000100-.000200 93/7 TIN LEAD IN CRIMP AREA "Z", ALL OVER .000050 NICKEL.
- 2

REELED FOR MINI APPLICATOR.
- 3

SHEARED EDGES PERMITTED TO BE UNPLATED.
- 4

.000015 GOLD IN AREA "K", .000100-.000200 BRIGHT TIN-LEAD IN AREA "Z", ALL OVER .000050 NICKEL.
- 5

.000015 GOLD IN CONTACT AREA, .000050 NICKEL ENTIRE CONTACT.
- 6

POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 7

.000030 ON CONTACT AREA, .000100-.000200 MATTE TIN IN CRIMP AREA "Z", ALL OVER .000050 NICKEL.

	LOOSE PIECE	3 7	5-102920-2
	—	3 7	5-102920-1
OBSOLETE	LOOSE PIECE	3 5	102920-8
OBSOLETE	—	3 5	102920-7
OBSOLETE	LOOSE PIECE	3 4	102920-5
OBSOLETE	—	3 4	102920-4
	LOOSE PIECE	3 1	102920-2
	—	3 1	102920-1
	REMARKS	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATE HELM 03MAY89	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608							
DIMENSIONS: INCHES		CHK C. OBERMAN 02JUN89	NAME CONTACT, MOD IV 1/2, RECEPTACLE, CRIMP SNAP-IN							
		APVD J. GESFORD 02JUN89								
		PRODUCT SPEC 108-25021								
MATERIAL CU-SN-P ALLOY 521 .008 THK COML		APPLICATION SPEC 114-25003	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
		WEIGHT -	A2	00779	C=102920	-				
SEE TABLE		CUSTOMER DRAWING			SCALE	10:1	SHEET	1 OF 1	REV	G