

# FLUKE®

## ScopeMeter® 190C, 190B, and 120 Series

### ScopeMeter 190C and 190B Series: Speed, performance and analysis power

For demanding applications, the ScopeMeter 190C and 190B Series high-performance oscilloscopes offer specifications usually found on top-end bench instruments. With up to 200 MHz bandwidth, 2.5 GS/s real time sampling and a deep memory of 27,500 points per input, they're ideal for engineers who need the full capabilities of a high-performance scope in a hand-held, battery powered instrument.

- Dual input - 200, 100 or 60 MHz bandwidth
- Up to 2.5 GS/s real time sampling per input

- High waveform resolution of 3000 datapoints per channel
- Frequency Spectrum using FFT analysis (190C)
- Connect-and-View™ automatic triggering, a full range of manual trigger modes plus external triggering
- Digital Persistence for analyzing complex, dynamic signals like on an analog oscilloscope (190C)
- Fast display update rate for seeing dynamic behavior instantaneously
- Automatic capture and replay of 100 screens
- 27,500 points and more per input record length using ScopeRecord™ mode



**Connect  
and  
View**

## Technical Data

- 1,000 V CAT II and 600 V CAT III safety certified
- Up to 1,000 V independently floating isolated inputs
- Four hours rechargeable NiMH battery pack

### ScopeMeter 120 Series: Three-in-one simplicity

The compact ScopeMeter 120 Series is the rugged solution for industrial troubleshooting and installation applications. It's a truly integrated test tool, with oscilloscope, multi-meter and "paperless" recorder in one affordable, easy-to-use instrument. Find fast answers to problems in machinery, instrumentation, control and power systems.

- A dual input 40 MHz or 20 MHz digital oscilloscope
- Two 5,000 counts true-rms digital multimeters
- Cursor measurements (Fluke 124, 125)
- A dual input TrendPlot recorder
- Connect-and-View trigger simplicity for hands-off operation
- Shielded test leads for oscilloscope, resistance, continuity and capacitance measurements
- Full bandwidth, VPS40 10:1 40 MHz probe included standard with Fluke 124, 125
- Up to seven hours battery operation
- 600 V CAT III safety certified
- Optically isolated RS-232 interface
- Rugged, compact case
- Bus Health test for industrial bus systems (Fluke 125)
- Power measurements and harmonics measurement (Fluke 125)

Now including the **NEW** ScopeMeter 125



# Technical specifications 190C and 190B Series

## Oscilloscope mode

### Vertical deflection

|           | Fluke 190C<br>Fluke 199B | Fluke 196C<br>Fluke 196B | Fluke 192B |
|-----------|--------------------------|--------------------------|------------|
| Bandwidth | 200 MHz                  | 100 MHz                  | 60 MHz     |
| Rise time | 1.7 ns                   | 3.5 ns                   | 5.8 ns     |

**Bandwidth limiter:** User selectable: 10 kHz, 20 MHz or off

**Number of inputs:** Two plus external trigger.

All inputs isolated from each other and ground.

**Input coupling:** AC or DC, with ground level indicator

**Input sensitivity:** 2 mV/div to 100 V/div (Fluke 190C Series); 5 mV/div to 100 V/div (Fluke 190B Series)

**Normal/invert:** On both input channels; switched separately

**Variable attenuator:** Variable gain on input channel A

**Input voltage:** 1000 V CAT II, 600 V CAT III rated—see “general specifications” for further details

**Vertical resolution:** 8 bit

**Accuracy:**  $\pm (1.5 \% \text{ of reading} + 0.04 \times \text{range/div})$

**Input impedance:**  $1 \text{ M}\Omega \pm 1 \% // 15 \text{ pF} \pm 2 \text{ pF}$

### Horizontal

|                               | Fluke 190C<br>Fluke 199B | Fluke 196C<br>Fluke 196B | Fluke 192B           |
|-------------------------------|--------------------------|--------------------------|----------------------|
| Maximum real-time sample rate | 2.5 GS/s                 | 1 GS/s                   | 500 MS/s             |
| Number of digitizers          | 2                        | 2                        | 2                    |
| Time base range               | 5 ns/div to 5 s/div      |                          | 10 ns/div to 5 s/div |

**Maximum record length:** 3000 points per input in Scope mode; 27,500 points per input in ScopeRecord™ roll mode (5 ms/div to 2 min/div)

**Accuracy:**  $\pm (0.01 \% \text{ of reading} + 1 \text{ pixel})$

**Glitch capture:** 50 nsec (at 5  $\mu\text{s/div}$  to 1 min/div); 250 nsec (at 2 min/div)

### Display and acquisition

|                   | Fluke 190C                                      | Fluke 190B            |
|-------------------|-------------------------------------------------|-----------------------|
| Display           | 144 mm Full color LCD                           | 144 mm Monochrome LCD |
| Display modes     | Input A, input B, dual, average, replay         |                       |
| Persistence modes | Digital persistence: short/medium/long/infinite | Persistence on / off  |

**Visible screen width:** 12 divisions

**Waveform mathematics:** A + B, A - B, A \* B, all with user selectable scaling of resultant; A versus B (X - Y mode); Frequency Spectrum using FFT analysis (190C only)

**Acquisition modes:** Normal, auto, single shot, ScopeRecord™ roll, glitch capture, waveform compare, waveform compare with automatic “Pass / Fail testing” (in 199C and 196C only)

### Trigger and delay

**Source:** Input A, input B, external trigger input. All input references isolated from each other and from ground

**Modes:** Automatic Connect-and-View™ free run, single shot, edge, delay, video, video line, selectable pulsewidth, dual slope (190C only), N-cycle (190C only)

**Connect-and-View™:** Advanced automatic triggering that recognizes signal patterns, automatically sets up and continuously adjusts triggering, time base and amplitude. Automatically displays stable waveforms of complex and dynamic signals like motor drive and control signals.

**Video triggering:** NTSC, PAL, PAL+, SECAM. Includes field 1, field 2 and line select.

**Pulse width triggering:** Pulse width qualified by time. Allows for triggering  $<t$ ,  $>t$ ,  $=t$ ,  $\neq t$ , where t is selectable in minimal steps of 0.01 div. or 50 nsec.

**Time delay:** One full screen of pre-trigger view or up to 100 screens (= 1200 divisions) of post-trigger delay

**Dual slope triggering:** Both rising and falling transitions, when crossing the trigger level, initiate an acquisition (190C only)

**N-cycle triggering:** Triggers on N-th occurrence of a trigger event; N to be set in the range 2 to 99 (190C only)

### Automatic capture of 100 screens

The instrument ALWAYS memorizes the last 100 screens (no user setup required). When an anomaly occurs on screen, the REPLAY button can be pressed to review the full screen sequence over and over.

Instrument can be set up for triggering on glitches or intermittent anomalies and will operate in “baby-sit” mode and will capture 100 events.

Alternatively, the 199C and 196C can be set up in waveform compare mode to store only matching (“Pass”) or only non-matching (“Fail”) acquired waveforms in the replay memory bank for further analysis.

**Replay:** Manual or continuous replay. Displays the captured 100 screens as a “live” animation or under manual control. Each screen has date- and time-stamp.

**Replay storage:** Up to 2 sets of 100 screens each can be saved for later recall and analysis

### FFT – Frequency Spectrum Analysis (190C only)

Shows frequency content of oscilloscope waveform using Fast Fourier Transform

**Window:** Automatic, Hamming, Hanning or None

**Automatic window:** Digitally re-samples acquired waveform to get optimum frequency resolution in FFT resultant

**Vertical scale:** Linear/logarithmic, in volts

**Frequency axis:** Logarithmic; frequency range automatically set as function of timebase range of oscilloscope

### Waveform compare and pass/fail testing

**Waveform compare:** Provides storage and display of a reference waveform for visual comparison with newly acquired waveforms. Reference is derived from an acquired waveform and can be modified in the ScopeMeter or externally using FlukeView® Software.

**Pass/Fail Testing (199C, 196C):** In waveform compare mode, the Color Scopemeter can be set up to store only matching (“Pass”) or only non-matching (“Fail”) acquired waveforms in the replay memory bank for further analysis.

### Automatic scope measurements

Vdc, Vac rms, Vac+dc, Vpeak max, Vpeak min, Vpeak to peak, Aac, Adc, Aac+dc, frequency (Hz), risetime, fall-time, power factor, Watts, VA, VA reactive, phase, pulse width (pos/neg), duty cycle (pos/neg), temperature °C, temperature °F, dBV, dBm into 50  $\Omega$  and 600  $\Omega$

Vpwm ac, Vpwm ac+dc for measurement on pulse width modulated motor drives and frequency inverters

## Cursor measurements

**Source:** Input A, input B or the mathematical result trace (excluding A vs B curve)

**Dual horizontal lines:** Voltage at cursor 1 and 2, voltage between cursors

**Dual vertical lines:** Time between cursors, 1/T between cursors (in Hz), voltage between markers, risetime with markers, falltime with markers; Vrms between cursors (190C only), watts between cursors (190C only)

**Single vertical line:** Min-Max and Average voltage at cursor position; frequency and rms-value of individual frequency component in FFT result (190C only)

## Zoom

Up to 16x horizontal zoom

## Recorder mode

### ScopeRecord – roll mode

Dual input waveform storage mode

**Source and display:** Input A, input B, dual

**Memory depth:** 27,500 points per input. Each point consists of Min-Max pair

**Min-Max values:** Min-Max values are measured at high sample rates ensuring capture and display of glitches

| Time base range   | 5 ms/div to 1 min/div | 2 min/div |
|-------------------|-----------------------|-----------|
| Recorded timespan | 6 sec to 24 hr        | 48 hr     |
| Glitch capture    | 50 ns                 | 250 ns    |
| Sample rate       | 20 MS/s               | 4 MS/s    |
| Resolution        | 200 µsec to 2 sec     | 4.8 sec   |

**Recording modes:** Single sweep, continuous roll, Start-on-Trigger, Stop-on-Trigger

**Stop-on-Trigger (through external):** ScopeRecord mode can be stopped by an individual trigger event, or by an interruption of a repetitive trigger signal

**Horizontal scale:** Time from start, time of day

**Zoom:** Up to 100x

**Memory:** Up to 2 dual input ScopeRecord waveforms can be saved for later recall and analysis

### TrendPlot™ recording

Single or dual input electronic paperless chart recorder. Plots, displays and stores meter and scope measurements.

**Source and display:** Input A, input B or DMM input

**Memory depth:** 18,000 points recording. Per record point a minimum, a maximum and an average value, plus a date and timestamp are recorded.

**Ranges:** 5 s/div to 30 min/div in normal view mode; 5 min/div to 48 hr/div in view all mode, giving overview of total record

**Recorded timespan:** Up to 22 days with a resolution of 1 minute

**Recording mode:** Continuous roll for the duration of the full recordable timespan

**Measurement speed:** 5 measurements per second

**Horizontal scale:** Time from start, time of day

**Zoom:** Up to 64x zoom

**Memory:** Up to 2 TrendPlot recordings can be saved for later recall and analysis

## Cursor measurements – all recorder modes

**Source:** Input A, B or DMM input

**Dual vertical lines:** Min-Max or Average voltage. Time between cursors

**Single vertical line:** Min-Max or Average voltage. Absolute date and time or time from start

## Meter mode

Via 4 mm banana inputs. Fully isolated from scope inputs and scope ground. The specified accuracy is valid over the temperature range 18 °C to 28 °C (65 °F to 82 °F). Add 10 % of specified accuracy for each degree C below 18 °C or above 28 °C.

**Maximum resolution:** 5,000 counts

**Voltmeter ranges:** 500 mV, 5 V, 50 V, 500 V, 1,000 V

**Accuracy:**

Vdc ± (0.5 % + 5 counts)

Vac true rms

15 Hz to 60 Hz: ± (1 % + 10 counts)

60 Hz to 1 kHz: ± (2.5 % + 15 counts)

Vac+dc true rms

dc to 60 Hz: ± (1 % + 10 counts)

60 Hz to 1 kHz: ± (2.5 % + 15 counts)

**Ohms:**

Ranges: 500 Ω, 5 kΩ, 50 kΩ, 500 kΩ, 5 MΩ, 30 MΩ

Accuracy: ± (0.6 % + 5 counts)

## Other meter functions

**Continuity:** Beeper on < 50 Ω (± 30 Ω)

**Diode test:** Up to 2.8 V

**Amps:** Adc, Aac, Aac+dc using an optional current clamp or shunt. Scaling factors: 0.1 mV/A ... 100 V/A

**Temperature (°C, °F):** With optional accessories. Scale factors 1 mV/°C or 1 mV/°F

**Input impedance:** 1 MΩ ± 1 % // 10 pF ± 2 pF

**Advanced meter functions:** Auto/manual ranging, relative measurements (zero reference), TrendPlot recording

## General specifications

### Memory save and recall

**Scope memories:** 10 memory locations that each can contain two waveforms plus corresponding setup

**Recorder memories:** 2 memory locations that each can contain 100 captured dual input scope screens, or a dual input ScopeRecord (27,500 Min-Max pairs per input), or a dual input Trendplot (18,000 min-max pairs + average values)

### Real-time clock

Time and date stamp for ScopeRecord, 100 captured screens and TrendPlots

### Mechanical data

**Size:** 256 x 169 x 64 mm (10.1 x 6.6 x 2.5 in)

**Weight:** 2 kg (4.4 lbs)

### Case

**Design:** Rugged, shock proof with integrated protective holster

**Drip and dust proof:** IP51 according to IEC529

**Shock and vibration:** Shock 30 g, vibration

|            | Fluke 190C                            | Fluke 190B                         |
|------------|---------------------------------------|------------------------------------|
| Display    | Bright full-color LCD with backlight, | Bright LCD with backlight          |
| Brightness | 80 Cd/m² typ. using power adapter     | 125 Cd/m² typ. using power adapter |

(sinusoidal) 3 g according to MIL-PRF-28800F Class 2

**Display size:** 115.2 mm x 86.4 mm (4.54 in x 3.4 in)

**Resolution:** 320 x 240 pixels

**Contrast and brightness:** User adjustable, temperature compensated

## Power

**Line power:** Country-specific line voltage adapter/battery charger included

**Battery power:** Rechargeable NiMH (installed)

**Battery operating time:** 4 hours

**Battery charging time:** 4 hours

**Battery power saving functions:** Auto power down with adjustable power down time. On-screen battery status indicator.

## Safety

### Compliance:

EN61010-1-2001, Pollution degree 2;

UL 3111-1, with approval;

CAN/CSA C22.2, No. 61010-1-04, with approval;

ANSI/ISA-82.02.01

## Input voltage ratings

**Maximum probe voltage:** 1000 V CAT II/600 V CAT III (Maximum voltage between 10:1 probe tip [VPS200] and reference lead)

**Floating voltage:** 1000 V CAT II/600 V CAT III (Maximum voltage between earth ground and any terminal [signal input or shielding])

### Independently isolated inputs:

1000 V CAT II/600 V CAT III

(Maximum voltage between any terminal of one input or probe [VPS200] and any other terminal of another input or probe [VPS200])

**Maximum voltage on BNC input directly (input A or B):** 300 V CAT III

**Maximum voltage on meter input:**

1,000 V CAT II/600 V CAT III

## Environmental

**Operating temperature:** 0 °C to +50 °C

**Storage temperature:** -20 °C to +60 °C

## Humidity:

10 °C to 30 °C: 95% RH non condensing

30 °C to 40 °C: 75% RH non condensing

40 °C to 50 °C: 45% RH non condensing

**Maximum operating altitude:** 3,000 m (10,000 feet)

**Maximum storage altitude:** 12 km (40,000 feet)

**Electro-Magnetic-Compatibility (EMC):** EN 61326-1 for emission and immunity

## Optically-isolated PC/printer interface

**PC communication:** Transfer instrument settings, screen images, waveform data and waveform references, compatible with FlukeView® software for Windows® via optional PM9080.

**To printer:** Supports HP Laserjet®, DeskJet, Epson FX/LQ, Seiko DPU-414 and Postscript printers via optional PAC 91

## Warranty

Three-years, parts and labor on mainframe instrument  
One-year on accessories

## Accessories

| Standard accessories                  | Fluke 199C, Fluke 196C, Fluke 199B, Fluke 196B, Fluke 192B                                                                                                                                |
|---------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rechargeable battery pack (installed) | BP190                                                                                                                                                                                     |
| Line voltage adapter/battery charger  | BC190                                                                                                                                                                                     |
| Voltage probes and accessories        | 10:1 voltage probe (VPS200, 1 red + 1 grey) including hook clip, ground lead with mini alligator clip, ground lead with hook clip, 4 mm add-on probe tip, ground lead to 4 mm banana plug |
| Multimeter test leads                 | TL75 Hard Point test lead set (1 red, 1 black)                                                                                                                                            |
| User manual                           | 10 language versions on CD-ROM, "Getting Started" booklet included with instrument                                                                                                        |

# Technical specifications 120 Series

## Oscilloscope mode

### Vertical deflection

| Bandwidth and risetime               | Fluke 125, 124 | Fluke 123 |
|--------------------------------------|----------------|-----------|
| Bandwidth (risetime)                 |                |           |
| • with VPS40 probes                  | 40 MHz         | 20 MHz    |
| • input A and B directly             | 40 MHz         | 20 MHz    |
| • with STL120 Shielded Test Leads    | 12.5 MHz       | 12.5 MHz  |
| Instrument risetime (input directly) | 8.75 ns        | 17.5 ns   |

**Number of inputs:** 2

**Input coupling:** AC, DC with ground level indicator

**Input sensitivity:** 5 mV to 500 V/div (with the included VPS40 (Fluke 125, 124) and STL120 shielded test leads measure up to 600 Vrms, CAT III)

**Input voltage:** 600 V CAT III. See "general specifications" for more detailed information.

**Vertical resolution:** 8 bit

**Accuracy:**  $\pm (1 \% \text{ of reading} + 0.05 \times \text{range/div})$

**Input impedance:**  $1 \text{ M}\Omega \pm 1 \% // 225 \text{ pF}$  with STL120 shielded test leads;  $1 \text{ M}\Omega \pm 1 \% // 20 \text{ pF} \pm 3 \text{ pF}$  with BB120;  $5 \text{ M}\Omega \pm 1 \% // 15.5 \text{ pF}$  with VPS40, 10:1 Voltage probe

## Horizontal

**Max. sample rate (both channels simultaneously):**

Fluke 125, 124: 2.5 GS/s for repetitive signals;

25 MS/s for single shot

Fluke 123: 1.25 GS/s for repetitive signals; 25 MS/s for single shot

**Number of digitizers:** 2

**Time base range:** 10 ns/div to 1 min/div; 20 ns/div to 1 min/div (Fluke 123)

**Maximum record length:** 512 Min-Max points per input

**Accuracy:**  $\pm (0.1 \% \text{ of reading} + 1 \text{ pixel})$

**Glitch detect:** 40 ns

## Display and acquisition

**Display modes:** Input A, input A and B, envelope, smooth

**Acquisition modes:** Normal (including glitch capture), single shot, roll

## Trigger and delay

**Source:** Input A, input B, external via optional ITP120

**Modes:** Automatic Connect-and-View, Free Run, Edge, Single Shot, Video, Video Line

**Connect-and-View:** Advanced automatic triggering that recognizes signal patterns and automatically sets up and continuously adjusts triggering, time base and amplitude. Automatically displays stable pictures of complex and dynamic signals like motor drive and control signals

**Video triggering:** NTSC, PAL, PAL+, SECAM. Includes line select

**Time delay:** Up to 10 divisions pre-trigger view

## Measurements

Vdc, Vac, Vac+dc, Vpeak max, Vpeak min, Vpeak to peak, frequency (Hz), positive pulse width, negative pulse width, positive duty cycle, negative duty cycle, Amp ac, Amp dc, Amp ac+dc, Phase, Temperature °C, Temperature °F, dBV, dBm into 50 Ω and 600 Ω. (Amps, °C or °F with optional probes)

## Cursor measurements (125, 124)

**Sources:** Input A, Input B

**Modes:** Single or dual vertical cursor, dual horizontal cursor, risetime or falltime

**Measurements:**

Single vertical line: Average, min value, max value, time from start of recording in roll mode

Dual vertical lines: ΔV at markers, time between cursors, 1/T between cursors (in Hz)

Dual horizontal lines: High, low or ΔV – readout, risetime and falltime: transition time, 0 %-level, 100 %-level, with markers at 10 % and 90 %

**Accuracy:** As oscilloscope

## Bus health tester (Fluke 125 only)

Bus health automatically analyzes the electrical signals on the network to give waveform data and measure individual parameters. Automatic comparison of the measurement results to the standards results in “good” or “false” indicators to be displayed per parameter.

**Bus types and reference standards used:**

AS-i (EN50295, 166 kb/s)®;

CAN-bus (ISO-11898, up to 1 Mb/s);

Interbus S (EIA-485, up to 10 Mb/s)®;

ControlNet (61158 type 2, 2.5 Mb/s)®;

Modbus (EIA-232, up to 115 kb/s and

EIA-485, up to 10 Mb/s)®;

Foundation Fieldbus H1 (61158 type 1, 31.25 kb/s)

and H2 (61158 type 1, up to 10 Mb/s);

Profibus DP (EIA-485, up to 10 Mb/s) and

PA (61158 type 1, 31.25 kb/s);

Ethernet [10Base2 (coaxial) and 10BaseT (UTP)], 10 Mb/s;

RS-232 (EIA-232, up to 115 kb/s);

RS-485 (EIA-485, up to 10 Mb/s);

or user defined system

**Measured parameters:** Baud rate, risetime, falltime, high level, low level, distortion, amplitude and jitter, with comparison to system’s standard values

## Power measurements (Fluke 125 only)

**Measure types:** Watt, VA, VAR, Power Factor (PF)

**Power configuration:** Single phase or balanced

3-phase (delta-configuration) mains supply

**Voltage measurement:** Channel A, using STL120, voltage probe or direct input

**Current measurement:** Channel B, using i400s

current clamp (included) or other compatible clamp

**Current clamp sensitivity:** 0.1/1/10/100/1000 mV/A, 10 mV/mA and 400 mV/A

## Harmonics mode (Fluke 125 only)

Converts waveform information into a harmonics display (using FFT processing), which shows the relative amplitudes of the 1st up to the 33rd harmonic

**Harmonics frequency range:** DC to 33rd harmonic (fundamental ≤ 60 Hz); DC to 24th (fundamental ≤ 400 Hz)

**Analyzed waveform:** Voltage waveform (Ch.A), current waveform (Ch.B) or power (Ch.A x Ch.B), automatically generated

**Display:** Bargraph showing 1st up to 33rd harmonic, amplitude displayed in % relative to fundamental

**Timebase setting:** 5 ms/div.

**Measurements:** Relative amplitude of individual harmonic; THD in % or %f

## Dual input meter

The specified accuracy is valid over the temperature range 18 °C to 28 °C (64 °F to 82 °F). Add 10 % of specified accuracy for each °C below 18 °C or above 28 °C (64 °F to 82 °F)

**Max. meter bandwidth:** 40 MHz (Fluke 125, 124), 20 MHz (Fluke 123)

## Voltage measurements

**Measurement selection:** Vdc, Vac rms, Vac+dc rms, Vpeak max, Vpeak min, V<sub>pk-pk</sub>

**Ranges:** 500 mV, 5 V, 50 V, 500 V, 1250 V

**Full scale reading:** 5,000 counts

**Accuracy**

**Vdc:** ± (0.5 % + 5 counts)

**Vac rms:**

1 Hz to 60 Hz: ± (1 % + 10 counts)

60 Hz to 1 kHz: ± (2.5 % + 15 counts)

20 kHz to 1 MHz: ± (5 % + 20 counts)

**Vac+dc true-rms:**

DC to 60 Hz: ± (1 % + 10 counts)

60 Hz to 1 kHz: ± (2.5 % + 15 counts)

20 kHz to 1 MHz: ± (5 % + 20 counts)

**Vpeak:**

Max peak or Min peak: 5 % of full scale

Peak-to-peak: 10 % of full scale

## Ohms

**Ranges:** 500 Ω, 5 kΩ, 50 kΩ, 500 kΩ, 5 MΩ, 30 MΩ (all models), 50.00 Ω (Fluke 125 only)

**Max. resolution:** 5,000 counts

**Accuracy:** ± (0.6 % of reading + 5 counts)

## Capacitance

**Ranges:** 50 nF to 500 μF

**Max. resolution:** 5,000 counts

**Accuracy:** ± (2 % of reading + 10 counts)

## Other meter functions

**Frequency:** Up to 70 MHz (Fluke 125, 124) or up to 40 MHz (Fluke 123)

**Rotational speed (RPM):** Revolutions per minute, based on 1, 2 or 4 or 8 pulses per 2 revolutions (Fluke 125 only)

**Max. RPM reading:** 50 kRPM

**Continuity:** Beeper on < 30 Ω

**Diode test:** Up to 2.8 V

**Amps:** Amp dc, Amp ac, Amp ac+dc using an optional current clamp or shunt. Scaling factors: 0.1 mV/Amp to 100 V/Amp

**Duty cycle:** 2 % to 98 %, up to 30 MHz  
**Temperature (°C, °F):** With optional accessories. Scale factors 1 mV/°C or 1 mV/°F  
**Number of inputs:** 2  
**Input impedance:** 1 MΩ ± 1 % // 10 pF ± 2 pF  
**Advanced meter functions:** Auto/manual ranging, TouchHold®, Relative measurements (zero reference), TrendPlot recording

## Recorder mode

### Trendplot recording

Dual input electronic paperless chart recorder. Plots and displays the actual, minimum, maximum and average of any measurement.  
**Source and display:** Input A, input A and B  
**Range:** 15 s/div to 2 days per division (automatic)  
**Recorded timespan:** Up to 16 days with a resolution of 1.5 hours  
**Recording mode:** Continuous with automatic vertical scaling and horizontal time compression  
**Measurement speed:** 2.5 measurements per second maximum  
**Horizontal scale:** Time from start

## General specifications

### Case

**Design:** Rugged, shock proof with integrated protective holster  
**Drip and dust proof:** IP51 according to IEC529  
**Shock and vibration:** Shock 30 g according to MIL-PRF-28800F, Class 2, par. 3.8.4.2 and 4.5.5.3.1  
**Shock and vibration:** Vibration 3 g according to MIL-PRF-28800F, Class 2, par. 3.8.5.1 and 4.5.5.4.1

### Display

Bright LCD with CCFL backlight, 60 (35) cd/m<sup>2</sup> with (without) power adapter  
**Size:** 72 x 72 mm (2.8 x 2.8 inch)  
**Resolution:** 240 x 240 pixels  
**Contrast and brightness:** User adjustable, temperature compensated

### Memory save and recall

20 (10 in Fluke 123) instrument screens with user set-ups and user text

### Real-time clock

Time and date stamp TrendPlot recording

### Power

**Line power:** Country-specific line voltage adapter/battery charger included  
**Battery power:** Rechargeable Ni-MH BP120MH (installed)  
**Battery operating time:** Up to 7 hours using BP120MH  
**Battery charging time:** 7 hours  
**Battery power saving functions:** Auto power down with adjustable power down time. On-screen battery power indicator

## Mechanical data

**Size:** 50 x 115 x 232 mm (2 x 4.5 x 9.1 in)  
**Weight:** 1.2 kg (2.64 lbs)

## Safety

**Compliance:**  
 EN61010-1-2001, Pollution degree 2;  
 UL 3111-1;  
 CAN/CSA C22.2, No. 61010-1-04, including cCSA-US-approval;  
 ANSI/ISA-82.02.01

## Input voltage ratings

**Maximum input voltage:** 600 V CAT III  
 (Maximum voltage between input and reference lead)  
**Maximum input voltage using VPS40 Probe:**  
 600 V CAT III, 1000 V CAT II (Maximum voltage between probe tip input and reference lead)  
**Floating voltage:** 600 V CAT III  
 (Maximum voltage between earth ground and any terminal [signal input or reference lead])  
**Maximum voltage between reference leads:**  
 Instrument has common grounds connected via self recovering fault protection. For different ground potential measurements between inputs, use DP120 differential voltage probe

## Environmental

**According to MIL-PRF-28800F, Class 2**

**Operating temperature:** 0 °C to +50 °C  
**Storage temperature:** -20 °C to +60 °C  
**Humidity:**  
 10 °C to 30 °C, 95% RH non condensing;  
 30 °C to 40 °C, 75% RH non condensing;  
 40 °C to 50 °C, 45% RH non condensing  
**Maximum operating altitude:** 2,000 m (6,500 feet);  
 3,000 m (10,000 feet) voltages ≤ 400 V  
**Maximum storage altitude:** 12 km (40,000 feet)  
**Electro-Magnetic-Compatibility (EMC):**  
 EN61326-1 for emissions and immunity

## Optically isolated PC/printer interface

To printer: Supports HP Laserjet®, Deskjet®, Epson FX/LQ and postscript printers via optional PAC91  
 To PC: Transfer instrument settings, screen images and data, compatible with FlukeView® software for Windows® via optional PM9080

## Warranty


Three-years (parts and labor) on main instrument  
 One-year on accessories

## Accessories

| Standard accessories                  | Fluke 125, Fluke 124, Fluke 123                                                                                                                                                                                                       |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rechargeable battery pack (installed) | BP120MH                                                                                                                                                                                                                               |
| Line voltage adapter/battery charger  | PM8907                                                                                                                                                                                                                                |
| Voltage probes and accessories        | STL120 Shielded Test lead set; VPS40 high impedance 10:1 probe, 40 MHz (1 black, included with Fluke 125, 124); HC120 hook clips; ground leads with mini alligator clips; AC120 alligator clips; BB120 BNC-to-Shielded banana adapter |
| Multimeter test leads                 | TL75 Hard Point test lead set (1 black)                                                                                                                                                                                               |
| Current clamp                         | i400s Current Clamp (included with Fluke 125 only)                                                                                                                                                                                    |
| User manual                           | 15 language versions on CD-ROM, "Getting Started" booklet included with instrument                                                                                                                                                    |

# International safety standards

| Measurement voltage category | Summary description                                                                                                                                                                                                                                                                                                                    |
|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAT IV                       | Three phase at utility connection, any outdoor conductors (under 1,000 V) <ul style="list-style-type: none"> <li>• Outside and service entrance</li> <li>• Service drop from pole to building</li> <li>• Run between meter and panel</li> <li>• Overhead line to detached building</li> <li>• Underground line to well pump</li> </ul> |
| CAT III                      | Three-phase distribution (under 1,000 V), including single phase commercial lighting and distribution panels <ul style="list-style-type: none"> <li>• Feeders and short branch circuits</li> <li>• Distribution panel devices</li> <li>• Heavy appliance outlets with "short" connections to service entrance</li> </ul>               |
| CAT II                       | Single-phase receptable connected loads <ul style="list-style-type: none"> <li>• Outlets and long branch circuits</li> <li>• All outlets at more than 10 m (30 ft) from Category III source</li> <li>• All outlets at more than 20 m (60 ft) from Category IV source</li> </ul>                                                        |
| CAT I                        | Electronic <ul style="list-style-type: none"> <li>• Electronic equipment</li> <li>• Low energy equipment with transient limiting protection</li> </ul>                                                                                                                                                                                 |



To protect your instrument and—more importantly—yourself, choose a test tool that can withstand the electrical hazards present in the environment in which you plan to use it.

EN61010 establishes international safety requirements for electrical measurement equipment. It separates the various electrical environments into installation categories based on the danger from

high-voltage energy transients. To choose the right tool, the voltage rating alone does not determine the safety. It is the combination of voltage rating and installation category that determines maximum transient withstand capability of the tool. CAT III rated instruments are recommended for measurement on industrial power distribution systems.

## FlukeView® ScopeMeter® Software for Windows®

### FlukeView software adds PC power to your Fluke ScopeMeter Test Tools.

FlukeView ScopeMeter software helps you get more out of your ScopeMeter:

- Store instrument's screen copies on the PC, in color (with Fluke 190C Series) or in black and white (Fluke 190B and 120 Series)
- Copy color screen images into your reports and documentation (color screen images with Fluke 190C Series only)
- Capture and store waveform data from your ScopeMeter on your PC
- Create and archive waveform references for automatic (Fluke 190C Series) or visual (Fluke 190B and 190C Series) comparison
- Use cursors for parameter measurement
- Includes waveform analysis, e.g., FFT spectrum analysis
- Copy waveform data into your spreadsheet for detailed analysis
- Extended recording of up to four user-selected measurements help you monitor and analyze slow moving signals and related events
- Logging of other readings directly into other application programs, e.g., spreadsheet
- Add user text to instrument setups and send these to the instrument for operator reference and instructions

- Capture complete replay sequence into the PC for further analysis and documentation
- English, French and German versions included on a single CD-ROM

Note: Some functionality may be available with specific ScopeMeter models only

### System requirements

- Pentium 90 or better
- CD-ROM drive
- Windows® 95/98/Me/NT 4.0/2000/XP
- One free RS232 port or USB port
- PM9080 optically isolated RS232 adapter/cable, or:
- OC4USB optically isolated USB interface adapter/cable, available separately or included in SCC120/SCC190 kit and in ScopeMeter "S" versions

### Supported instruments

Full support for Fluke 199C, 199B, 199, 196C, 196B, 196, 192B, 192, 125, 124, 123



## Selection guide

|                                                          | Color ScopeMeter 190C Series                                                                                                                        |            | ScopeMeter 190B Series |            |                        | ScopeMeter 120 Series                                 |                                     |                           |
|----------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|------------|------------------------|------------|------------------------|-------------------------------------------------------|-------------------------------------|---------------------------|
|                                                          | Fluke 199C                                                                                                                                          | Fluke 196C | Fluke 199B             | Fluke 196B | Fluke 192B             | Fluke 125                                             | Fluke 124                           | Fluke 123                 |
| Bandwidth                                                | 200 MHz                                                                                                                                             | 100 MHz    | 200 MHz                | 100 MHz    | 60 MHz                 | 40 MHz                                                | 40 MHz                              | 20 MHz                    |
| Max real time sample rate                                | 2.5 GS/s                                                                                                                                            | 1 GS/s     | 2.5 GS/s               | 1 GS/s     | 500 MS/s               | 25 MS/s                                               | 25 MS/s                             | 25 MS/s                   |
| Max equivalent time sample rate                          | —                                                                                                                                                   | —          | —                      | —          | —                      | 2.5 GS/s                                              | 2.5 GS/s                            | 1.25 GS/s                 |
| Display                                                  | 14.4 cm full color LCD                                                                                                                              |            | 14.4 cm monochrome LCD |            |                        | 10.2 cm monochrome LCD                                |                                     |                           |
| Digital persistence                                      | Yes, gives analog oscilloscope like waveform decay (user selectable)                                                                                |            | —                      |            |                        | —                                                     |                                     |                           |
| Envelope mode                                            | Yes                                                                                                                                                 |            | Yes                    |            |                        | Yes                                                   |                                     |                           |
| Waveform compare                                         | Visual reference and automatic 'Pass / Fail' testing                                                                                                |            | Visual reference       |            |                        | —                                                     |                                     |                           |
| Max record length in Scope Mode:<br>in ScopeRecord mode: | 3000 points per input channel, allowing for high time resolution signal analysis using zoom 27,000 points per input or more (5 ms/div to 2 min/div) |            |                        |            |                        | 512 min/max points per input                          |                                     |                           |
| Number of inputs                                         | 2 plus external/DMM input, all isolated from each other and from ground                                                                             |            |                        |            |                        | 2                                                     |                                     |                           |
| Number of digitizers                                     | 2                                                                                                                                                   |            |                        |            |                        | 2                                                     |                                     |                           |
| Independently floating isolated inputs                   | Up to 1000 V between inputs, references and ground                                                                                                  |            |                        |            |                        | —                                                     |                                     |                           |
| Input sensitivity                                        | 2 mV/div to 100 V/div                                                                                                                               |            | 5 mV/div. to 100 V/div |            |                        | 5 mV/div to 500 V/div                                 |                                     |                           |
| Glitch capture                                           | Up to 3 ns using pulse width triggering; 50 µs peak detect at 5 ms/div to 1 min/div                                                                 |            |                        |            |                        | 40 ns                                                 |                                     |                           |
| Timebase range in Scope mode                             | 5 ns/div to 2 min/div                                                                                                                               |            |                        |            | 10 ns/div to 2 min/div | 10 ns/div to 1 min/div                                |                                     | 20 ns/div to 1 min/div    |
| Trigger types                                            | Connect-and-View™, Free Run, Single Shot, Edge, Delay, Video Frame, Video Line Selectable pulse width and external                                  |            |                        |            |                        | Connect-and-View™, Free Run, Single Shot, Edge, Video |                                     |                           |
|                                                          | Dual Slope trigger and Event trigger (n-cycle)                                                                                                      |            | —                      |            |                        |                                                       |                                     |                           |
| Scope measurements                                       | 7 cursor measurements, 30 automatic measurements                                                                                                    |            |                        |            |                        | As 124 + Power, VA, VAR, PF, RPM, Vpwm; THD           | cursors + 26 automatic measurements | 26 automatic measurements |
|                                                          | Automatic Vrms and watts measurement on cursor limited part of waveform                                                                             |            | —                      |            |                        |                                                       |                                     |                           |
| Bus health test function                                 | —                                                                                                                                                   |            |                        |            |                        | For standard industry buses                           | —                                   |                           |
| Waveform mathematics                                     | A + B, A - B, A x B, A versus B (X-Y-mode, giving Lissajous diagrams)                                                                               |            |                        |            |                        | Harmonics mode                                        | —                                   |                           |
|                                                          | + Frequency Spectrum (FFT)                                                                                                                          |            | —                      |            |                        |                                                       |                                     |                           |
| Power measurements                                       | P (W), VA, VAR, PF                                                                                                                                  |            |                        |            |                        | Power, VA, VAR, PF, Vpwm                              | —                                   |                           |
| ScopeRecord trigger modes                                | Start on trigger, stop on trigger, stop in absence of trigger signal                                                                                |            |                        |            |                        | —                                                     |                                     |                           |
| Capture last 100 screens                                 | Automatic, with replay capability                                                                                                                   |            |                        |            |                        | —                                                     |                                     |                           |
| Dual input TrendPlot                                     | Yes, with cursors and zoom                                                                                                                          |            |                        |            |                        | Yes, with cursors                                     |                                     | Yes                       |
| Memory for screens and set-ups                           | 10 screens with set-up; 5 more memories are made available upon registration of the ScopeMeter                                                      |            |                        |            |                        | 20                                                    |                                     | 10                        |
| Memory for recordings                                    | Two, each can store 100 scope screens, a ScopeRecord or a TrendPlot                                                                                 |            |                        |            |                        |                                                       |                                     |                           |
| True-rms multimeter                                      | 5000 counts, Volts, Amps, Ohms, Continuity, Diode, Temp                                                                                             |            |                        |            |                        | Dual fully featured 5000 counts DMM                   |                                     |                           |
| Safety certified (EN61010-1)                             | 1000 V CAT II / 600 V CAT III (instrument and included accessories)                                                                                 |            |                        |            |                        | 600 V CAT III (instrument and included accessories)   |                                     |                           |
| Battery (installed)                                      | 4 hr Ni-MH (BP190MH)                                                                                                                                |            |                        |            |                        | 7 hr Ni-MH (BP120MH)                                  |                                     |                           |
| Line Power                                               | Adapter/battery-charger included (BC190)                                                                                                            |            |                        |            |                        | Adapter/battery-charger included (PM8907)             |                                     |                           |
| Size                                                     | 25.6 x 16.9 x 6.4 mm (10.1 x 6.7 x 2.5 in)                                                                                                          |            |                        |            |                        | 23.2 x 11.5 x 5.0 mm (9.2 x 4.5 x 2 in)               |                                     |                           |
| Weight                                                   | 2 kg (4.4 lb)                                                                                                                                       |            |                        |            |                        | 1.2 kg (2.64 lbs)                                     |                                     |                           |
| PC and Printer Interface                                 | Using optional optically insulated adapter/cable OC4USB (USB) or PM9080 (RS-232)                                                                    |            |                        |            |                        |                                                       |                                     |                           |
| Warranty                                                 | Three-years on main instrument, one-year on the standard accessories                                                                                |            |                        |            |                        |                                                       |                                     |                           |

Detailed technical specifications, optional accessories and a virtual product demo can be found on the Fluke web site. Check it out at: [www.fluke.com/scopemeter](http://www.fluke.com/scopemeter).

## Ordering information

|              |                                                       |         |                                                                                 |
|--------------|-------------------------------------------------------|---------|---------------------------------------------------------------------------------|
| Fluke-199C/S | Color ScopeMeter (200 MHz / 2.5 GS/s) with SCC190 kit | BP120MH | Rechargeable NiMH Battery for use with Fluke 120 Series                         |
| Fluke-199C   | Color ScopeMeter (200 MHz / 2.5 GS/s)                 | BP190   | Rechargeable NiMH Battery for use with Fluke 190 Series                         |
| Fluke-196C/S | Color ScopeMeter (100 MHz / 1 GS/s) with SCC190 kit   | SW90W   | FlukeView ScopeMeter Software for Windows                                       |
| Fluke-196C   | Color ScopeMeter (100 MHz / 1 GS/s)                   | OC4USB  | Optically isolated USB adapter/cable                                            |
| Fluke-199B/S | ScopeMeter (200 MHz / 2.5 GS/s) with SCC190 kit       | PM9080  | Optically isolated RS232 adapter/cable                                          |
| Fluke-199B   | ScopeMeter (200 MHz / 2.5 GS/s)                       | SCC190  | Software - Cable - Case kit for Fluke 190 Series                                |
| Fluke-196B/S | ScopeMeter (100 MHz / 1 GS/s) with SCC190 kit         | SCC120  | Software - Cable - Case kit for Fluke 120 Series                                |
| Fluke-196B   | ScopeMeter (100 MHz / 1 GS/s)                         | C195    | Durable, universal soft carrying case for ScopeMeter Test Tools and accessories |
| Fluke-192B/S | ScopeMeter (60 MHz / 500 MS/s) with SCC190 kit        | C190    | Hard shell protective carrying case for Fluke 190 Series                        |
| Fluke-192B   | ScopeMeter (60 MHz / 500 MS/s)                        | C125    | Durable, protective soft carrying case for Fluke 120 Series                     |
| Fluke-125/S  | Industrial ScopeMeter, 40 MHz, with SCC120 kit        | C120    | Hard shell protective carrying case for Fluke 120 Series                        |
| Fluke-125    | Industrial ScopeMeter, 40 MHz                         | DP120   | Differential Voltage Probe for use with Fluke 120 Series                        |
| Fluke-124/S  | Industrial ScopeMeter, 40 MHz, with SCC120 kit        | VPS40   | 40 MHz, 10:1 Voltage probe set for use with Fluke 120 Series                    |
| Fluke-124    | Industrial ScopeMeter, 40 MHz                         |         |                                                                                 |
| Fluke-123/S  | Industrial ScopeMeter, 20 MHz, with SCC120 kit        |         |                                                                                 |
| Fluke-123    | Industrial ScopeMeter, 20 MHz                         |         |                                                                                 |

**Fluke. Keeping your world up and running.®**

**Fluke Corporation**  
PO Box 9090, Everett, WA USA 98206

**Fluke Europe B.V.**  
PO Box 1186, 5602 BD Eindhoven, The Netherlands

**For more information call:**  
In the U.S.A. (800) 443-5853 or Fax (425) 446-5116  
In Europe/M-East/Africa +31 (0) 40 2675 200 or Fax +31 (0) 40 2675 222  
In Canada (800)-36-FLUKE or Fax (905) 890-6866  
From other countries +1 (425) 446-5500 or Fax +1 (425) 446-5116  
Web access: <http://www.fluke.com>

©2007 Fluke Corporation. All rights reserved.  
Specifications subject to change without notice.  
Trademarks are the property of their respective owners.  
Printed in U.S.A. 4/2007 1629083 D-EN-N Rev F