

THIN FILM CHIP INDUCTORS

ATFC-0402

 RoHS/RoHS II Compliant



1.00 x 0.50 x 0.32mm

FEATURES:

- Photolithographic single layer ceramic chip
- High SRF, excellent Q, superior temperature stability
- Tight tolerance $\pm 0.1\text{nH}$ available
- Self resonant frequency controlled within 10%
- Stable inductance in high frequency circuit
- Highly stable design for critical needs

APPLICATIONS:

- Cell phones and GPS
- VCO, TCXO Circuit and RF Transceiver Module
- Wireless LAN, Bluetooth Module, Communication Appliances

STANDARD SPECIFICATIONS:

PARAMETERS

ABRACON P/N:	ATFC-0402
Operating temperature:	-45°C to +85°C
Storage temperature:	+25 $\pm$ 3°C, 80% RH max

Part Number ATFC-0402- Inductance Code	L(nH)	Tolerance	Q, Min @ 500MHz	SRF Min (GHz)	R _{DC} Max (Ω)	I _{DC} Max (mA)
ATFC-0402-0N2	0.2	B, C, S	13	14	0.10	800
ATFC-0402-0N3	0.3	B, C, S	13	14	0.10	800
ATFC-0402-0N4	0.4	B, C, S	13	14	0.10	800
ATFC-0402-0N5	0.5	B, C, S	13	14	0.15	700
ATFC-0402-0N6	0.6	B, C, S	13	14	0.15	700
ATFC-0402-0N8	0.8	B, C, S	13	14	0.15	700
ATFC-0402-0N9	0.9	B, C, S	13	14	0.15	700
ATFC-0402-1N0	1.0	B, C, S	13	12	0.15	700
ATFC-0402-1N1	1.1	B, C, S	13	12	0.15	700
ATFC-0402-1N2	1.2	B, C, S	13	12	0.15	700
ATFC-0402-1N3	1.3	B, C, S	13	10	0.25	700
ATFC-0402-1N4	1.4	B, C, S	13	10	0.25	700
ATFC-0402-1N5	1.5	B, C, S	13	10	0.25	700
ATFC-0402-1N6	1.6	B, C, S	13	10	0.25	560
ATFC-0402-1N7	1.7	B, C, S	13	10	0.25	560
ATFC-0402-1N8	1.8	B, C, S	13	10	0.25	560
ATFC-0402-1N9	1.9	B, C, S	13	8	0.35	560
ATFC-0402-2N0	2.0	B, C, S	13	8	0.35	560
ATFC-0402-2N1	2.1	B, C, S	13	8	0.35	440
ATFC-0402-2N2	2.2	B, C, S	13	8	0.35	440
ATFC-0402-2N3	2.3	B, C, S	13	8	0.35	440
ATFC-0402-2N4	2.4	B, C, S	13	8	0.35	440
ATFC-0402-2N5	2.5	B, C, S	13	8	0.35	440
ATFC-0402-2N6	2.6	B, C, S	13	8	0.35	440
ATFC-0402-2N7	2.7	B, C, S	13	8	0.35	440
ATFC-0402-2N8	2.8	B, C, S	13	6	0.45	380
ATFC-0402-2N9	2.9	B, C, S	13	6	0.45	380
ATFC-0402-3N0	3.0	B, C, S	13	6	0.45	380
ATFC-0402-3N1	3.1	B, C, S	13	6	0.45	380
ATFC-0402-3N2	3.2	B, C, S	13	6	0.45	380
ATFC-0402-3N3	3.3	B, C, S	13	6	0.45	380
ATFC-0402-3N4	3.4	B, C, S	13	6	0.55	380
ATFC-0402-3N5	3.5	B, C, S	13	6	0.55	380
ATFC-0402-3N6	3.6	B, C, S	13	6	0.55	380
ATFC-0402-3N7	3.7	B, C, S	13	6	0.55	340
ATFC-0402-3N8	3.8	B, C, S	13	6	0.55	340
ATFC-0402-3N9	3.9	B, C, S	13	6	0.55	340
ATFC-0402-4N3	4.3	B, C, S	13	6	0.65	320
ATFC-0402-4N7	4.7	B, C, S	13	6	0.65	320
ATFC-0402-5N4	5.4	B, C, S	13	6	0.85	280
ATFC-0402-5N6	5.6	B, C, S	13	6	0.85	280
ATFC-0402-5N9	5.9	B, C, S	13	6	0.85	280
ATFC-0402-6N5	6.5	B, C, S	13	6	1.05	260
ATFC-0402-6N8	6.8	B, C, S	13	6	1.05	260

THIN FILM CHIP INDUCTORS

ATFC-0402

 RoHS/RoHS II Compliant



1.00 x 0.50 x 0.32mm

Key Electrical Specifications (Con'd)

Part Number ATFC-0402- Inductance Code	L(nH)	Tolerance	Q, Min @ 500MHz	SRF Min (GHz)	RDC Max (Ω)	IDC Max (mA)
ATFC-0402-7N2	7.2	B, C, S	13	6	1.05	260
ATFC-0402-8N0	8.0	B, C, S	13	5.5	1.25	220
ATFC-0402-8N1	8.1	B, C, S	13	5.5	1.25	220
ATFC-0402-8N2	8.2	B, C, S	13	5.5	1.25	220
ATFC-0402-9N1	9.1	B, C, S	13	5.5	1.25	220
ATFC-0402-10N	10.0	F, G, H, J	13	4.5	1.35	200
ATFC-0402-10N8	10.8	F, G, H, J	13	4.5	1.35	200
ATFC-0402-12N	12.0	F, G, H, J	13	3.7	1.55	180
ATFC-0402-13N8	13.8	F, G, H, J	13	3.7	1.75	180
ATFC-0402-15N	15.0	F, G, H, J	13	3.3	1.75	130
ATFC-0402-17N	17.0	F, G, H, J	13	3.1	1.95	100
ATFC-0402-18N	18.0	F, G, H, J	13	3.1	2.15	100
ATFC-0402-20N8	20.8	F, G, H, J	13	2.8	2.55	90
ATFC-0402-22N	22.0	F, G, H, J	13	2.8	2.65	90
ATFC-0402-27N	27.0	F, G, H, J	13	2.5	3.25	75
ATFC-0402-33N	33.0	J	13	2.5	4.50	75

Test Conditions and Equipments

Inductance (L)

- Test equipment: Agilent4287A+Agilent16196C
- Test frequency: 500MHz

PART IDENTIFICATION:


ATFC- 0402- -

Inductance Code
Please refer to the table above

Inductance Tolerance
B: $\pm 0.1\text{nH}$
C: $\pm 0.2\text{nH}$
S: $\pm 0.3\text{nH}$
F: $\pm 1\%$
G: $\pm 2\%$
H: $\pm 3\%$
J: $\pm 5\%$


Packaging
T: Tape and Reel
(10kpcs reel)

OUTLINE DIMENSIONS:



A	B	C	D
1.0 $\pm$ 0.05	0.5 $\pm$ 0.05	0.32 $\pm$ 0.05	0.20 $\pm$ 0.10

Recommended Land Pattern



A	B	C
0.50	0.45	0.60 $\pm$ 0.2

Dimension: mm

THIN FILM CHIP INDUCTORS



ATFC-0402

 RoHS/RoHS II Compliant




1.00 x 0.50 x 0.32mm

MATERIALS:



No.	Material
1	Alumina Substrate
2	Inner Electrode (Ni-Cr)
3	Barrier Layer (Ni)
4	External Electrode (Sn)
5	Edge Electrode
6	Cu Circuits
7	Overcoat

REFLOW PROFILE:



THIN FILM CHIP INDUCTORS

ATFC-0402


 RoHS/RoHS II Compliant




1.00 x 0.50 x 0.32mm

TAPE & REEL:

T= tape and reel (10,000pcsreel)



A	B	W	E	F	P0	P1	P2	$\Phi D0$	T
0.70 $\pm$ 0.05	1.16 $\pm$ 0.05	8.00 $\pm$ 0.10	1.75 $\pm$ 0.05	3.50 $\pm$ 0.05	4.00 $\pm$ 0.10	2.00 $\pm$ 0.05	2.00 $\pm$ 0.05	1.55 $\pm$ 0.05	0.40 $\pm$ 0.03



ΦA	ΦB	ΦC	W	T
178.0 $\pm$ 1.0	60.0 $\pm$ 1.0	13.5 $\pm$ 0.7	9.5 $\pm$ 1.0	11.5 $\pm$ 1.0

Dimension: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 04-17-20

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ATFC-0402-0N2-BT](#) [ATFC-0402-0N4-BT](#) [ATFC-0402-0N8-BT](#) [ATFC-0402-1N0-BT](#) [ATFC-0402-1N1-BT](#) [ATFC-0402-1N2-BT](#) [ATFC-0402-1N3-BT](#) [ATFC-0402-1N4-BT](#) [ATFC-0402-1N5-BT](#) [ATFC-0402-1N6-BT](#) [ATFC-0402-1N7-BT](#) [ATFC-0402-1N8-BT](#) [ATFC-0402-1N9-BT](#) [ATFC-0402-2N0-BT](#) [ATFC-0402-2N1-BT](#) [ATFC-0402-2N2-BT](#) [ATFC-0402-2N3-BT](#) [ATFC-0402-2N4-BT](#) [ATFC-0402-2N5-BT](#) [ATFC-0402-2N6-BT](#) [ATFC-0402-2N7-BT](#) [ATFC-0402-2N8-BT](#) [ATFC-0402-2N9-BT](#) [ATFC-0402-3N0-BT](#) [ATFC-0402-3N1-BT](#) [ATFC-0402-3N2-BT](#) [ATFC-0402-3N3-BT](#) [ATFC-0402-3N4-BT](#) [ATFC-0402-3N5-BT](#) [ATFC-0402-3N6-BT](#) [ATFC-0402-3N7-BT](#) [ATFC-0402-3N8-BT](#) [ATFC-0402-3N9-BT](#) [ATFC-0402-4N7-BT](#) [ATFC-0402-5N6-BT](#) [ATFC-0402-5N9-BT](#) [ATFC-0402-6N8-BT](#) [ATFC-0402-7N2-BT](#) [ATFC-0402-8N0-BT](#) [ATFC-0402-8N2-BT](#) [ATFC-0402-9N1-BT](#) [ATFC-0402-10N-GT](#) [ATFC-0402-12N-GT](#) [ATFC-0402-15N-GT](#) [ATFC-0402-17N-GT](#) [ATFC-0402-18N-GT](#) [ATFC-0402-22N-GT](#) [ATFC-0402-27N-GT](#) [ATFC-0402-20N8-G-T](#) [ATFC-0402-1N4-B-T](#) [ATFC-0402-3N2-B-T](#) [ATFC-0402-3N6-B-T](#) [ATFC-0402-3N9-B-T](#) [ATFC-0402-8N0-B-T](#) [ATFC-0402-10N-G-T](#) [ATFC-0402-3N3-B-T](#) [ATFC-0402-15N-G-T](#) [ATFC-0402-3N7-B-T](#) [ATFC-0402-1N2-B-T](#) [ATFC-0402-27N-G-T](#) [ATFC-0402-1N3-B-T](#) [ATFC-0402-8N2-B-T](#) [ATFC-0402-18N-G-T](#) [ATFC-0402-3N8-B-T](#) [ATFC-0402-22N-G-T](#) [ATFC-0402-5N6-B-T](#) [ATFC-0402-1N8-B-T](#) [ATFC-0402-2N3-B-T](#) [ATFC-0402-3N5-B-T](#) [ATFC-0402-1N1-B-T](#) [ATFC-0402-9N1-B-T](#) [ATFC-0402-2N8-B-T](#) [ATFC-0402-1N5-B-T](#) [ATFC-0402-3N0-B-T](#) [ATFC-0402-4N7-B-T](#) [ATFC-0402-2N0-B-T](#) [ATFC-0402-2N1-B-T](#) [ATFC-0402-2N7-B-T](#) [ATFC-0402-3N4-B-T](#) [ATFC-0402-13N8-G-T](#) [ATFC-0402-1N9-B-T](#) [ATFC-0402-7N2-B-T](#) [ATFC-0402-0N2-B-T](#) [ATFC-0402-2N6-B-T](#) [ATFC-0402-1N0-B-T](#) [ATFC-0402-2N5-B-T](#) [ATFC-0402-1N6-B-T](#) [ATFC-0402-2N4-B-T](#) [ATFC-0402-1N7-B-T](#) [ATFC-0402-33N-J-T](#) [ATFC-0402-3N1-B-T](#) [ATFC-0402-2N2-B-T](#) [ATFC-0402-6N8-B-T](#) [ATFC-0402-0N4-B-T](#) [ATFC-0402-0N8-B-T](#) [ATFC-0402-17N-G-T](#) [ATFC-0402-5N9-B-T](#) [ATFC-0402-2N9-B-T](#) [ATFC-0402-12N-G-T](#)