

PANDUIT PART NO.*	MAT'L SUFFIX	RECOMMENDED FASTENER	'A'	'B'	'C'	'D'	'E'	'F'	'G' (REF)	'H' (REF)	'I' (REF)	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100 pcs.
TM1S4	NONE -0 -30 -69	#4 (M2.5) SCREW	0.513 [13.0]	0.316 [8.0]	0.230 [5.8]	0.130 ±.020 (3.3) ±(.5)	0.067 ±.020 (1.7) ±(.5)	0.125 [3.2]	0.075 [1.9]	0.226	0.121	MINIATURE ONLY	0.064 (29.0)
TM1S6	NONE -0 -30 -69	#6 (M3) SCREW							0.080 [2.0]	0.277	0.146		0.057 (26.0)

Technical drawing of a mechanical part showing a front view and a cross-section A-A.

Front View: A rectangular part with a central circular hole. Dimensions are indicated as follows:

- A : Total width of the part.
- A' : Width of the central circular hole.
- B' : Total height of the part.

Cross-section A-A: A U-shaped profile. Dimensions are indicated as follows:

- G' : Total height of the part.
- H' : Width of the central U-shaped cavity.
- F' : Height of the side walls.
- C' : Total width of the part.
- I' : Width of the base of the U-shaped cavity.

A note "SEE NOTE 2" points to the central circular hole.

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. HOLE DIMENSIONS SHOULD ACCOMMODATE SPECIFIED RECOMMENDED FASTENER.

G00239CN_PB_TMS_A_08

TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

SEE TABLE

GB0239CN

DWG
A
SIZE

8	6-8-05	TMSA		CHANGED RECOMMENDED FASTENER FROM M3.0 TO M2.5	GB0239CN	8				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		