


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	B	Material changed from steel		11/23/94				
1116	C	Was dwg #CCS-T0-1*1*	JWM	6/01/01	JC	6/20/01	JC	6/20/01



PART NO.	WIRE RANGE (AWG)	DIAMETER 'B'	L	C	WALL THICK-NESS
CCS-T0-1010	12-10	.135	.56	.28	.040
CCS-T0-1414	16-14	.090	.56	.28	.030
CCS-T0-1818	22-18	.070	.56	.28	.030

NOTES:

1. MATERIAL: ANNEALED COPPER
FINISH: ELECTRO-TIN PLATING
2. CONTINUOUS OPERATING TEMPERATURE:
-40°F (-40°C) TO 347°F (175°C)
3. VOLTAGE RATING: 600 V.
4. TO BE FREE OF BURRS.



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. WE SHALL DETERMINE THE CAUSE OF FAILURE OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



LR22130K6

OSHA
Acceptable

Tolerances: Unless
Otherwise Specified:

.X = ±.015
.XX = ±.010
.XXX = ±.005

SPC-F005.DWG

DRAWN BY:

DATE:

JAP

11/12/91

CHECKED BY:

DATE:

JC

11/21/91

APPROVED BY:

DATE:

JL

11/21/91

DRAWING TITLE:

Non-Insulated Butt Connectors

SIZE DWG. NO.

A

TA-349

ELECTRONIC FILE

TA-349.dwg

REV

C

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1



SPC TECHNOLOGY