

The information contained in this technical data sheet is of a general nature and provided for information only. Panacol does not warrant any of the data. It is the user's responsibility to determine the suitability of this product for any intended use. Panacol recommends that each user adequately tests its proposed use and application before actual repetitive use, using the data in this data sheet as a general guideline. The user assumes all risk and liability connected with the use of this product. The user should adopt such precautions as may be advisable for the protection of property and persons against any hazards that maybe involved in this product's handling or use. Panacol specifically disclaims any liability for consequential or incidental damages of any kind arising from the handling or use of this product. The information contained in this technical data sheet offers no assurance that the product use, application, or process will not infringe on existing patents or licenses of others. Nothing in this technical data sheet transfers or grants license for the use of any patents, trade secrets, intellectual property, or confidential information that is the property of Panacol.

**Adhesives  
and more...**

## TECHNICAL DATASHEET

## Vitralit® 6138

Vitralit® 6138 is a UV- and thermally curable adhesive. It has a good resistance to chemicals, an application range for high temperatures and an extraordinary thermal conductivity.

The incorporated spacers of 40 µm guarantee the identical space between the building components and the carrier material, even during automatic manufacturing.

### Shelf life:

Store in original, unopened containers for 6 months at max. 25 °C

## Technical Data

Color	white
Resin	acrylate
Filler	approx. 58% Aluminiumoxid

## UNCURED PROPERTIES

Viscosity (Brookfield LVT/25 °C) [Pa·s]	PE-Norm P001	150 to 170
Flash point [°C]	PE-Norm P050	> 93
Density [g/cm³]	PE-Norm P003	approx. 2.05

## Curing

UV(UV-A 60mW/cm² Thickn.st. 0,5mm): [sec.]	PE-Norm P002	30
Thermal Curing 140 °C :[Min]	PE-Norm P035	30
Full Strength [hours]	PE-Norm P032	after 12

## CURED PROPERTIES

Temperature Resistance [°C]	PE-Norm P030	-40 to 180
Hardness [Shore D]	PE-Norm P052	55 to 65
Tg [°C] (DSC)	PE-Norm P009	> 44
Thermal conductivity [W/m·K]	ASTM 1530	1.05

## Mechanical Data

Lap Shear Strength (Alu/Alu) [MPa]	[PE-Norm P013]	approx. 14.0
Lap Shear Strength (Alu/Cu) [MPa]	[PE-Norm P013]	approx. 5.5
Lap Shear Strength (Steel/Steel) [MPa]	[PE-Norm P013]	approx. 11.0
Tensile Strength (Glas/Stahl) [MPa]	[PE-Norm P013]	approx. 9,0
Tensile Strength (Glass/Alu) [MPa]	[PE-Norm P013]	approx. 8,0

## Instructions for Use

### Surface Preparation

The surfaces to be adhered should be free of dust, oil, fat or any other dirt in order to optimise reproducible bonds. Lightly soiled surfaces can be cleaned with cleaner IP, whereas substrates with low surface energy (such as polyethylene, polypropylene or Teflon) need to be treated physically using plasma or corona to create a suitable working surface. For glass bonding applications we have developed a special primer pen which can be easily applied to prepare the surface for best results.

### Application

Our products are delivered ready for use. As soon as you receive them, you can dispense them, be it by hand from the container, or semi/fully automatically. When applied automatically, we recommend the use of air pressure with the appropriate cartridge/piston combination to dispense the adhesive at the required speed and accuracy. If help is required, please consult our engineering department.

Please read the corresponding **Safety Data Sheet** for this product.

**Adhesives  
and more...**