





Plastic caps:





black KF 4105
grey KF 4107
red KF 4109
white KF 4110

P.C.B. MOUNTING HOLE DIMENSIONS (TOP VIEW)



CIRCUIT DIAGRAM (BOTTOM VIEW)



Tolerances:			Date	Name	FP 1 F / FP 2 F	
			01/09	dr		
			knitter-switch		20 25 69	Page
Circuit diagram	11/11	dr				1/2
Temperatures	04/11	dr				
Modifications	Date	Name				

Specifications:

Contact rating:	max.: 0.4VA, 28V DC min.: 1µA, 20mV DC
Contact resistance:	100mOhm max.
Insulation resistance:	500MOhm min. at 250V DC
Operating temperature:	-40°C to +85°C
Storage temperature:	-40°C to +85°C
Mechanical life:	min. 30 000 cycles
Soldering conditions:	auto-soldering: max.: 250 +/-5°C, 7sec. max.: 270 +/-5°C, 5sec.
Mounting:	on pc-board
ESD resistance:	8kV min. (between lever and terminals)
Switching function:	on - mom
Material:	Contacts: phosphor bronze, gold plated Terminals: PC terminals, crimped, phosphor bronze, gold plated Case / lever: PES, UL94V-0, washable



Tolerances:			Date	Name	FP 1 F / FP 2 F	
			01/09	dr		
			knitter-switch		20 25 69	Page
						2/2
Modifications	Date	Name				